

SCSI Ultra2/U160/U320 LVD Cable (HD68 M/M) 10-ft.

MODEL NUMBER: **S450-010**



Highlights

- Premium double-shielded cable
- Meets the most current SCSI specifications for high-speed devices

System Requirements

- Any external SCSI device or host controller card requiring HD68 interface

Package Includes

- 10-ft. SCSI U2/U160/U320 LVD/SE cable HD68M to HD68M w/thumb screws

Description

Multi-platform SCSI III external peripheral cable HD68M/M. This 10ft cable is designed to connect two SCSI III (fast and wide) or SCSI II devices together. Supports all legacy transfer rates through Ultra 320. Manufactured using double shielded 34 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene.

Features

- Backwards compatibility with previous SCSI generations
- Supports all SCSI transfer rates through 320/mb/s
- LVD/SE compliant
- Double shielded (foil and braid)
- 34 twisted pair conductors
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

Specifications

OVERVIEW	
Intended Application	Connecting Drives
Cable Type	SCSI
Model Type	SCSI Ultra2/160/320 External
INPUT	
Cable Length (ft.)	10

Cable Length (m)	3.05
UPC ASSIGNMENT	
Unit Carton UPC#	037332121318
PHYSICAL	
Color	Black
Style	SCSI
CONNECTIONS	
Connector A	 HD68 (MALE)
Connector B	 HD68 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

Related Items

Optional Products

Model Number	Description	Qty.
S140-000	External SCSI U320 LVD/SE Active Terminator (HD68 M)	1
S450-003	3-ft. SCSI Ultra2/U160/U320 LVD Cable (HD68 M/M w/thumbscrews)	1
S450-010	6-ft. SCSI Ultra2/U160/U320 LVD Cable (HD68 M/M w/thumbscrews)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:

<http://www.tripplite.com/sku/S450-010>.