

ULTEMTM RESIN ATX200

REGION AMERICAS

DESCRIPTION

High flow Polyetherimide blend. ECO Conforming, UL94 V0 Listing.

INDUSTRY	SUB INDUSTRY
Electrical and Electronics	Electrical Devices and Displays, Electrical Components and Infrastructure
Industrial	Electronic Material Handling, Electronic Material

TYPICAL PROPERTY VALUES

Revision 20200610

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
MECHANICAL			
Tensile Stress, yld, Type I, 5 mm/min	96	MPa	ASTM D 638
Tensile Strain, brk, Type I, 5 mm/min	70	%	ASTM D 638
Flexural Stress, yld, 2.6 mm/min, 100 mm span	144	MPa	ASTM D 790
Flexural Modulus, 2.6 mm/min, 100 mm span	3170	MPa	ASTM D 790
IMPACT			
Izod Impact, unnotched, 23°C	2082	J/m	ASTM D 4812
Izod Impact, notched, 23°C	53	J/m	ASTM D 256
Izod Impact, Reverse Notched, 3.2 mm	2136	J/m	ASTM D 256
THERMAL			
HDT, 1.82 MPa, 6.4 mm, unannealed	190	°C	ASTM D 648
Relative Temp Index, Elec ⁽¹⁾	115	°C	UL 746B
Relative Temp Index, Mech w/impact ⁽¹⁾	115	°C	UL 746B
Relative Temp Index, Mech w/o impact ⁽¹⁾	115	°C	UL 746B
PHYSICAL			
Specific Gravity	1.26	-	ASTM D 792
Mold Shrinkage, flow, 3.2 mm	0.5 – 0.7	%	SABIC method
Melt Flow Rate, 337°C/6.6 kgf	24	g/10 min	ASTM D 1238
ELECTRICAL			
Comparative Tracking Index (UL) {PLC}	4	PLC Code	UL 746A
Hot-Wire Ignition (HWI), PLC 0	≥0.75	mm	UL 746A
High Amp Arc Ignition (HAI), PLC 4	≥0.75	mm	UL 746A
FLAME CHARACTERISTICS ⁽¹⁾			
UL Yellow Card Link	E121562-221073	-	-
UL Recognized, 94V-0 Flame Class Rating	≥1.5	mm	UL 94
UL Recognized, 94V-2 Flame Class Rating	≥0.75	mm	UL 94
INJECTION MOLDING			
Drying Temperature	135	°C	
Drying Time	4 – 6	hrs	
Drying Time (Cumulative)	10	hrs	

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
Maximum Moisture Content	0.02	%	
Melt Temperature	350 – 370	°C	
Nozzle Temperature	350 – 370	°C	
Front - Zone 3 Temperature	350 – 370	°C	
Middle - Zone 2 Temperature	345 – 365	°C	
Rear - Zone 1 Temperature	340 – 360	°C	
Mold Temperature	135 – 165	°C	
Back Pressure	0.3 – 0.7	MPa	
Screw Speed	40 – 70	rpm	
Shot to Cylinder Size	40 – 60	%	
Vent Depth	0.025 – 0.076	mm	

(1) UL Ratings shown on the technical datasheet might not cover the full range of thicknesses and colors. For details, please see the UL Yellow Card.

DISCLAIMER

Any sale by SABIC, its subsidiaries and affiliates (each a "seller"), is made exclusively under seller's standard conditions of sale (available upon request) unless agreed otherwise in writing and signed on behalf of the seller. While the information contained herein is given in good faith, SELLER MAKES NO WARRANTY, EXPRESS OR IMPLIED, INCLUDING MERCHANTABILITY AND NONINFRINGEMENT OF INTELLECTUAL PROPERTY, NOR ASSUMES ANY LIABILITY, DIRECT OR INDIRECT, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OR PURPOSE OF THESE PRODUCTS IN ANY APPLICATION. Each customer must determine the suitability of seller materials for the customer's particular use through appropriate testing and analysis. No statement by seller concerning a possible use of any product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right.