





DUAL-IN-LINE SOCKETS

SERIES 115...001 • VERY LOW PROFILE • OPEN FRAME



- Low profile DIP socket, sits only .122" above the PCB
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 115 uses MM #0501 pins. See page 162 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION							
	A	B	C									
10	0.5	0.2	0.3	41	115-XX-210-41-001000							
4	0.2	0.3	0.4	102	115-XX-304-41-001000							
6	0.3	0.3	0.4	67	115-XX-306-41-001000							
8	0.4	0.3	0.4	50	115-XX-308-41-001000							
10	0.5	0.3	0.4	40	115-XX-310-41-001000							
14	0.7	0.3	0.4	28	115-XX-314-41-001000							
16	0.8	0.3	0.4	25	115-XX-316-41-001000							
18	0.9	0.3	0.4	22	115-XX-318-41-001000							
20	1.0	0.3	0.4	20	115-XX-320-41-001000							
22	1.1	0.3	0.4	18	115-XX-322-41-001000							
24	1.2	0.3	0.4	16	115-XX-324-41-001000							
28	1.4	0.3	0.4	14	115-XX-328-41-001000							
20	1.0	0.4	0.5	20	115-XX-420-41-001000							
22	1.1	0.4	0.5	18	115-XX-422-41-001000							
24	1.2	0.4	0.5	16	115-XX-424-41-001000							
28	1.4	0.4	0.5	14	115-XX-428-41-001000							
32	1.6	0.4	0.5	12	115-XX-432-41-001000							
24	1.2	0.6	0.7	16	115-XX-624-41-001000							
28	1.4	0.6	0.7	14	115-XX-628-41-001000							
32	1.6	0.6	0.7	12	115-XX-632-41-001000							
36	1.8	0.6	0.7	11	115-XX-636-41-001000							
40	2.0	0.6	0.7	10	115-XX-640-41-001000							
42	2.1	0.6	0.7	9	115-XX-642-41-001000							
48	2.4	0.6	0.7	8	115-XX-648-41-001000							
50	2.5	0.6	0.7	8	115-XX-650-41-001000							
52	2.6	0.6	0.7	7	115-XX-652-41-001000							
50	2.5	0.9	1.0	8	115-XX-950-41-001000							
52	2.6	0.9	1.0	7	115-XX-952-41-001000							
64	3.2	0.9	1.0	6	115-XX-964-41-001000							
SPECIFY PLATING CODE XX =						91	93		41 ◆	43 ◆	47 ◆	
Sleeve (Pin) 						200 μ" Sn/Pb	200 μ" Sn/Pb		200 μ" Sn	200 μ" Sn	200 μ" Sn	
Contact (Clip) 						10 μ" Au	30 μ" Au		10 μ" Au	30 μ" Au	Au Flash	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[115-43-964-41-001000](#) [115-43-952-41-001000](#) [115-43-950-41-001000](#) [115-43-652-41-001000](#) [115-43-650-41-001000](#) [115-43-648-41-001000](#) [115-43-642-41-001000](#) [115-43-636-41-001000](#) [115-43-432-41-001000](#) [115-43-428-41-001000](#) [115-43-424-41-001000](#) [115-43-422-41-001000](#) [115-43-420-41-001000](#) [115-43-322-41-001000](#) [115-43-310-41-001000](#) [115-43-306-41-001000](#) [115-43-304-41-001000](#) [115-43-210-41-001000](#) [115-43-640-41-001000](#) [115-43-632-41-001000](#) [115-43-628-41-001000](#) [115-43-624-41-001000](#) [115-43-328-41-001000](#) [115-43-324-41-001000](#) [115-43-320-41-001000](#) [115-43-318-41-001000](#) [115-43-316-41-001000](#) [115-43-314-41-001000](#) [115-43-308-41-001000](#) [115-93-624-41-001000](#) [115-93-628-41-001000](#) [115-93-310-41-001000](#) [115-13-318-41-001000](#) [115-93-314-41-001000](#) [115-93-318-41-001000](#) [115-93-316-41-001000](#) [115-93-640-41-001000](#) [115-93-632-41-001000](#) [115-93-324-41-001000](#) [115-93-320-41-001000](#) [115-93-328-41-001000](#) [115-93-306-41-001000](#) [115-93-308-41-001000](#) [115-93-964-41-001000](#) [115-93-952-41-001000](#) [115-93-950-41-001000](#) [115-93-652-41-001000](#) [115-93-650-41-001000](#) [115-93-648-41-001000](#) [115-93-642-41-001000](#) [115-93-636-41-001000](#) [115-93-432-41-001000](#) [115-93-428-41-001000](#) [115-93-424-41-001000](#) [115-93-422-41-001000](#) [115-93-420-41-001000](#) [115-93-322-41-001000](#) [115-93-304-41-001000](#) [115-93-210-41-001000](#)