

HCM1A1707

Automotive grade

High current power inductors



Product features

- AEC-Q200 Grade 1 qualified
- High current carrying capacity
- Magnetically shielded, low EMI
- Frequency range up to 1 MHz
- Inductance range from 1.0 μ H to 68 μ H
- Current range from 5.2 A to 48 A
- 17.5 mm x 17.2 mm footprint surface mount package in a 7.0 mm height
- Moisture Sensitivity Level (MSL): 1
- Alloy powder core material
- Halogen free, lead free, RoHS compliant

Applications

- Body electronics
 - Central body control module
 - Headlamps, tail lamps and interior lighting
 - Heating ventilation and air conditioning controllers (HVAC)
 - Doors, window lift and seat control
- Advanced driver assistance systems
 - Adaptive cruise control (ACC)
 - Automatic parking control
 - Collision avoidance system/ Car black box system
- Infotainment and cluster electronics
 - Audio subsystem: head unit and trunk amp
 - Digital instrument cluster
 - In-vehicle infotainment (IVI) and navigation
- Chassis and safety electronics
 - Airbag control unit
 - Electronic stability control system (ESC)
 - Electric parking brake
 - Electronic power steering (EPS)/ Anti-locking braking system (ABS)
- Engine and Powertrain Systems
 - Electric pumps, motor control and auxiliaries
 - Powertrain control module (PCU)/ Engine Control unit (ECU)
 - Transmission Control Unit (TCU)

Environmental Data

- Storage temperature range (Component): -55 °C to +155 °C
- Operating temperature range: -55 °C to +155 °C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 (latest revision) compliant



Product Specifications

Part Number ⁶	OCL ¹ (μH) $\pm 20\%$	FLL ² (μH) minimum	I_{rms} ³ (A)	I_{sat} ⁴ (A)	DCR (m Ω) typical @ +20 °C	DCR (m Ω) maximum @ +20 °C	K-factor ⁵
HCM1A1707-1R0-R	1.0	0.64	33	48	1.4	1.55	133
HCM1A1707-1R5-R	1.5	0.96	25.5	46	2.05	2.25	94
HCM1A1707-2R2-R	2.2	1.41	24	28	2.4	2.65	105
HCM1A1707-3R3-R	3.3	2.11	21	22	3.1	3.40	103
HCM1A1707-4R7-R	4.7	3.01	18	20	4.4	4.72	85
HCM1A1707-6R8-R	6.8	4.35	12	18	6.55	7.55	79
HCM1A1707-8R2-R	8.2	5.25	12	16	8.1	8.70	45
HCM1A1707-100-R	10	6.4	12	14	9.3	10	49
HCM1A1707-150-R	15	9.6	9.0	14	14.5	15.5	30
HCM1A1707-220-R	22	14.1	8.0	11	20.5	23	27
HCM1A1707-330-R	33	21.1	6.0	9.0	35.1	37	20
HCM1A1707-470-R	47	30.1	5.5	8.0	41	47	17
HCM1A1707-680-R	68	43.5	5.2	6.0	51	60	17

1. Open Circuit Inductance (OCL) Test Parameters: 100 kHz, 0.25 V_{rms}, 0.0 Adc, +25 °C

2. Full Load Inductance (FLL) Test Parameters: 100 kHz, 0.25 V_{rms}, I_{rms}, +25 °C

3. I_{rms}: DC current for an approximate temperature rise of 30 °C without core loss. Derating is necessary for AC currents. PCB layout, trace thickness and width, air-flow, and proximity of other heat generating components will affect the temperature rise. It is recommended that the temperature of the part not exceed 155 °C under worst case operating conditions verified in the end application.

4. I_{sat}: Peak current for approximately 20% rolloff @ +25 °C

5. K-factor: Used to determine B_{pp} for core loss (see graph). B_p-p = K * L * ΔI . B_{pp}: (Gauss), K: (K-factor from table), L: (Inductance in μH), ΔI (Peak to peak ripple current in Amps).

6. Part Number Definition: HCM1A1707-xxx-R



HCM1A1707 = Product code and size

xxx= inductance value in μH , R= decimal point,


If no R is present then last character equals number of zeros

-R suffix = RoHS compliant


Dimensions (mm)



Recommended Pad Layout



Schematic



Part marking: HCM1A1707, XXX=inductance value in μH , R=decimal point. If no R is present then last character equals number of zeros.

xxxx=Lot code

All soldering surfaces to be coplanar within 0.1 millimeters

DCR measured from point "a" to point "b"


Color: Grey

Do not route traces or vias underneath the inductor



Packaging information (mm)

Drawing not to scale







Supplied in tape and reel packaging, 200 parts per 13" diameter reel








Core loss vs B_{p-p}









Core loss vs B_{p-p}









Core loss vs B_{p-p}




Inductance and temperature rise vs. current



Inductance and temperature rise vs. current



Inductance and temperature rise vs. current



Solder reflow profile




Table 1 - Standard SnPb Solder (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5mm)	235°C	220°C
≥2.5mm	220°C	220°C

Table 2 - Lead (Pb) Free Solder (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6mm	260°C	260°C	260°C
1.6 – 2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C

Reference JEDEC J-STD-020

Profile Feature	Standard SnPb Solder	Lead (Pb) Free Solder
Preheat and Soak		
• Temperature min. (T_{smin})	100°C	150°C
• Temperature max. (T_{smax})	150°C	200°C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 Seconds	60-120 Seconds
Average ramp up rate T_{smax} to T_p	3°C/ Second Max.	3°C/ Second Max.
Liquidous temperature (T_L)	183°C	217°C
Time at liquidous (t_L)	60-150 Seconds	60-150 Seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)** within 5 °C of the specified classification temperature (T_C)	20 Seconds**	30 Seconds**
Average ramp-down rate (T_p to T_{smax})	6°C/ Second Max.	6°C/ Second Max.
Time 25°C to Peak Temperature	6 Minutes Max.	8 Minutes Max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

** Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics