

Remote Programmable HCS-Series

Remote Programmable Laboratory Grade Switching Mode Power Supply

BENCH TOP



Description

Following up on the success of our HCS series high power supplies, we come up with this new range of low power supplies based on the feedbacks from end users.

We add an USB port for access to computer to run cyclical operation with programmable voltage, current, period time and cycles.

The on-housing presets, separate remote control, rotary encoder dual action control for easy tuning of voltage and current, and all the features of the original HCS are kept. In addition it is of universal AC input voltage.

It is probably the most cost effective Remote Programmable Power supply with such advanced features and protections. It is ideal for laboratory, university, work shop, production, quality control and sophisticated DIY applications.

Features

- Remote Programmable via USB to computer .
- 20 programmable sets of V, I & cycle periods for repetitive operation up to 999 cycles .
- 3 user defined V & I panel presets for frequent use
- Wired Remote Control of V, I, & output On-Off without computer.
- Rotary encoder knob with definitive action of fine and coarse tuning
- Smart cooling fan speed control from zero to full speed
- Self diagnostic check on LED display and cooling fan on start up
- Isolated ground , Active PFC & high power efficiency
- Universal AC input
- Over load , Tracking Over Voltage Protections
- Constant Current limit setting with output open circuit

Specifications

Models	HCS - 3200	HCS - 3202	HCS - 3204
Output			
Variable Output Voltage	1 - 18VDC	1 - 36VDC	1 - 60VDC
Variable Output Current	0 - 20A	0 - 10A	0 - 5A
Voltage Regulation			
Load (10 - 100% Rated Current)	50mV		
Line (90 - 264VAC Variation)	20mV		
Current Regulation			
Load (10 - 90% Rated Voltage)	100mA	100mA	100mA
Line (90 - 264VAC Variation)	50mA		
Ripple & Noise			
Ripple & Noise (r.m.s.) Voltage	5mV	5mV	5mV
Ripple & Noise (peak-peak) Voltage	50mV	50mV	50mV
Switching Frequency	100 - 120Khz~	100 - 120Khz~	100 - 120Khz~
Tracking Over Voltage Protections	O/P 1-5V : set voltage +2V O/P 5-18V : set voltage +3V	O/P 1-5V : set voltage +2V O/P 5-20V : set voltage +3V O/P 20-36V : set voltage +4V	O/P 1-5V : set voltage +2V O/P 5-20V : set voltage +3V O/P 20-60V : set voltage +4V
Meter Type & Accuracy			
Voltage Meter	3 Digit LED Display $\pm 0.2\%$ +3counts		
Current Meter	3 Digit LED Display $\pm 0.2\%$ +3counts		
Input Voltage	90 - 264VAC 50/60Hz~		
Full Load Input Current (230VAC/100VAC)	2.1/4.6A	2.1/4.6A	1.7/3.8A
Efficiency (230VAC)	85%	86%	86%
Power Factor Control	Power factor correction >0.95 at optimal load		
Cooling Method	Thermostatic Control Fan from Zero to full speed		
Protections	Overload, Short Circuit by Constant Current, Output Tracking Over Voltage, Over Temperature		
Special Features	3 User defined V & I preset, Remote control V, I and output on-off		
Preset Cycle Programming	Max. 20 presets of V & I, Max. preset time 100 minutes (99min + 60sec), Max. preset cycle 999		
Approvals	CE EMC: EN 55011, 55022 LVD: EN 60950, 61010		
Dimensions (WxHxD)	200x80x208 mm 7.8x3.2x8.2 inch		
Weight	2.4 kg 5.2 lbs		

■ All values are based on the Standard ambient Temperature 25°C and Pressure 0.1Mpa.

■ SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE