



- SEE SHEET 2 FOR  
ADDITIONAL LEAD FREE  
PART NUMBERS

|                                              |                       |              |      |      |       |       |    |                 |                            |    |
|----------------------------------------------|-----------------------|--------------|------|------|-------|-------|----|-----------------|----------------------------|----|
|                                              |                       | <div>3</div> | .125 | .318 | .184  | .100  | 1  | 2               | 4- 87348-3                 | -3 |
|                                              | OBSOLETE              | <div>2</div> |      |      | 4.840 | 4.000 | 40 | 40              | 4-                         | -2 |
|                                              | OBSOLETE              |              |      |      | 4.840 | 4.000 | 40 | 40              | 4-                         | -1 |
|                                              |                       |              |      |      | 3.984 | 3.900 | 39 | 40              | 4-                         | -0 |
|                                              | OBSOLETE              |              |      |      | 3.884 | 3.800 | 38 | 39              | 3-                         | -9 |
|                                              | OBSOLETE              |              |      |      | 3.784 | 3.700 | 37 | 38              | 3-                         | -8 |
|                                              | OBSOLETE              |              |      |      | 3.684 | 3.600 | 36 | 37              | 3-                         | -7 |
|                                              | <div>5</div> OBSOLETE |              |      |      | 3.584 | 3.500 | 35 | 36              | 3-                         | -6 |
| SUPERCEDED BY 3-103321-5                     |                       |              |      |      | 3.484 | 3.400 | 34 | 35              | 3-                         | -5 |
|                                              | OBSOLETE              |              |      |      | 3.384 | 3.300 | 33 | 34              | 3-                         | -4 |
|                                              | OBSOLETE              |              |      |      | 3.284 | 3.200 | 32 | 33              | 3-                         | -3 |
|                                              | OBSOLETE              |              |      |      | 3.184 | 3.100 | 31 | 32              | 3-                         | -2 |
| SUPERCEDED BY 3-103321-1                     |                       |              |      |      | 3.840 | 3.000 | 30 | 31              | 3-                         | -1 |
| SUPERCEDED BY 3-103321-0                     |                       |              |      |      | 2.984 | 2.900 | 29 | 30              | 3-                         | -0 |
| SUPERCEDED BY 2-103321-9                     |                       |              |      |      | 2.884 | 2.800 | 28 | 29              | 2-                         | -9 |
|                                              | OBSOLETE              |              |      |      | 2.784 | 2.700 | 27 | 28              | 2-                         | -8 |
|                                              | OBSOLETE              |              |      |      | 2.684 | 2.600 | 26 | 27              | 2-                         | -7 |
| SUPERCEDED BY 2-103321-6                     |                       |              |      |      | 2.584 | 2.500 | 25 | 26              | 2-                         | -6 |
| SUPERCEDED BY 2-103321-5                     |                       |              |      |      | 2.484 | 2.400 | 24 | 25              | 2-                         | -5 |
| SUPERSEDED BY 2-103321-4                     |                       |              |      |      | 2.384 | 2.300 | 23 | 24              | 2-                         | -4 |
|                                              | OBSOLETE              |              |      |      | 2.284 | 2.200 | 22 | 23              | 2-                         | -3 |
| SUPERCEDED BY 2-103321-2                     |                       |              |      |      | 2.100 | 2.100 | 21 | 22              | 2-                         | -2 |
|                                              | OBSOLETE              |              |      |      | 2.840 | 2.000 | 20 | 21              | 2-                         | -1 |
|                                              | <div>5</div> OBSOLETE |              |      |      | 1.984 | 1.900 | 19 | 20              | 2-                         | -0 |
|                                              | OBSOLETE              |              |      |      | 1.884 | 1.800 | 18 | 19              | 1-                         | -9 |
| SUPERSEDED BY 1-103321-8                     |                       |              |      |      | 1.784 | 1.700 | 17 | 18              | 1-                         | -8 |
| SUPERCEDED BY 1-103321-7                     |                       |              |      |      | 1.684 | 1.600 | 16 | 17              | 1-                         | -7 |
| SUPERCEDED BY 1-103321-6                     |                       |              |      |      | 1.584 | 1.500 | 15 | 16              | 1-                         | -6 |
| SUPERCEDED BY 1-103321-5                     |                       |              |      |      | 1.484 | 1.400 | 14 | 15              | 1-                         | -5 |
|                                              |                       |              |      |      | 1.384 | 1.300 | 13 | 14              | 1-                         | -4 |
| SUPERCEDED BY 1-103321-3                     |                       |              |      |      | 1.284 | 1.200 | 12 | 13              | 1-                         | -3 |
|                                              |                       |              |      |      | 1.184 | 1.100 | 11 | 12              | 1-                         | -2 |
| SUPERCEDED BY 1-103321-1                     |                       |              |      |      | 1.840 | 1.000 | 10 | 11              | 1-                         | -1 |
|                                              |                       |              |      |      | .984  | .900  | 9  | 10              | 1-                         | -0 |
| SUPERCEDED BY 103321-9                       |                       |              |      |      | .884  | .800  | 8  | 9               |                            | -9 |
|                                              |                       |              |      |      | .784  | .700  | 7  | 8               |                            | -8 |
| SUPERCEDED BY 103321-7                       |                       |              |      |      | .684  | .600  | 6  | 7               |                            | -7 |
|                                              |                       |              |      |      | .584  | .500  | 5  | 6               |                            | -6 |
|                                              |                       |              |      |      | .484  | .400  | 4  | 5               |                            | -5 |
|                                              |                       |              |      |      | .384  | .300  | 3  | 4               |                            | -4 |
|                                              |                       |              |      |      | .284  | .200  | 2  | 3               |                            | -3 |
|                                              |                       |              |      |      | .184  | .100  | 1  | 2               |                            | -2 |
|                                              | <div>2</div>          |              | .125 | .318 | .084  | 0     | 0  | 1               | 87348-1                    | -1 |
| SHEET 2 FOR<br>TIONAL LEAD FREE<br>- NUMBERS |                       | FINISH       | E    | D    | C     | B     | A  | NO<br>OF<br>POS | ASSEMBLY<br>PART<br>NUMBER |    |

|                                                                                       |  |                                                                                                                               |  |                                                                                         |  |                                                                                                       |                    |                       |
|---------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--------------------|-----------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>K HELM<br>CHK<br>R. FEIDT<br>APVD<br>R. FEIDT<br>PRODUCT SPEC<br>—<br>APPLICATION SPEC<br>—<br>WEIGHT<br>—             |  | 6-89<br>6-89<br>6-89                                                                    |  |  TE Connectivity |                    |                       |
| DIMENSIONS:<br>INCHES                                                                 |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>0 PLC ± —<br>1 PLC ± —<br>2 PLC ± —<br>3 PLC ± .005<br>4 PLC ± —<br>ANGLES ± ± — |  | NAME<br>ASSEMBLY, MOD II, HEADER, SINGLE ROW,<br>.100 C/L, VERTICAL, .025 SQ POSTS<br>— |  | RESTRICTED TO<br>—                                                                                    |                    |                       |
|  |  | FINISH<br>SEE TABLE                                                                                                           |  |                                                                                         |  | SIZE<br>A2                                                                                            | CAGE CODE<br>00779 | DRAWING NO<br>C-87348 |
| MATERIAL<br>—                                                                         |  | CUSTOMER DRAWING                                                                                                              |  | SCALE<br>4:1                                                                            |  | SHEET<br>1 of 2                                                                                       |                    | REV<br>K 1            |

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS |     |             |      |      |
|-----|------|-----------|-----|-------------|------|------|
| AD  | 38   | P         | LTR | DESCRIPTION | DATE | APVD |
|     |      | -         | -   | SEE SHEET 1 | -    | -    |

D

C

B

A


D

C

B

A

|                       |              |      |      |       |       |    |           |                      |    |
|-----------------------|--------------|------|------|-------|-------|----|-----------|----------------------|----|
|                       | <div>4</div> | .125 | .318 | 3.984 | 3.900 | 39 | 40        | 9-87348-0            |    |
| <div>5</div> OBSOLETE |              |      |      | 3.584 | 3.500 | 35 | 36        | 8-                   | -6 |
| <div>5</div> OBSOLETE |              |      |      | 1.984 | 1.900 | 19 | 20        | 7-                   | -0 |
|                       |              |      |      | 1.384 | 1.300 | 13 | 14        | 6-                   | -4 |
| <div>5</div> OBSOLETE |              |      |      | 1.184 | 1.100 | 11 | 12        | 6-                   | -2 |
|                       |              |      |      | 1.840 | 1.000 | 10 | 11        | 6-                   | -1 |
|                       |              |      |      | .984  | .900  | 9  | 10        | 6-                   | -0 |
|                       |              |      |      | .784  | .700  | 7  | 8         | 5-                   | -8 |
|                       |              |      |      | .584  | .500  | 5  | 6         | 5-                   | -6 |
|                       |              |      |      | .484  | .400  | 4  | 5         | 5-                   | -5 |
|                       |              |      |      | .384  | .300  | 3  | 4         | 5-                   | -4 |
|                       |              |      |      | .284  | .200  | 2  | 3         | 5-                   | -3 |
|                       |              |      |      | .184  | .100  | 1  | 2         | 5-                   | -2 |
|                       | <div>4</div> | .125 | .318 | .084  | 0     | 0  | 1         | 5-87348-1            |    |
|                       | FINISH       | E    | D    | C     | B     | A  | NO OF POS | ASSEMBLY PART NUMBER |    |

|                                                                                       |                                                                            |                                                                                                                                 |  |                                                                                                       |           |            |               |        |     |    |
|---------------------------------------------------------------------------------------|----------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|-----------|------------|---------------|--------|-----|----|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                                                            | DWN<br>K HELM<br>6-89                                                                                                           |  |  TE Connectivity |           |            |               |        |     |    |
|                                                                                       |                                                                            | CHK<br>R. FEIDT<br>6-89                                                                                                         |  |                                                                                                       |           |            |               |        |     |    |
|                                                                                       |                                                                            | APVD<br>R. FEIDT<br>6-89                                                                                                        |  |                                                                                                       |           |            |               |        |     |    |
| DIMENSIONS:<br>INCHES                                                                 |                                                                            | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br><br>0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± .005<br>4 PLC ± -<br>ANGLES ± - |  | NAME                                                                                                  |           |            |               |        |     |    |
|  | ASSEMBLY, MOD II, HEADER, SINGLE ROW,<br>.100 C/L, VERTICAL, .025 SQ POSTS |                                                                                                                                 |  |                                                                                                       |           |            |               |        |     |    |
|                                                                                       | -                                                                          |                                                                                                                                 |  |                                                                                                       |           |            |               |        |     |    |
|                                                                                       |                                                                            |                                                                                                                                 |  |                                                                                                       |           |            |               |        |     |    |
| MATERIAL                                                                              |                                                                            | FINISH                                                                                                                          |  | SIZE                                                                                                  | CAGE CODE | DRAWING NO | RESTRICTED TO |        |     |    |
| -                                                                                     |                                                                            | SEE TABLE                                                                                                                       |  | WEIGHT -                                                                                              | A2        | 00779      | C=87348       | -      |     |    |
| CUSTOMER DRAWING                                                                      |                                                                            |                                                                                                                                 |  |                                                                                                       | SCALE     | 4:1        | SHEET         | 2 of 2 | REV | K1 |