



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		A1	REL PER ECR 08-010125	21APR08	JR RL



SUGGESTED MATING TAB



- 1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
 - 2 - NO BURRS PERMISSIBLE AT HOLE.
 - 3 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F.
 - 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 CONTINUOUS STRIP ON REELS.
- 2 ACCEPTS #22-#18 AWG WIRE SIZES. WIRE CRIMP: .080 F TYPE
- 3 INSULATION RANGE IS 2.29-3.94 [.090-.155] DIA. INSULATION CRIMP: .180 F TYPE



0.002032[.000080] MIN TIN PLATE	1742630-2
-	1742630-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	14AUG07	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: MM [INCHES]		CHK	MS FEHER	14AUG07				
		APVD	R LONDON	14AUG07	NAME			
		PRODUCT SPEC			RECEPTACLE, POSITIVE LOCK, 6.35 [.250] SERIES			
MATERIAL		APPLICATION SPEC			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		114-2074			A2	00779	C=1742630	-
H06 BRASS		FINISH			SCALE 5:1 SHEET 1 of 1 REV A1			
SEE TABLE		CUSTOMER DRAWING						