



## 8W Interchangeable Plug Series with Micro-USB Connector PSM08R Adapter Meets EISA and CEC Requirements



### Features

- Double Insulated
- Field Changeable AC Plugs
- Efficiency Level IV Compliance
- 5% NL-FL Regulation
- Low Leakage Current
- Micro-USB Connector
- Class B EMI
- CCCV

### Applications

- Wireless Communications
- Networking
- Portable Equipment
- Peripherals

### Safety Approvals

- cUL/UL
- SAA
- CCC
- C-Tick
- PSE

### Mechanical Characteristics

- Length: 71.7mm (2.82in)
- Width: 45mm (1.77in)
- Height: 29.79mm (1.17in)
- Weight: 128g (4.52oz)

### Output Specifications

Model	DC Output Voltage	Load		Ripple <sup>(1)</sup> P-P (max.)	Regulation Line & Load	Efficiency Level <sup>(2)</sup>
		Min.	Max.			
PSM08R-050(M)	5V	0A	1.6A	100mV	±5%	IV

(1) Measured with by-pass capacitors 0.1uF/10uF at output connector terminal and oscilloscope set at 20MHz. (Tested oscilloscope after waiting 1 minute).

(2) Level IV efficient products do not qualify for CE marking and therefore cannot be sold to countries in the EU

- Interchangeable clips sold separately.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phihong:](#)

[PSM08R-050\(M\)-R](#)