

**SMPTE COMPATIBLE
HDTV CONNECTION SYSTEM
3K.93C SERIES**



LEMO pioneered and set the standard for HDTV

The global standard for HDTV fibre connector



LEMO developed the 3K.93C Series connectors in the early stages of the introduction of HDTV, becoming the standard for high-definition TV. It is one of the only connectors being used worldwide that complies fully with SMPTE, ARIB and EBU standards for both signal and cable. LEMO's 3K.93C connectors are the standard in national and international broadcast companies.



Fast transition to HDTV

Transition to HDTV is easier than ever with LEMO. The wide range of shell styles and termination procedures, for even non-fibre experts, makes it possible for everyone to be successful in HDTV. The LEMO 3K.93C connector uses two single-mode fibre contacts, two high voltage contacts, and two signal contacts. Cable drums and cable assemblies with standard lengths are available off the shelf.

Over 20'000 stainless steel shells mating cycles offered

The rugged stainless steel outer shell of the LEMO 3K.93C connectors ensures a very long product life, when properly cleaned. The fibre optic contact can will last many years.


Simple maintenance

The optical contacts are accessible for fast cleaning; an optional simple, lightweight and portable fibre inspection unit helps the user view the condition of the fibre optic contact to ensure reliable operation.

Benefits

- Quick disconnect Push-Pull self latching system
- Over 11 shells to meet various application needs
- Stainless steel shell for rugged and harsh environment
- Optional pre-terminated F2 contacts for simple and rapid field assembly
- UL certified connectors
- ARIB (BTA S-1005B), ANSI/SMPTE (304 and 311) and EBU (R100-1999) compatible

Outside Broadcast Van Configuration



Highest performance with LEMO standard F2 fibre contact

The advantage of using epoxy and polish contacts is the reliability of the termination and longevity of the connector to assure a quality signal transmission. These contacts are very robust and can withstand wide outdoor temperature variations.

Extend the quality of your connection

LEMO offers quality assembly service for HDTV connection systems. The connector assembly is done in-house by qualified personnel.

NEW F2 fibre optic contacts in various dimensions

LEMO now offers 3 choices of F2 ferrule size to fit your fibre dimensions.


Fibres are manufactured to about 125 microns, but in some occasion the fibres might be larger. LEMO's choice of inner ferrule diameter are fit for 125 μm , 125.5 μm and 126 μm fibres.

Designed for use with the LEMO 3K.93C, these contacts can be used directly into any LEMO connector where the F2 contact is used.

NEW



Studio Configuration



3K.93C Series

General characteristics

Cable retention force	> 700 N
Endurance: Brass+Cr	> 10000 cycles
Endurance: Stainless steel	20000 cycles
Drop test	2 m
Shock	100 g, 10-50 ms
Vibration	7 cycles (20-2000Hz)
Standard F2 temperature range	-40° C, +80° C
Pre-terminated F2 temperature range	-20° C, +60° C
Humidity	up to 95% at 60° C
Water resistance	Depth of 1.8 m for 48 hours
Corrosion	48 hours, 5% salt water test
Index protection	IP 68

Electrical contacts

	Power	Signal
Number of contacts	2	2
Male contact ø	1.3 mm	0.9 mm
Contact type	crimp	crimp
Conductor AWG min.	18	24
Conductor AWG max.	14	20
Working Voltage max.	≤ 600 V rms	≤ 42 V rms
Test Voltage	2250 V rms	1000 V rms
Rated current	10 A	3 A
Contact resistance	< 4 mΩ	< 5 mΩ
Shell to shell conductivity		
Insulation resistance		> 10 ⁹ Ω

Fibre optic contacts

Characteristics	Value	Standard
Number of contacts	2	
Fibre core/cladding ø	single mode 9/125 µm	
Ferrule bore inside ø	125 µm ²	
Mean insertion loss	0.10 dB ¹⁾	IEC 61300-3-4
Return loss (machine polishing)	< -45 dB	IEC 61300-3-6


Note: ¹⁾ tested at 1300 nm in accordance with IEC 61300-03-04 method B.
²⁾ other ferrule bore ø available (126 µm).

Recommended SMPTE/ARIB cables


Cable group	Type	Utilisation	Sheath ø
1	2SM-6.8-98.3	Reduced diameter	6.8 ± 0.3
2	2SM-9.2-37.5	Standard	9.2 ± 0.3
3	2SM-12-15	Long distances	12.0 ± 0.4
4 1)	2SM-16-37.5	Studio	16.0 ± 0.5

Note: ¹⁾ The outer sheath shall be removed for assembly.


Models



Mixed contact type



Part Number Example





Note: ¹⁾ The «Variant» position in the reference is used to indicate the presence of a collet nut for fitting the bend relief. For models with the «T» type of cable adapter the «Z» should always be indicated and a bend relief can be ordered separately as indicated in the «Accessories» section. An order for a connector with bend relief should thus include two part numbers.

Fibre Optic Contact


Reference	Contact	Ferrule hole	Type	Gender
E	FFS.F2.BA2.LCE30	125 µm	Crimp	Male
K	FFS.F2.BA2.LCT10	125 µm	Epoxy	Male
X	FFS.F2.BX2.LCE30	125.5 µm	Crimp	Male
V	FFS.F2.BX2.LCT10	125.5 µm	Epoxy	Male
F	FFS.F2.BB2.LCE30	126 µm	Crimp	Male
N	FFS.F2.BB2.LCT10	126 µm	Epoxy	Male

Reference	Contact	Ferrule hole	Type	Gender
E	PSS.F2.BA2.LCE30	125 µm	Crimp	Female
K	PSS.F2.BA2.LCT10	125 µm	Epoxy	Female
X	PSS.F2.BX2.LCE30	125.5 µm	Crimp	Female
V	PSS.F2.BX2.LCT10	125.5 µm	Epoxy	Female
F	PSS.F2.BB2.LCE30	126 µm	Crimp	Female
N	PSS.F2.BB2.LCT10	126 µm	Epoxy	Female

FGW Straight plug, cable adapter, with bend relief



Part Number	Cable group	Dim. (mm)			Cable ø	Housing material
		L	M	S1		
FGW.3K.93C.CLET96Z	2-4	101	81	15	9.5	8.9
FGW.3K.93C.CLET12Z	3	135	115	20	12.5	11.6

Note: The bend relief must be ordered separately (see page 8). Fibre optic contacts included.

FUW Straight plug, cable collet adapter and long shell for fitting a bend relief with cap


Part Number	Cable group	Cable ø		Housing material
		Max	Min	
FUW.3K.93C.TLEC74	1	7.4	6.2	Stainless steel
FUW.3K.93C.TLEC96	2-4	9.5	8.9	
FUW.3K.93C.TLEC12	3	12.5	11.6	


Note: The bend relief with cap GMF.3K.085.EANZ must be ordered separately (see page 8). Fibre optic contacts included.

FXW Fixed plug with round flange (4 holes mounting), without collet


Part Number	Housing material
FXW.3K.93C.TLE	Stainless steel


Note: Fibre optic contacts included.

Note: all dimensions are in millimetre.

FMW Fixed plug with round flange (4 holes mounting), cable adapter, with bend relief



Part Number	Cable group	Cable ø		Collet type	Housing material
		Max	Min		
FMW.3K.93C.TLEC96Z	2-4	9.5	8.9	C	Stainless steel
FMW.3K.93C.TLET96Z	2-4	9.5	8.9	T	

Note: The bend relief must be ordered separately (see page 8). Fibre optic contacts included.

EDW Fixed socket (receptacle) with rear square flange (4 holes mounting), and earthing tag



Part Number	Housing material
EDW.3K.93C.TLE	Stainless steel

Note: Fibre optic contacts included.

EBW Fixed socket (receptacle) with front square flange (4 holes mounting)




Part Number	Housing material
EBW.3K.93C.TLE	Stainless steel

Note: Fibre optic contacts included.

ENW Fixed socket (receptacle), nut fixing, and earthing tag


Part Number	Housing material
ENW.3K.93C.TLE	Stainless steel


Note: Fibre optic contacts included.

PHW Free socket (receptacle), cable adapter, with bend relief


Part Number	Cable group	Dim. (mm)		Câble ø	Housing material
		L	S1		
PHW.3K.93C.CLET96Z	2-4	105	15	9.5	8.9
PHW.3K.93C.CLET12Z	3	139	20	12.5	11.6

Note: The bend relief must be ordered separately (see page 8). Fibre optic contacts included.


PUW Free socket (receptacle), cable collet adapter and long shell for fitting a bend relief with cap

Part Number	Cable group	Cable ø		Housing material
		Max	Min	
PUW.3K.93C.TLEC74	1	7.4	6.2	Stainless steel
PUW.3K.93C.TLEC96		9.5	8.9	
PUW.3K.93C.TLEC12		12.5	11.6	

Note: The bend relief with cap GMP.3K.085.EANZ must be ordered separately (see p. 8). Fibre optic contacts included.



PEW Fixed socket (receptacle), nut fixing, cable adapter, with bend relief (back panel mounting)

Part Number	Cable group	L max (mm)	Cable ø		Collet type	Housing material
			Max	Min		
PEW.3K.93C.TLEC96Z	2-4	136	9.5	8.9	C	Stainless steel
PEW.3K.93C.TLET96Z		105	9.5	8.9	T	

Note: The bend relief must be ordered separately (see page 8). Recommended «C» collet type with enhanced «EMC» protection. Fibre optic contacts included.

PBW Fixed socket (receptacle) with rear square flange (4 holes mounting), cable adapter, with bend relief

Part Number	Cable group	L max (mm)	Cable ø		Collet type	Housing material
			Max	Min		
PBW.3K.93C.TLEC96Z	2-4	136	9.5	8.9	C	Stainless steel
PBW.3K.93C.TLET96Z		105	9.5	8.9	T	

Note: The bend relief must be ordered separately (see page 8). Recommended «C» collet type with enhanced «EMC» protection. Fibre optic contacts included.

F2 fibre optic contacts

The standard F2 fibre contact is the highest performing solution on the market regarding thermal stability and very low signal loss. The F2 pre-terminated fibre optic



contact was designed as repair solution. These pre-terminated contacts enable simple and rapid on-site-terminations. The design eliminates the need to polish fibre

optic elements as well as preparing and using special epoxies for the fibre assembly.

Optical characteristics

Characteristics	Contact model	Value	Standard
Average insertion loss fibre 9/125 µm	FFS, PSS (standard F2)	0.10 dB	IEC 61300-03-04
Return loss fibre 9/125 µm (UPC)	FFS, PSS (standard F2)	≥ 45 dB	IEC 61300-03-06


FFS.F2 Standard F2 male fibre optic contact

Part Number	For connector models	Cable structure	Cable ø
FFS.F2.BA2.LCT10	PHW, PEW, PBW, PUW	Buffer coated fibre	0.25 to 1.1
FFS.F2.BA2.LCE30	EDW, ENW, EBW	Tight jacket cable	1.7 to 3.0

Note: The above contacts are fitted with a 125 µm bore ferrule


PSS.F2 Standard F2 female fibre optic contact

Part Number	For connector models	Cable structure	Cable ø
PSS.F2.BA2.LCT10	FGW, FMW, FUW	Buffer coated fibre	0.25 to 1.1
PSS.F2.BA2.LCE30	FXW	Tight jacket cable	1.7 to 3.0

Note: The above contacts are fitted with a 125 µm bore ferrule

PSS.F2 Alignment device for F2 female fibre optic contact

Part Number
PSS.F2.290.NZZ

Note:
Alignment device should be ordered as replacement item. All dimensions are in millimetre.

Pre-terminated contacts are available under part number:


For male contact: FFT.F2.BA2.LCE10 and for female contact: PST.F2.BA2.LCE10

Cables – ARIB, SMPTE & EBU mixed camera cables

Mixed camera cables have been specially designed for HDTV Broadcast requirements resulting in the primary standards in Japan and USA.

These standards are fairly similar, except for the colour coding of the control cores. While the diameter of the central strength member is the same in

both standards (1.8 mm) some manufacturers use 1.6 mm only.



Rugged HDTV camera cable

Cables in broadcast need to have high resistance against flexing and twisting,

which is a challenge for fragile fibre optic cables. These cables require good

abrasion resistance, load bearing as well as tensile strength capabilities.

SMPTE 311M-1998 (USA standard connector)

Optical fibre	Typical data	Mechanical properties of cable	Typical data
Attenuation (1300 µm)	0.8 dB/km	Tensile strength	700N minimum
Core diameter	9.5 ± 1µm	Cyclic flexing	15000 cycles
Cladding diameter	125 ± 1µm	Bend radius	7 x diameters
Buffer diameter	0.9 ± 0.05mm		

Power conductor	Typical data	Signal conductor	Typical data
Conductor resistance	< 43 Ω/km	Conductor resistance	< 184 Ω/km
Insulation resistance	> 10000 MΩ/km	Insulation resistance	> 10000 MΩ/km
Withstand voltage	1750 Vrms	Withstand voltage	1750 Vrms


EBU R100-1999 (European standard connector)

General specifications	Typical data	Optical specifications	Typical data
Temperature	-40° C to +80° C	Fibre core/cladding ø	9/125 µm, single (SM) fibre
Humidity	90-95% relative humidity at 40° C ± 2 for 96 hours	Insertion loss	less than 0.5 dB at 1300 nm ²
Durability	10000 cycles	Return loss	better than -45 dB (machine polishing)

Power conductor	Typical data	Signal conductor	Typical data
Voltage	600 Vrms (maximum working voltage)	Voltage	42 Vrms or 60 Vrms (maximum working voltage)
Current	10 A (maximum working current)	Current	3 A (maximum working current)

Accessories

GMA Bend relief



Part Number	Cable group	Dim. (mm)	
		A	L
GMA.3B.090.DN	2-4	9	42
GMA.4B.011.DN	3	11	60

Ref.	Colour	Ref.	Colour	Ref.	Colour
A	blue	J	yellow	R	red
B	white	M	brown	S	orange
G	grey	N	black	V	green

Note: The last letter «N» of the part number indicates the colour black of the bend relief.
For others colour, refer to the adjacent table and replace letter «N» by the letter of the colour required.

GMF Bend relief with cap



Part Number	For connector model
GMF.3K.085.EANZ	FUW

Material: black EPDM


GMP Bend relief with cap



Part Number	For connector model
GMP.3K.085.EANZ	PUW

Material: black EPDM


GMF Coloured ring for bend relief with cap



Part Number	Colour
GMF.3K.265.RG	grey
GMF.3K.265.RN	black
GMF.3K.265.RR	red
GMF.3K.265.RV	green

Material: Silicone



Bee Blanking caps



Part Number	For connector model
BHA.3K.100.EAN	FMW, FXW
BRA.3K.200.EAN	EDW, PEW
BFG.3K.100.EAN	FMW, FXW
BRF.3K.200.EAN	PUW
BHA.3K.100.715EN	FMW, FXW
BRA.3K.100.715EN	EBW, EDW, ENW, PBW, PEW

Material: black EPDM


GM● Gaiters



Part Number	Colour	Dimension L (mm)	For connector model
GMP.3K.140.165PER	red	165	PUW
GMP.3K.140.165PEN	black	165	PUW
GMF.3K.140.156PEV	green	156	FUW
GMF.3K.140.156PEN	black	156	FUW

Material: PVC

BRR Spring loaded dust cap for EDW and EBW



Part Number	Dimensions (mm)					
	A	B	C	L	M	N
BRR.3K.200.PZSG	29	29	23	8.1	3	33.2

Note: On request, this cap is available in black. If so replace the last letter «G» of the part number by «N».

Material: Polyoxymethylene (POM) grey (or black)

Patch panels

PB Patch panel




2U panel with one row of 6 or 10 plugs or sockets (receptacles) of the 3K.93C Series.

P	B	G	3	K	9	3	C	M	W	9	6	0	6
Ref.				Ref.				Ref.				Nb of connectors	
Ref.				Front side connection				Ref.				Nb of connectors	
C				MW				9606				6	
G				Plug FMW				1206				6	
N				EW				9610				10	
T				BW				1210				10	

Cable assembly

MFP Cable assembly


Assembly cable with one straight plug (FUW) and one straight socket (receptacle) (PUW), both complete with GMF/GMP bend relief with cap.



Part Number	Description	Cable type	Part Number	Description	Cable type
MFP.3K.93C.092M025	25 meter length	2SM-9.2-37.5	MFP.3K.93C.120M025	25 meter length	2SM-12-15
MFP.3K.93C.092M050	50 meter length	2SM-9.2-37.5	MFP.3K.93C.120M050	50 meter length	2SM-12-15
MFP.3K.93C.092M100	100 meter length	2SM-9.2-37.5	MFP.3K.93C.120M100	100 meter length	2SM-12-15
MFP.3K.93C.092M200	200 meter length	2SM-9.2-37.5	MFP.3K.93C.120M200	200 meter length	2SM-12-15

Part Number	Description	Cable type
MFP.3K.93C.160M025	25 meter length	2SM-16-37.5
MFP.3K.93C.160M050	50 meter length	2SM-16-37.5
MFP.3K.93C.160M100	100 meter length	2SM-16-37.5
MFP.3K.93C.160M200	200 meter length	2SM-16-37.5

Panel cut-outs




Models	Dimensions (mm)				
	A	B	D	L	L1
FMW, FXW	23.2	—	3.2 or M3	39	20.6
EBW	23.2	—	3.2 or M3	30	23.0
EDW	23.2	—	3.2 or M3	30	23.0
ENW, PEW	24.2	22.6	—	32	—
PBW	23.2	—	3.2 or M3	30	23.0

Note: 1) Minimum distance between two neighbouring components.

Tooling

DRV Complete workstation for fibre optic contact



Part Number	Contact type
DRV.91.CF2.PN	F2

Note: other tools such as polishing machine and optical test instrument are also necessary.

Part Number	Description	Part Number	Description
DRV.91.CF2.PN	Standard F2 contact termination workstation	DPD.99.010.5K	Crimping tool for screen crimping on FUW and PUW
DPE.99.524.337K	Crimping tool for fibre optic contact	DPC.91.701.V	Manual crimping tool (signal contacts ø 0.9)
DCS.91.F12.3LA	Epoxy curing jig	DPC.91.101.A	Manual crimping tool (power contacts ø 1.3)
WST.FR.220.VA	Epoxy curing oven (220 V)	DCF.92.090.3LT	Extraction tool, crimp cont. ø 0.9 (automatic model)
WST.FR.110.VA	Epoxy curing oven (110 V)	DCF.92.131.3LT	Extraction tool, crimp cont. ø 1.3 (automatic model)
DCC.91.312.5LA	Extractor for fibre optic contact (assembly house)	FFS.F2.BA2.EZZ	Dummy ferrule for polishing
DCP.91.023.TN	Spanner for tightening collet nut		

DCS.3K.175.72LN Cable puller



The LEMO cable puller, is a pull through tool that allows passing the cable through narrow sections and protects the optical fibre during installation.

●UW Parts for field repair with pre-terminated F2 contact



Part Number (Repair kit for FUW plug)	Content part number	Description	Quantity
FUW.3K.93C.ZLMC96W	EGW.3K.444.EL EGG.3B.660.ZZM FGW.3K.565.ZZC PST.F2.BA2.LCE10 FGW.3K.146.ZZA FFS.3K.130.LNV FFS.3K.160.DN GDA.99.140.100VK GMA.30.025.CN	Insulator for plug Contact for signal Contact for power Pre-terminated F2 contact Anchor with screws Earthing body with o-ring Crimp ring O-ring for backshell Protection sleeve	1 2 2 2 1 1 1 1 2

Part Number (Repair kit for PUW socket/receptacle)	Content part number	Description	Quantity
PUW.3K.93C.ZLCC96W	FGW.3K.344.EL FGG.3B.560.ZZC EGW.3K.666.ZZM FFT.F2.BA2.LCE10 FGW.3K.146.ZZA FFS.3K.130.LNV FFS.3K.160.DN GDA.99.140.100VK GMA.30.025.CN	Insulator for socket (recep.) Contact for signal Contact for power Pre-terminated F2 contact Anchor with screws Earthing body with o-ring Crimp ring O-ring for backshell Protection sleeve	1 2 2 2 1 1 1 1 2

Tooling for field termination

Part Number	Description	Part Number	Description
DCE.91.093.BVC	Positioner for signal ¹⁾ (male), 0.9 mm	DPC.91.701.V	Manual crimping tool (signal contacts ø 0.9)
DCE.91.093.BVM	Positioner for signal ¹⁾ (female), 0.9 mm	DPC.91.101.A	Manual crimping tool (power contacts ø 1.3)
DCE.91.133.BVCW	Positioner for power ²⁾ (male and female), 1.3 mm	DCP.91.023.TN	Spanner for tightening collet nut
WST.OU.110.20PN	Fibre cleaver for pre-terminated contact	WST.PN.102.3CR	Primary coat stripper
DPD.99.010.5K	Crimping tool for cable group 2-4 (FUW and PUW)		
DPD.99.301.3K	Crimping tool for cable group 3 (FUW and PUW)		

Note:

1) These positioners are suitable for use with both manual and pneumatic crimping tools according to the MIL-C-22520/7-01 standard.
 2) These turrets can be used with manual crimping tool according to MIL-C-22520/1-01 standard. Power contacts are special with an oversized crimp barrel.



Maintenance tools

DCS.91.F23.LA Cleaning tool F2 contact



Used for maintenance cleaning. The tool is made with a sponge alcohol reservoir (supplied empty).
 16 dry cotton buds are included. The threaded end allows extraction/reinstallation of the F2 contact alignment device.

DCS.F2.035.PN Alignment device tool



Simple tool with two threaded end for installation/extraction of the F2 contact alignment device. For use with WST.KI.125.34 kit above.

WST.FB.CI1.10US2 Video inspection viewer



A portable fibre optic viewer for F2 contact consisting of handset probe, LCD display, ferrule tips for LEMO contacts & software & United States - AC power supply all in a rugged case.
 European power supply version (WST.FB.CI1.10EU2).
 An optional USB capture device is also available (Part number: WST.FB.CI1.00USB2)

WST.KI.125.34 Cleaning kit F2 contact



Fibre optic cleaning kit of 2 cotton buds, 1 dry and 1 being soaked in IPA (Isopropyl Alcohol) used for cleaning the fibre optic contacts.

DCT.F2.125.PA Fibre Optic ferrule cleaner



This cleaning tool comes with a bush for different cleaning configurations. More than 500 cleaning per cleaner. This cleaner is for on-site purposes only and should not replace regular maintenance cleaning with cotton buds and alcohol.

DCS.F2.N02.PA Fibre Optic one-click cleaner



Insert the one-click cleaner into the insulator and push until an audible "click" is heard. The cleaner uses a mechanical push action to advance an optical grade cleaning tape. More than 500 cleaning per cleaner. Product includes special LEMO F2 ferrule adaptor.

LEMO HEADQUARTERS

SWITZERLAND

LEMO SA

Chemin des Champs-Courbes 28 - P.O. Box 194 - CH-1024 Ecublens
Tel. (+41 21) 695 16 00 - Fax (+41 21) 695 16 02 - e-mail: info@lemo.com

LEMO SUBSIDIARIES

AUSTRIA

LEMO Elektronik GesmbH
Lemböckgasse 49/E6-3
1230 Wien
Tel: (+43 1) 914 23 20 0
Fax: (+43 1) 914 23 20 11
sales@lemo.at

CANADA

LEMO Canada Inc
44 East Beaver Creek Road, unit 20
Richmond Hill, Ontario L4B 1G8
Tel: (+1 905) 889 56 78
Fax: (+1 905) 889 49 70
info-canada@lemo.com

CHINA

LEMO Electronics (Shanghai) Co., Ltd
5th Floor, Block 6, City of ELITE,
1000 Jinhai Road, Pudong
Shanghai, China 201206
Tel: (+86 21) 5899 7721
Fax: (+86 21) 5899 7727
cn.sales@lemo.com

DENMARK

LEMO Denmark A/S
Gammel Mosevej 46
2820 Gentofte
Tel: (+45) 45 20 44 00
Fax: (+45) 45 20 44 01
info-dk@lemo.com

FRANCE

LEMO France Sàrl
24/28 Avenue Graham Bell
Bâtiment Balthus 4
Bussy Saint Georges
77607 Marne la Vallée Cedex 3
Tel: (+33 1) 60 94 60 94
Fax: (+33 1) 60 94 60 90
info-fr@lemo.com

GERMANY

LEMO Elektronik GmbH
Hanns-Schwindt-Str. 6
81829 München
Tel: (+49 89) 42 77 03
Fax: (+49 89) 420 21 92
info@lemo.de

HONG KONG

LEMO Hong Kong Ltd
Unit 1207, 12/F, Corporation Square,
8 Lam Lok Street, Kowloon Bay,
Kowloon - Hong Kong
Tel: (+852) 2174 0468
Fax: (+852) 2174 0492
hk.sales@lemo.com

HUNGARY

REDEL Elektronika Kft
Nagysándor József u. 6-12
1201 Budapest
Tel: (+36 1) 421 47 10
Fax: (+36 1) 421 47 57
info-hu@lemo.com

ITALY

LEMO Italia srl
Viale Lunigiana 25
20125 Milano
Tel: (+39 02) 66 71 10 46
Fax: (+39 02) 66 71 10 66
sales.it@lemo.com

JAPAN

LEMO Japan Ltd
2-7-22, Mita,
Minato-ku, Tokyo, 108-0073
Tel: (+81 3) 54 46 55 10
Fax: (+81 3) 54 46 55 11
lemoinfo@lemo.co.jp

NETHERLANDS / BELGIUM

LEMO Connectors Benelux
De Trompet 1060
1967 DA Heemskerk
Tel. (+31) 251 25 78 20
Fax (+31) 251 25 78 21
info@lemo.nl

NORWAY / ICELAND

LEMO Norway A/S
Stanseveien 6B
0975 Oslo
Tel: (+47) 22 91 70 40
Fax: (+47) 22 91 70 41
info-no@lemo.com

SINGAPORE

LEMO Asia Pte Ltd
4 Leng Kee Road,
#06-09 SiS Building
Singapore 159088
Tel: (+65) 6476 0672
Fax: (+65) 6474 0672
sg.sales@lemo.com

SPAIN / PORTUGAL

IBERLEMO SAU
Brasil, 45, 08402 Granollers
Barcelona
Tel: (+34 93) 860 44 20
Fax: (+34 93) 879 10 77
info-es@lemo.com

SWEDEN / FINLAND

LEMO Nordic AB
Marihällsvägen 39A
168 65 Bromma
Tel: (+46 8) 635 60 60
Fax: (+46 8) 635 60 61
info-se@lemo.com

SWITZERLAND

LEMO Verkauf AG
Grundstrasse 22 B
6343 Rotkreuz
Tel: (+41 41) 790 49 40
Fax: (+41 41) 790 49 43
ch.sales@lemo.com

UNITED KINGDOM

LEMO UK Ltd
12-20 North Street
Worthing, West Sussex, BN11 1DU
Tel: (+44 1903) 23 45 43
Fax: (+44 1903) 20 62 31
lemouk@lemo.com

USA

LEMO USA Inc
P.O. Box 2408
Rohnert Park, CA 94927-2408
Tel: (+1 707) 578 88 11
(+1 800) 444 53 66
Fax: (+1 707) 578 08 69
info@lemosusa.com

© C.A.T.-HD.LEM.P0606, updated October 2014

LEMO DISTRIBUTORS

AUSTRALIA, BRAZIL, CHILE, CZECH REPUBLIC, GREECE, INDIA, ISRAEL,
NEW ZEALAND, PAKISTAN, POLAND, RUSSIA, SOUTH AFRICA,
SOUTH KOREA, TAIWAN, TURKEY, UKRAINE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO](#):

[FGW.3K.93C.CLMT96Z](#) [FFS.F2.BA2.LCT10](#) [FUW.3K.93C.TLMC96](#) [FXW.3K.93C.TLM](#) [FMW.3K.93C.TLMT96Z](#)