





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.*	MAT'L SUFFIX	MATERIAL	MOUNTING RIVET	'A'	'B'	'C'	'D'	'E'	'F'	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT (g) lbs/100 pcs.
TM2R6	NONE	NYLON 6/6	#6 (M3)	0.630 [16.0]	0.425 [10.8]	0.275 [7.0]	0.215 [5.5]	0.060 [1.5]	0.155 [3.9]	MINIATURE INTERMEDIATE STANDARD	0.127 (57.8)
	-0	WEATHER RESISTANT NYLON									
	-30	HEAT STABILIZED NYLON									
TM3R6	NONE	NYLON 6/6	#6 (M3)	0.860 [21.84]	0.610 [15.94]	0.375 [9.5]	0.320 [8.1]	0.088 [2.2]	0.210 [5.3]	MINIATURE INTERMEDIATE STANDARD LT. HEAVY	0.371 (168.3)
	-0	WEATHER RESISTANT NYLON									



- * NOTES:
1. SEE CURRENT PRICE SHEET FOR PART
NUMBER SUFFIX DESIGNATION FOR
PACKAGE SIZE.

SECTION A-A

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYER

G00239BU_PB_TMR_09

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

TIE MOUNT
TM2R6 & TM3R6

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

9	4/5/04	JAD		REMOVE -30 OPTION FOR TM3R6	GB0239BU	9				DRAWN BY DWP	SEE TABLE	SCALE NONE	
8	3/16/04	JAD		CHANGE DIM 'A' AND 'B' ON TM3R6	GB0239BU	8				DATE 04/15/96		DRAWING NO.	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		OK'D		GB0239BU	SIZE