

Communication module - NLC-COM-ENET-MB1 - 2701124

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ethernet communication module. Allows the Nanoline controller to be connected to an Ethernet, operating as a Modbus TCP Server.

Product Description

Adds Ethernet connectivity (Modbus TCP Server functionality) to Nanoline controller. Attaches to left-side of base unit.

Your advantages

- ✓ Enables all I/O points, registers, timers, counters, program flags, and system flags to be read and written remotely
- ✓ Password control can limit access (read-only or read/write)
- ✓ Watchdog timer monitors communication, providing either a warning or fault
- ✓ Connects to an Ethernet network to function as a Modbus TCP client

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 325295
GTIN	4046356325295
Weight per Piece (excluding packing)	144.200 g
Custom tariff number	85176200
Country of origin	India

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	40 mm
-------	-------

Communication module - NLC-COM-ENET-MB1 - 2701124

Technical data

Dimensions

Height	103.5 mm
Depth	43 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	90 %

Interfaces

Interface	Ethernet 10/100Base T
Connection method	RJ45
Transmission speed	10/100 Mbps (auto negotiation)
Transmission length	100 m
Signal LEDs	LNK/ACT; Module; Network

Supply

Power supply connection	Screw connection
Supply voltage	24 V DC (Power available via logic module)
Max. current consumption	180 mA (at 18 V DC)
Typical current consumption	110 mA


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Communication module - NLC-COM-ENET-MB1 - 2701124

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27242216
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27242700
eCl@ss 5.1	27242700
eCl@ss 6.0	27242200
eCl@ss 7.0	27242216
eCl@ss 8.0	27242216

Communication module - NLC-COM-ENET-MB1 - 2701124

Classifications

eCl@ss

eCl@ss 9.0	27242216
------------	----------

ETIM

ETIM 2.0	EC001417
ETIM 3.0	EC001417
ETIM 4.0	EC001417
ETIM 5.0	EC001417
ETIM 6.0	EC001417
ETIM 7.0	EC001417

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39122329
UNSPSC 18.0	39122329
UNSPSC 19.0	39122329
UNSPSC 20.0	39122329
UNSPSC 21.0	39122329

Approvals

Approvals

Approvals

UL Listed / EAC

Ex Approvals

Approval details

UL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 238705

Communication module - NLC-COM-ENET-MB1 - 2701124

Approvals

EAC



EAC-Zulassung