


**Product: [6339Q8](#)**

Surveillance CATV MATV, RG-6 #18 Sol BC, FFEP Core, Quad Shield, Flamarrest® Jkt, CMP

**Product Description**

Surveillance, CATV & MATV, RG-6, 18 AWG solid bare copper, foam FEP core, Duofoil® + 60% aluminum braid + Duofoil® + 40% aluminum braid, Low Smoke PVC jacket, CMP, CATV

**Technical Specifications**
**Product Overview**

Suitable Applications:	CATV, MATV
------------------------	------------

**Construction Details**

RG Type:	6
----------	---

**Conductor**

Size	Stranding	Nom. Diameter	Material
18 AWG	Solid	0.040 in	BC - Bare Copper

**Insulation**

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.171 in (4.34 mm)	White

**Outer Shield**

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Aluminum		60%
3	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
4	Braid	Aluminum		40%

**Outer Jacket**

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.267 in (6.78 mm)

**Electrical Characteristics**
**Attenuation**

Frequency	Nom. Attenuation
1 MHz	0.24 dB/100ft
3 MHz	0.45 dB/100ft
5 MHz	0.55 dB/100ft
8 MHz	0.70 dB/100ft
10 MHz	0.85 dB/100ft
50 MHz	1.50 dB/100ft
100 MHz	2.10 dB/100ft
200 MHz	3.10 dB/100ft
400 MHz	4.50 dB/100ft
700 MHz	6.00 dB/100ft
900 MHz	6.90 dB/100ft
1000 MHz	7.30 dB/100ft

## Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
6.4 Ohm/1000ft	2.5 Ohm/1000ft (8.2 Ohm/km)	16.3 pF/ft (53.5 pF/m)	75 Ohm	83%

## Voltage

UL Voltage Rating
300 V (CMP)

## Mechanical Characteristics

### Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

### Bend Radius

Installation Min.
2.6 in (66 mm)

Max. Pull Tension:	76 lbs (34 kg)
Bulk Cable Weight:	39 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Sustainability:	CA Prop 65, Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	NFPA 262
NEC / UL Compliance:	CATV, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.597 Revision Date: 09-07-2025
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
6339Q8 8771000	Natural	Reel	1,000 ft	612825176060	C
6339Q8 877U1000	Natural	UnReel	1,000 ft	612825176053	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.