


SMD Power Inductor


CDRH50D28R



Dimension - [mm]



Land pattern and Schematics - [mm]



Electrical Characteristics

Part No.	Stamp	Inductance (μH) [Within] ※1	D.C.R. (mΩ) [Within] (at 20℃)	Saturation current (A) ※2		Temperature rise current (A) ※3
				(at 20℃)	(at 105℃)	
CDRH50D28RNP-1R2NC	A	1.2±30%	13±25%	4.80	4.10	5.40
CDRH50D28RNP-1R6NC	B	1.6±30%	15±25%	4.20	3.60	4.70
CDRH50D28RNP-2R2NC	C	2.2±30%	17±25%	3.65	3.05	4.30
CDRH50D28RNP-3R0MC	D	3.0±20%	25±25%	3.10	2.55	3.50
CDRH50D28RNP-4R7MC	E	4.7±20%	40±25%	2.50	2.15	2.70
CDRH50D28RNP-6R8MC	F	6.8±20%	61±25%	2.10	1.75	2.20
CDRH50D28RNP-100MC	G	10±20%	87±25%	1.70	1.40	1.75
CDRH50D28RNP-150MC	H	15±20%	140±20%	1.40	1.10	1.30
CDRH50D28RNP-220MC	J	22±20%	175±20%	1.15	0.98	1.16
CDRH50D28RNP-330MC	K	33±20%	248±20%	0.94	0.78	0.98
CDRH50D28RNP-470MC	L	47±20%	370±20%	0.78	0.65	0.78


※1. Inductance measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 70% of it's nominal value.

※3. Temperature rise current: The value of D.C. current when the temperature rise is Δt=40℃(Ta=20℃).












SMD Power Inductor

CDRH50D28R



Saturation Current & Temperature Rise Graph

— L (20°C) — L (105°C) — ΔT




SMD Power Inductor CDRH50D28R




Solder Reflow Condition

Heat Endurance



Temperature Chart



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel.+852-2880-6781
FAX.+852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel.+81-48-691-7300
FAX.+81-48-691-7340
sales@jp.sumida.com

Chicago

Tel.+1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel.+86-21-5836-3299
FAX.+86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel.+82-2-6237-0777
FAX.+82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel.+49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel.+86-755-8291-0228
FAX.+86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel.+65-6296-3388
FAX.+65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel.+49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel.+886-2-8751-2737
FAX.+886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel.+1-408-321-9660
FAX.+1-408-321-9308
sales@us.sumida.com