

Single-phase Multi-winding Transformers


Type UTI

Transformers

VA Rating		Rated input voltage	Rated output voltage	Type Article No.	Price see price list
IEC	UL/CSA	V	V		

UTI single-phase multi-winding transformers

Universal control -, isolating -and safety transformers
UL 506, CSA 22.2 No. 66
IEC/EN 61 558-2-2, CE



100	100	208 230	2 × 115	UTI0,1-115 206923	
200	200	380 400		UTI0,2-115 206924	
315	315	415 440		UTI0,315-115 206925	
500	500	460 480		UTI0,5-115 206926	
630	630	500 525		UTI0,63-115 206927	
800	800	550 575		UTI0,8-115 206928	
1000	1000	600		UTI1,0-115 206929	
100	100	208 230	1 × 24	UTI0,1-24 206930	
200	200	380 400		UTI0,2-24 206931	
315	315	415 440		UTI0,315-24 206932	
500	500	460 480		UTI0,5-24 206933	
630	630	500 525		UTI0,63-24 206934	
800	800	550 575		UTI0,8-24 206935	
1000	1000	600		UTI1,0-24 206936	

• UTI transformers are also suitable for use in control circuits in accordance with VDE 0113 and EN 60 204 (Electrical control panels for CE machinery).

• UTI multi-winding transformers have fixed secondaries, either 2 x 115 V or 1 x 24 V. A broad range of voltages (208 - 600) can be applied to the transformer primary (using terminals 1.1 and 1.2). Obtain desired voltage by connecting wire jumper to number locations shown below.

Example: 480 VAC
Jumper terminals 1.5 and 1.8
Apply 480V to terminals 1.1 and 1.2

Primary voltage	Wire jumper
1.1 ○ 208	1.1-1.9/1.2-1.3
230	1.1-1.8/1.2-1.4
380	1.3-1.0
400	1.4-1.0
415	1.3-1.9
440	1.4-1.9
460	1.4-1.8
480	1.5-1.8
500	1.6-1.8
525	1.3-1.7
550	1.4-1.7
575	1.5-1.7
600	1.6-1.7

Secondary voltage	Wire jumper
2.1 ○ 24	-
2.2 ○	

Secondary voltage	Wire jumper
2.1 ○ 115	2.1 - 2.4/2.3 - 2.2
230	2.3 - 2.4
2.3 ○	
2.4 ○	
2.1 ○	

Note:
if two separate 115 V secondaries are required, no jumper is necessary and each 115V secondary would have 50% of the rated VA.