


For Patient-Care Areas - 4-outlet Medical-Grade Power Strip with 3-ft. Coiled Cord (Extends to 10 Feet)

MODEL NUMBER: **PS-410-HGOEMCC**



Description

Tripp Lite's PS-410-HG-OEMCC Power Strip is designed to be installed on any mobile cart, diagnostic equipment, instrument, IV pole, etc. It is TUV tested to UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack, table or pedestal-mounted. Features 4 output receptacles, 3-ft. AC coiled cord (extends to 10-ft.) and two built-in resettable circuit breakers that control power to all outlets and protect against overloads. Switchless design prevents accidental shutoff. Optional -use keyhole mounting tabs and flanges.

PLUG/OUTLETS: NEMA 5-15P-HG hospital-grade plug and 4 NEMA5-15R-HG hospital-grade receptacles

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: All-metal coil corded multi-outlet strip.

Features

- Versatile power distribution strip designed to be installed on any mobile cart, IV pole, etc.
- TUV tested to UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted
- 4 x NEMA 5-15R-HG hospital-grade output receptacles
- 3-ft. AC coiled cord (extends to 10-ft.) with integrated, molded NEMA5-15P-HG hospital-grade plug
- Rugged all-metal housing withstands years of use without breakage
- 15A electrical capacity with two built-in resettable circuit breakers
- 120V, 50/60Hz
- Optional-use keyhole mounting tabs and flanges
- Switchless design prevents accidental shutoff

Specifications

Highlights

- Versatile power distribution strip designed to be installed on any mobile cart, IV pole, etc.
- Tested to UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted
- 4 hospital-grade receptacles and hospital-grade plug
- 3-ft coiled cord, extends to 10-ft.
- Two 15-amp resettable circuit breakers

Applications

- Mobile carts, IV poles and other UL 1363A certified usages.
- Can be used in Patient Care Areas, when properly mounted.

Package Includes

- PS-410-HGOEMCC Power Strip
- Owner's manual and warranty information



General Info	
Product Group	POWER STRIPS
OVERVIEW	
Intended Application	Hospital/Medical
Model Type	For Patient-Care Areas
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Outlet Quantity / Type	4 NEMA 5-15R-HG
Outlet Orientation	Single row of 4
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	10
Input Cord Length (m)	4.572
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.44 x 6.18 x 9.92
Shipping Dimensions (hwd / cm)	6.19 x 15.7 x 25.2
Shipping Weight (lbs.)	2.4
Shipping Weight (kg)	1.09
Unit Dimensions (hwd / in.)	1.73 x 2.50 x 8.54
Unit Dimensions (hwd / cm)	4.39 x 6.35 x 21.69
Unit Weight (lbs.)	2.2
Unit Weight (kg)	1.0
Material of Construction	Metal



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Integrated Keyhole Mounting Tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White
Color (AC Line Cord)	White
Style	Strip
Outlets Measurement (Center to Center)	77.60mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
CERTIFICATIONS	
Approvals	TUV tested to UL 1363A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.