



## IF Filters for Basestations

The following products presented in this data sheet are being withdrawn.

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B39730B3863U210		2006-12-01	2007-02-28	2007-05-31

For further information please contact your nearest EPCOS sales office, which will also support you in selecting a suitable substitute. The addresses of our worldwide sales network are presented at [www.epcos.com/sales](http://www.epcos.com/sales).



# SAW Components

Data Sheet B3863





## SAW Components

B3863

## Low-Loss Filter

72,9746 MHz

## Data Sheet


### Features

- Low-loss IF filter for CDMA base station
- Temperature stable
- Ceramic SMD package
- Unbalanced or balanced operation

### Terminals

- Gold plated


### Ceramic package DCC18



Dimensions in mm, approx. weight 0,8 g

### Pin configuration

- |            |                                  |
|------------|----------------------------------|
| 1          | Input or balanced input          |
| 10         | Input ground or balanced input   |
| 6          | Output or balanced output        |
| 5          | Output ground or balanced output |
| 3, 8       | Ground                           |
| 2, 4, 7, 9 | Case ground                      |



Type	Ordering code	Marking and Package according to	Packing according to
B3863	B39730-B3863-U210	C61157-A7-A54	F61074-V8081-Z000

Electrostatic Sensitive Device (ESD)

### Maximum ratings

Operable temperature range	$T$	-40 / +85	°C
Storage temperature range	$T_{stg}$	-40 / +85	°C
DC voltage	$V_{DC}$	0	V
Source power	$P_s$	0	dBm



# SAW Components

B3863

## Low-Loss Filter

72,9746 MHz

### Data Sheet

#### Characteristics

Operating temperature range:  $T = -40$  to  $+85$  °C  
Terminating source impedance:  $Z_S = 50 \Omega$  and matching network  
Terminating load impedance:  $Z_L = 50 \Omega$  and matching network

			min.	typ.	max.	
<b>Nominal frequency</b>	$f_N$		—	72,9746	—	MHz
<b>Minimum insertion attenuation</b>	$\alpha_N$		—	22,0	24,0	dB
<b>2,5 dB bandwidth</b>	$\alpha_{rel} \leq 2,5$ dB	$B_{2,5dB}$	2,48	2,54	—	MHz
<b>Amplitude ripple (p-p)</b>	$f_N \pm 1,05$ MHz	$\Delta\alpha$	—	1,7	2,2	dB
<b>Integrated phase error (rms)</b>	$f_N \pm 1,24$ MHz	$\Delta\phi$	—	3,4	4,0	deg
<b>Phase linearity (p-p)</b>	$f_N \pm 1,24$ MHz	$\Delta\phi$	—	15,5	18,0	deg
<b>Group delay ripple (p-p)</b>	$f_N \pm 1,05$ MHz	$\Delta\tau$	—	650	800	ns
<b>Return loss</b>	$f_N \pm 1,05$ MHz		—	10	—	dB
<b>Relative attenuation (relative to <math>\alpha_N</math>)</b>		$\alpha_{rel}$				
	0 MHz ... $f_N - 6,0$ MHz		45	60	—	dB
	$f_N \pm 1,505$ MHz ... $f_N \pm 1,875$ MHz		25 <sup>1)</sup>	28	—	dB
	$f_N \pm 1,875$ MHz ... $f_N \pm 2,305$ MHz		30	45	—	dB
	$f_N \pm 2,305$ MHz ... $f_N \pm 2,675$ MHz		35	41	—	dB
	$f_N \pm 2,675$ MHz ... $f_N \pm 4,0$ MHz		37	40	—	dB
	$f_N \pm 4,0$ MHz ... $f_N \pm 6,0$ MHz		40	44	—	dB
	$f_N + 6,0$ MHz ... 150 MHz		45	60	—	dB
<b>Input 3rd-order intercept point</b>	$IIP3$		40	—	—	dBm
<b>Temperature coefficient of frequency <sup>2)</sup></b>	$TC_f$		—	-0,036	—	ppm/K <sup>2</sup>
<b>Turnover temperature</b>	$T_0$		—	30,0	—	°C


<sup>1)</sup> 26 dB for temperatures greater than -25 °C

<sup>2)</sup> Temperature dependance of  $f_c$ :  $f_c(T_A) = f_c(T_0)(1 + TC_f(T_A - T_0)^2)$




## Data Sheet

## Normalized frequency response



## Normalized frequency response (passband)





# SAW Components


B3863

## Low-Loss Filter


72,9746 MHz

### Data Sheet

#### Normalized frequency response (wideband)



#### Test Matching Network to 50Ω (element values depend on PCB layout)





<b>SAW Components</b>	<b>B3863</b>
<b>Low-Loss Filter</b>	<b>72,9746 MHz</b>
<b>Data Sheet</b>	

**Published by EPCOS AG**

**Surface Acoustic Wave Components Division, SAW MC IS**

**P.O. Box 80 17 09, 81617 Munich, GERMANY**

© EPCOS AG 2003. Reproduction, publication and dissemination of this brochure and the information contained therein without EPCOS' prior express consent is prohibited.

Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.

This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.