

4

3

2

1

LOC CM DIST 53

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

MAY 26, 1981



© COPYRIGHT 1973

BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS

RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.



SECTION A-A



SECTION B-B

- ① .000030 THICK GOLD OVER NICKEL ON INSIDE OF RECEPTACLE; REMAINDER OF CONTACT IS NICKEL PLATED.
- ② .000030 THICK GOLD OVER NICKEL ON INSIDE OF RECEPTACLE AND WIRE BARREL; REMAINDER OF CONTACT IS NICKEL PLATED.

REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓		S	REDRAWN W/O CHANGE M-6457	6-8-81	MSF/S.H.
✓	✓		T	ADDED .090, .180 DIMS., PT. OF MEAS., M-7351	5/12/83	TW/DH
✓			U	REVISED AG 57	10/21/83	S. H. / S. H.
✓			U	RESTORED	4/3/85	BK0/RS
✓			V	REV PER ECN CM 116	8-6-85	CM/RS
			W	REV PER EC 0730-3607-91	1-6-94	RV RS

350689-7	GOLD	①	.010 BRASS	350570-7
—			.010 PH. BRZ	350570-6
350689-3	PRE-TIN		.00 PH. BRZ	350570-3
350689-2	GOLD	②	.010 BRASS	350570-2
350689-1	PRE-TIN			350570-1
LOOSE PIECE (REF)	FINISH		MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±	CONTRACT NO DR M. FEHER 5-26-81 CHK J.S. Heide 6/9/81 APPR R. P. B. 6-10-81 APPD	AMP AMP INCORPORATED Harrisburg, Pa.	
WIRE RANGE 24-18 AWG	DSGN APPD	NAME SOCKET, UNIVERSAL MATE-N-LOK	
INSULATION RANGE .100 DIA MAX	OTHER APPD	SIZE B	FSCM NO 00779
		DRAWING NO 350570	SHEET —
		SCALE 4-1	