



HCMD-10-S-03.00-01

**(2.54 mm) .100"**

# IDC SOCKET & TERMINAL CABLE

**Mates with:**

TSW, MTSW, TST, HTST,  
EW, ZST, MTLW, TSM,  
EJH-02 (HCSD only)

**SPECIFICATIONS**

For complete specifications and recommended PCB layouts see [www.samtec.com?HCSD](http://www.samtec.com?HCSD) or [www.samtec.com?HCSS](http://www.samtec.com?HCSS)

**HCSD, HCSS**

**Insulator Material:**  
Black Liquid Crystal Polymer  
**Temperature Range:**  
-20 °C to +105 °C  
(Rainbow Cable)  
-40 °C to +105 °C (Gray Cable)

**Voltage Rating:**

425 VAC/600 VDC

**Contact:**

Phosphor Bronze

**Plating:**

10 μ" (0.25 μm) Au on  
contact area, 150 μ" (3.81 μm)  
Sn on balance over  
50 μ" (1.27 μm) Ni.

**Lead Size Range:**

.024" (0.61 mm) SQ to

.026" (0.66 mm) SQ

**Lead Insertion Depth:**

.185" (4.70 mm) to

.250" (6.35 mm)

**Wire:**

28 AWG 7/36 stranded

Tinned Copper

**RoHS Compliant:**

Yes

**SPECIFICATIONS**

For complete specifications and recommended PCB layouts see [www.samtec.com?HCMD](http://www.samtec.com?HCMD) or [www.samtec.com?HCMS](http://www.samtec.com?HCMS)

**HCMD, HCMS**

**Insulator Material:**  
Black Liquid Crystal Polymer  
**Temperature Range:**  
-20 °C to +105 °C  
(Rainbow Cable)  
-40 °C to +105 °C (Gray Cable)

**Voltage Rating:**

425 VAC/600 VDC

**Terminal:**

Phosphor Bronze

**Plating:**

Sn over 50 μ" (1.27 μm) Ni

**Wire:**

28 AWG 7/36 stranded

Tinned Copper

**RoHS Compliant:**

Yes

**Note:**

IDC assemblies are  
non-standard, non-returnable.

| TYPE STRIP | ROW OPTION                                       | NO. PINS PER ROW                                          | END ASSEMBLY | ASSEMBLED LENGTH                                                                                       |
|------------|--------------------------------------------------|-----------------------------------------------------------|--------------|--------------------------------------------------------------------------------------------------------|
|            | <b>S</b><br>= Single<br><br><b>D</b><br>= Double | <b>-05, -08,<br/>-10, -12,<br/>-13, -15,<br/>-17, -20</b> |              | <b>-"XX.XX"</b><br>= Assembled Length<br><br>Assembled Length in<br>INCHES (±1/8")<br>2 inches minimum |

### HCM = Male Strip

| LEAD STYLE | A           |
|------------|-------------|
| -01        | (3.05) .120 |
| -02        | (5.84) .230 |

### HCS = Socket Strip

### -S = Single End

Socket or Male Plug on one end

### -D = Double End

Socket or Male Plug on each end

### -T = Transfer End

Male Plug on one end with socket on other.  
**Begin part number with HCM.**

HCSS-15-S-03.00-01-G

HCSD-10-S-03.00-01-T-G

## HCMD, HCMS, HCSD, HCSS SERIES

### LEAD STYLE

**-01**

= HCSS/HCSD or  
(3.05 mm) .120" tail for  
HCMS/HCMD

**-02**

= (5.84 mm) .230" tail  
HCMS/HCMD only

### PLATING OPTION

**-S**

= 10  $\mu$ " (0.25  $\mu$ m) Gold on contact area or tail,  
Tin on balance  
(Standard on HCSS & HCSD. Leave blank)

**-T**

= Tin  
(Standard on HCMS & HCMD. Leave blank)

### NOTCH POLARIZATION

**-N** = Notch Polarization



Required for HCSS and HCSD.  
(Not available on HCMS or HCMD,  
unless Transfer, then only the  
socket is polarized.)

### OTHER OPTIONS

**-P "XX"**

= Position Polarization



Specify "XX" as position. For  
Double the same position will  
be polarized on both ends. (Not  
available on HCM, unless Transfer,  
then only the socket is polarized)

**-ST "X"**

= Stripped & Tinned


Specify Suffix from table.  
All dimensions are  $\pm 1/16$ " (1.59 mm).



|             |              |
|-------------|--------------|
| <b>-ST8</b> | 1/8" (3.18)  |
| <b>-ST4</b> | 1/4" (6.35)  |
| <b>-ST2</b> | 1/2" (12.70) |
| <b>-ST3</b> | 3/8" (9.53)  |

**-S "XX"**

= Daisy Chain Single



When mating double row connector  
with two single row connectors, the  
outer most single will be connected  
to Conductor #1 and the inside  
single to Conductor #2.

**-R**

= Reversed



**-M**

= Middle Reversed



Requires -SXX, -WXX or -DXX

**-O**

= Outside Reversed



Requires -SXX, -WXX or -DXX

**-G**


= Gray Cable

Standard cable is color coded. Specify  
-G for Gray cable with one red edge.

**-B "XX"**

= Breakout

Specify "XX" as number of  
conductors to be broken out.



Breakout starts with  
Number 1 lead indicated  
by brown wire or red stripe.  
Shown on top side.


**-RW**

= Reversed Wiring

#1 wire opposite position #1

**-D "XX"**

= Daisy Chain, Double



**-W "XX"**

= Wiring Reversed  
Daisy Chain, Single

Same as -S "XX" except outer strip  
connected to conductor #2 and inside  
strip connected to conductor #1.