



1. MATERIAL:
HOUSING - PBT POLYESTHER, BLACK, UL 94V-0
- TERMINALS - 0.33 THICK PHOS BRONZE PLATED WITH 1.27um MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 2um MINIMUM THICK MATTE TIN IN ACTION PIN COMPLIANT PIN TERMINAL AREA OVER 1.27um MINIMUM THICK NICKEL UNDERPLATE
- SHIELD - 0.25 THICK COPPER ALLOY PLATED WITH 2.03um MINIMUM BRIGHT TIN OVER 1.27um MINIMUM NICKEL
- GROUNDING CLIP - 2.03 um MIN MATTE TIN OVER COPPER, PRE-PLATED COPPER ALLOY
- LED - DIFUSED EPOXY LENS 2.29 um SILVER OVER NICKEL PRE-PLATED CARBON STEEL LEADS
- ACTION PIN - COMPLIANT PIN CONTACTS 0.3 THICK BRASS PLATED WITH 2-4um BRIGHT TIN.
2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. DRILLED HOLE DIA = 1.020 ± 0.025
COPPER THICKNESS = 0.025 ± 0.075
TIN-LEAD THICKNESS = .008
4. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
5. DATE CODE LOCATED ON REAR OF PART APPROXIMATELY AS SHOWN
6. CONTACTS ARE NOT INTENDED TO BE ALIGNED WITH EACH OTHER
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
8. ONLY FOR 6368168-7, -8
CONTACT AREA LUBRICATED WITH BELLCORE APPROVED
LUBRICANT TECHNICAL REFERENCE GR-1217-CORE
ISSUE 1, NOVEMBER 1995.


6368168-1 SHOWN
SHEET 1





RECOMMENDED PANEL CUT-OUT





PC BOARD LAYOUT (COMPONENT SIDE)



6	8	N/A	N/A	N/A	N/A	NO	WITHOUT LED PORTS	6368168-8
	8	GREEN	GREEN	GREEN	GREEN	NO	WITH LED PORTS	6368168-7
		GREEN	GREEN	YELLOW	YELLOW	YES	WITH LED PORTS	6368168-6
		GREEN	GREEN	GREEN	GREEN	YES	WITH LED PORTS	6368168-5
		YELLOW	YELLOW	GREEN	GREEN	YES	WITH LED PORTS	6368168-4
7	OBSOLETE	N/A	N/A	N/A	N/A	YES	WITHOUT LED PORTS	6368168-2
		N/A	N/A	N/A	N/A	NO	WITHOUT LED PORTS	6368168-1
		LED #4	LED #3	LED #2	LED #1	GROUNDING CLIP	SHIELD STYLE	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28JUL2005 A. FERNANDEZ-NOVA CHG 28JUL2005 J. WESTMAN APVD 28JUL2005 S. FLICKINGER		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.1 3 PLC ±0.13 4 PLC ±. ANGLES ±.		NAME STACKED MODULAR JACK ASSEMBLY, 2X1, 8 POSITION, SHIELDED PANEL MOUNT, OFFSET, CAT 5	
		PRODUCT SPEC 108-1854 APPLICATION SPEC 114-2160		SIZE CAGE CODE DRAWING NO A1 00779 C-6368168	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		RESTRICTED TO SCALE 3:1 SHEET 1 OF 2 REV F	
CUSTOMER DRAWING					




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00	-	-	SEE SHEET 1	-	-	-



6368168-6 SHOWN
SHEET 2

SHIELD WITH LED CUTOUTS AND
STANDARD PANEL GROUNDS



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN A. FERNANDEZ-DOCK 28 JUL 2005	 TE Connectivity	
DIMENSIONS:		CHK J. WESTMAN 28 JUL 2005		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. FLICKINGER 28 JUL 2005	NAME STACKED MODULAR JACK ASSEMBLY, 2X1, 8 POSITION, SHIELDED PANEL GROUND, OFFSET, CAT 5	
	9 PLC ±	PRODUCT SPEC	SIZE	
	1 PLC ±	108-1854	CAGE CODE	
	3 PLC ±0.1	APPLICATION SPEC	DRAWING NO	
	5 PLC ±0.13	114-2160	A1 00779	
MATERIAL	FINISH	WEIGHT	C=6368168	
SEE NOTE 1	SEE NOTE 1	-	RESTRICTED TO	
CUSTOMER DRAWING		SCALE	3:1	SHEET 2 OF 2
		REV	-	