



30x30x10mm Series

Spot cooling, also suitable for small space requirements, laptops PC and notebook, PC.

EXTERNAL DIMENSIONS



Housing	Impeller	Bearing Available	Protection	Operating Temp*
Plastic (UL: 94V-0)	Plastic (UL: 94V-0)	Ball/Hydro	Current Limit	-10°C~70°C

*: -10°C~60°C for fans with sleeve/ball combination bearings.

SPECIFICATIONS (NOMINAL)

Frame Size	Model No.	Bearing type	Voltage (V)	Current (A)	Power (W)	Speed (rpm)	Air flow (CFM)	Static pressure (mmAq)	Noise level (dB/A)	Weight (g)
30x30x10mm	AD0305MX-G50	Hydro	5V	0.12	0.6	9000	4.52	4.51	28.2	8
30x30x10mm	AD0305MB-G50	Ball	5V	0.12	0.6	9000	4.52	4.51	28.2	8
30x30x10mm	AD0305LX-G50	Hydro	5V	0.09	0.45	8000	4.00	3.81	23.8	8
30x30x10mm	AD0305LB-G50	Ball	5V	0.09	0.45	8000	4.00	3.81	23.8	8
30x30x10mm	AD0305DX-G50	Hydro	5V	0.05	0.25	5500	2.46	1.97	14.6	8
30x30x10mm	AD0305DB-G50	Ball	5V	0.05	0.25	5500	2.46	1.97	14.6	8
30x30x10mm	AD0312MX-G50	Hydro	12V	0.09	1.08	9000	4.52	4.51	28.2	8
30x30x10mm	AD0312MB-G50	Ball	12V	0.09	1.08	9000	4.52	4.51	28.2	8
30x30x10mm	AD0312LX-G50	Hydro	12V	0.07	0.84	8000	4.00	3.81	23.8	8
30x30x10mm	AD0312LB-G50	Ball	12V	0.07	0.84	8000	4.00	3.81	23.8	8

Specifications subject to change without notice.

* Sound level is measured at the distance of one (1) meter from the axis of fan intake.

PERFORMANCE CURVES

* MOTOR PROTECTIVE CIRCUIT AND THIRD LEAD WIRE

0	1	2	3	4	5	6	7
✓						✓	

* SAFETY APPROVALS

✓	✓		✓
UL	UL	SP	CE

