

# 15/20 Watts

## JCM Series



- Very High Power Density
- 2:1 Input Range
- Operating Temperature -40 °C to +105 °C
- Single & Dual Outputs
- 1600 VDC Isolation
- High Efficiency – up to 89%
- 3 Year Warranty

### Specification

#### Input

|                                |                                                                                                                                                                                     |
|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Input Voltage Range            | <ul style="list-style-type: none"> <li>• 12 V (9-18 VDC)</li> <li>• 24 V (18-36 VDC)</li> <li>• 48 V (36-75 VDC)</li> </ul>                                                         |
| Input Current                  | <ul style="list-style-type: none"> <li>• See table</li> </ul>                                                                                                                       |
| Input Filter                   | <ul style="list-style-type: none"> <li>• Pi network</li> </ul>                                                                                                                      |
| Input Reflected Ripple Current | <ul style="list-style-type: none"> <li>• JCM15: 20 mA pk-pk, JCM20: 30 mA pk-pk through 12 <math>\mu</math>H inductor and 47 <math>\mu</math>F capacitor, 5 Hz to 20 MHz</li> </ul> |
| Input Surge                    | <ul style="list-style-type: none"> <li>• 12 V models: 36 VDC for 100 ms</li> <li>• 24 V models: 50 VDC for 100 ms</li> <li>• 48 V models: 100 VDC for 100 ms</li> </ul>             |

#### Output

|                          |                                                                                                                                                                                                                                                                                                                                                                                                                     |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Output Voltage           | <ul style="list-style-type: none"> <li>• See table</li> </ul>                                                                                                                                                                                                                                                                                                                                                       |
| Output Trim              | <ul style="list-style-type: none"> <li>• <math>\pm 10\%</math> max on single output</li> </ul>                                                                                                                                                                                                                                                                                                                      |
| Minimum Load             | <ul style="list-style-type: none"> <li>• No minimum load required</li> </ul>                                                                                                                                                                                                                                                                                                                                        |
| Initial Set Accuracy     | <ul style="list-style-type: none"> <li>• <math>\pm 1\%</math> max</li> </ul>                                                                                                                                                                                                                                                                                                                                        |
| Start Up Delay           | <ul style="list-style-type: none"> <li>• 20 ms typical</li> </ul>                                                                                                                                                                                                                                                                                                                                                   |
| Line Regulation          | <ul style="list-style-type: none"> <li>• JCM15: <math>\pm 0.2\%</math> max, JCM20: <math>\pm 0.5\%</math></li> </ul>                                                                                                                                                                                                                                                                                                |
| Load Regulation          | <ul style="list-style-type: none"> <li>• <math>\pm 0.5\%</math> max single, <math>\pm 1.0\%</math> max dual</li> </ul>                                                                                                                                                                                                                                                                                              |
| Cross Regulation         | <ul style="list-style-type: none"> <li>• <math>\pm 5\%</math> on dual output models (see note 2)</li> </ul>                                                                                                                                                                                                                                                                                                         |
| Transient Response       | <ul style="list-style-type: none"> <li>• <math>&lt; 3\%</math> max deviation, recovery to within 1% in 250 <math>\mu</math>s for a 25% load change</li> </ul>                                                                                                                                                                                                                                                       |
| Ripple & Noise           | <ul style="list-style-type: none"> <li>• 100 mV pk-pk, 20 MHz bandwidth, (see note 3)</li> </ul>                                                                                                                                                                                                                                                                                                                    |
| Overvoltage Protection   | <ul style="list-style-type: none"> <li>• 3.3 V models: 3.9 V typical</li> <li>• 5 V models: 6.2 V typical</li> <li>• 12 V models: 15 V typical</li> <li>• 15 V models: 18 V typical</li> <li>• <math>\pm 5</math> V models: <math>\pm 6.2</math> V typical</li> <li>• <math>\pm 12</math> V models: <math>\pm 15</math> V typical</li> <li>• <math>\pm 15</math> V models: <math>\pm 18</math> V typical</li> </ul> |
| Overload Protection      | <ul style="list-style-type: none"> <li>• 150% of full load typical</li> </ul>                                                                                                                                                                                                                                                                                                                                       |
| Short Circuit Protection | <ul style="list-style-type: none"> <li>• Trip &amp; restart (hiccup) with auto recovery</li> </ul>                                                                                                                                                                                                                                                                                                                  |
| Maximum Capacitive Load  | <ul style="list-style-type: none"> <li>• See table</li> </ul>                                                                                                                                                                                                                                                                                                                                                       |
| Temperature Coefficient  | <ul style="list-style-type: none"> <li>• <math>\pm 0.02/^{\circ}\text{C}</math> max</li> </ul>                                                                                                                                                                                                                                                                                                                      |
| Remote On/Off            | <ul style="list-style-type: none"> <li>• On <math>&gt; 3.0</math> VDC or open circuit</li> <li>• Off <math>&lt; 1.2</math> VDC or short circuit pins 2 &amp; 3</li> </ul>                                                                                                                                                                                                                                           |

#### General

|                       |                                                                                                                                                   |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Efficiency            | <ul style="list-style-type: none"> <li>• See table</li> </ul>                                                                                     |
| Isolation             | <ul style="list-style-type: none"> <li>• 1600 VDC Input to Output</li> <li>• 1600 VDC Input to Case</li> <li>• 1600 VDC Output to Case</li> </ul> |
| Isolation Capacitance | <ul style="list-style-type: none"> <li>• JCM15: 1200 pF max, JCM20: 1000 pF max</li> </ul>                                                        |
| Switching Frequency   | <ul style="list-style-type: none"> <li>• JCM15: 375 kHz typical, JCM20: 330 kHz typical</li> </ul>                                                |
| Power Density         | <ul style="list-style-type: none"> <li>• JCM15: 38.4 W/in<sup>3</sup>, JCM20: 51.3 W/in<sup>3</sup></li> </ul>                                    |
| MTBF                  | <ul style="list-style-type: none"> <li>• <math>&gt; 560</math> kHrs to MIL-STD-217F at 25 °C, GB</li> </ul>                                       |

#### Environmental

|                       |                                                                                                                                                                                               |
|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating Temperature | <ul style="list-style-type: none"> <li>• -40 °C to +105 °C, derate from 100% load at +65 °C to no load at +105 °C for JCM15 and 100% load at +55 °C to no load at 105 °C for JCM20</li> </ul> |
| Case Temperature      | <ul style="list-style-type: none"> <li>• +105 °C max</li> </ul>                                                                                                                               |
| Storage Temperature   | <ul style="list-style-type: none"> <li>• -40 °C to +125 °C</li> </ul>                                                                                                                         |
| Humidity              | <ul style="list-style-type: none"> <li>• Up to 90%, non-condensing</li> </ul>                                                                                                                 |
| Cooling               | <ul style="list-style-type: none"> <li>• Natural convection</li> </ul>                                                                                                                        |

#### EMC


|                    |                                                                                                                                             |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------|
| Emissions          | <ul style="list-style-type: none"> <li>• EN55022 class A conducted &amp; radiated with external components, see application note</li> </ul> |
| ESD Immunity       | <ul style="list-style-type: none"> <li>• EN61000-4-2, 6 kV contact discharge, 8 kV air discharge, Perf Criteria A</li> </ul>                |
| Radiated Immunity  | <ul style="list-style-type: none"> <li>• EN61000-4-3, 10 V/m, Perf Criteria A</li> </ul>                                                    |
| EFT/Burst          | <ul style="list-style-type: none"> <li>• EN61000-4-4, level 2, Perf Criteria A*</li> </ul>                                                  |
| Surge              | <ul style="list-style-type: none"> <li>• EN61000-4-5, level 2, Perf Criteria A</li> </ul>                                                   |
| Conducted Immunity | <ul style="list-style-type: none"> <li>• EN61000-4-6, 10 Vrms, Perf Criteria A</li> </ul>                                                   |
| Magnetic Field     | <ul style="list-style-type: none"> <li>• EN61000-4-8, 1 A/m, Perf Criteria A</li> </ul>                                                     |

\*External input capacitor required, 220  $\mu$ F/100 V.

**Notes**

1. Input current specified at nominal input.
2. Cross regulation for duals is  $\pm 5\%$  when one output is at 100% and the other is varied between 25% and 100%.
3. Measured with 1  $\mu\text{F}$  ceramic capacitor in parallel with a 10  $\mu\text{F}$  electrolytic across output rails on single output models or 1  $\mu\text{F}$  ceramic capacitor only on dual output models.

## Mechanical Details




| Pin Connections |               |               |     |        |       |
|-----------------|---------------|---------------|-----|--------|-------|
| Pin             | Single        | Dual          | Pin | Single | Dual  |
| 1               | +Vin          | +Vin          | 4   | +Vout  | +Vout |
| 2               | -Vin          | -Vin          | 5   | Trim   | Com   |
| 3               | Remote On/Off | Remote On/Off | 6   | -Vout  | -Vout |

## Notes

1. All dimensions are in inches (mm),
2. Weight: 0.04 lbs (20 g) approx.
3. Pin diameter:  $0.004 \pm 0.002$  ( $1.0 \pm 0.05$ )
4. Pin pitch tolerance:  $\pm 0.014$  ( $\pm 0.35$ )
5. Case tolerance:  $\pm 0.02$  ( $\pm 0.5$ )

## Application Notes


## Output Trim



| Trim Resistor Values |                |                  |
|----------------------|----------------|------------------|
| Model Number         | Trim up<br>10% | Trim down<br>10% |
| JCM-S3V3             | 8 kΩ           | 12 kΩ            |
| JCM-S05              | 10 kΩ          | 5 kΩ             |
| JCM-S12              | 20 kΩ          | 7 kΩ             |
| JCM-S15              | 20 kΩ          | 6 kΩ             |

*Approximate values.*

## Input Filter



Output can be externally trimmed by using the method above.  
(Single output models only). For variable trimming, use 100 k $\Omega$  potentiometer