



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn100%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	5 mOhms max.
D.C. RESISTANCE	3-5 @20°C	5 mOhms max.
D.C. RESISTANCE	7-11 @20°C	3.5 mOhms max.
INDUCTANCE	2-5 tie(3+4), 100kHz, 100mVAC, Ls	300.0uH min.
LEAKAGE INDUCTANCE	2-5 tie(3+4, 7+11), 100kHz, 100mVAC, Ls	400nH max.
DIELECTRIC	2-7 tie(3+4), 500VDC, 1 second	-
URNS RATIO	(2-4):(7-11)	1:1, ±1%
URNS RATIO	(3-5):(7-11)	1:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
6C	11/12	Method: Tape & Reel PKG-0793		Angles: ±1°	TRANSFORMER	750341136
6B	4/12	www.we-online.com/midcom		Decimals: ±.005 [.13]		
6A	10/11	SEE REVISION SHEET FOR		Fractions: ±1/64		
		REVISION LEVEL		Footprint: ±.005 [.13]		
				This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341136	SPECIFICATION SHEET 1 OF 1

