

Trage- und Aufstellbügel

Carrying and Rear up Handles


Technische Daten	Technical Data
Werkstoff Aufstellbügel PA6 UL94	Material Rear up handle PA6 UL94
Griffprofil Al Mg Si 0,5 naturton eloxiert	Handle profile Al Mg Si 0,5 natural anodized
Belastbarkeit bis 300 N / 0,3 m Griffprofillänge (statisch)	Carrying capacity up to 300 N / 0,3 m profile length (static)

30° rastender Aufstellbügel. Griffverstellung durch Druckknopfbetätigung. Einfache Montage durch Einlochbefestigung. Das Griffprofil wird durch Spreizklemmung gehalten und muss getrennt bestellt werden. Griffprofillängen nach Wahl = Gehäusebreite.

30° snap-in rear-up handle. Handle adjustment through push button operation. Simple installation on a single hole. The handle profile is kept in place by clampdown and must be ordered separately. Handle profile lengths according to customer requirement = case width.




1 Paar · 1 pair		
L	Farbe Aufstellbügel Color rear up handle	Art.-Nr.
180	schwarz · black	3791.7003
250	schwarz · black	3791.7001
180	Weißaluminium lackiert whitealuminium enameled	3791.7004
250	Weißaluminium lackiert whitealuminium enameled	3791.7002




Einschließlich Schrauben DIN 84-M4 und Scheiben DIN 125.
Including screws DIN 84-M4 and washers DIN 125.

Griffprofil · Grip profile	
L	Art.-Nr.
1000	3791.1000
3000	3791.3000

≠Andere Längen auf Anfrage · other length on request



Bohrschema · Drilling scheme



Anti-Rutsch-Element für Aufstellbügel

Anti-slide Element for Rear-up Handle

Technische Daten	Technical Data
Werkstoff Elastomer schwarz	Material Elastomer black
Umgebungstemperatur -30° C ... +100° C	Ambient temperature -30° C ... +100° C



Art.-Nr.	3791.0004
----------	-----------

