




NOTES:


1. SUGGESTED MOUNTING HOLE: $\phi.221$
2. HARDWARE IS INCLUDED

CAPACITANCE	5000 pF GMV
TEMP. RANGE	-55°C TO +125°C
CURRENT	10 AMPS
WORKING VOLTAGE	85°C 200 VDC 125°C 100 VDC
DC RESISTANCE	.01 OHMS MAX.

IL=PER MIL-STD-220, NO LOAD

FREQ. MHz	I.L. (db)
10	20
50	--
100	65
1 GHz	70
10 GHz	70

SCHEMATIC



MARKING

PART: 1270025
BAG: SCI
1270-025
DATE CODE
LOT NO.
QTY./BAG (200 MAX.)

	8	7	6	5	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	ERIE, FAIRVIEW PENNSYLVANIA	
	CN 210694	CN 209176	CN 200615	CN 184990 REDRAWN	CHANGE NOTICE	Fractions $\pm 1/64$			
						Dec. .xx $\pm$	Dwn. KAUFFMAN	Description	
						Dec. .xxx $\pm .010$	Ckd. 10/21/02	FILTER SING, PI, BSHG.	
						Angles $\pm 0^{\circ} 30'$			
						CODE IDENT. NO. DLSP2	Scale NONE	1270-025	