

Coaxial Cable Connector 24_QN-50-7-3/133_N

Description

Straight bulkhead cable feed through

Interface standards
QN QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.022 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU, RoHS	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00008734
Catalogue drawing	DCA-00008736
Assembly instruction	DOC-0000184790
Mounting hole	DOU-00008737

Ordering Information

Single package	24_QN-50-7-3/133_NE
----------------	---------------------

Additional Information

Suitable cables	RG_213_/U, GX_07272, RADOX_RF_213
-----------------	-----------------------------------