




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	19MAR2015	DL	CW
	B	ECR-15-013292	24SEP2015	DL	CW
	B1	ECR-16-018198	12FEB2017	QY	CW

- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 2.5 KV
POLLUTION DEGREE: 2
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X10XX000)


- 注释:
1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 2.5 KV
污染等级: 2
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
2. 端子需要单独订购.
(订货号参考图面: T20200X10XX000)



TYPE-1:T2030422101-000 TE LOGO
类 型-1:T2030422101-000 TE LOGO




4X M3 THREAD RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩0.5Nm



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	DAVID LI	18MAR2015	 TE Connectivity	
		CHK	CHRIS WANG	18MAR2015		
		APVD	XU XIANG	18MAR2015	NAME	
		PRODUCT SPEC			HDD-042-M	
		APPLICATION SPEC				
		114-137043				
		WEIGHT				
		-				
		CUSTOMER DRAWING				
					SIZE	RESTRICTED TO
					A3	-
					CAGE CODE	
					-	
					DRAWING NO	
					©T2030422101000	
					SCALE	
					1:1	
					SHEET	
					1 OF 2	
					REV	
					B1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-







ALL DIMENSIONS ARE SAME AS TYPE 1,
EXCEPT THOSE DEFINED IN THIS TYPE.
除了在本类型中定义的尺寸外，其它尺寸同类型1


NOTES:

SEE SHEET 1


注释:
见页 1



TYPE-2:T2030422101-001 STAINLESS STEEL SCREW,NO LOGO
类 型-2:T2030422101-001 不锈钢螺丝,无LOGO



T2030422101-001	HDD-042-M	HDD-042 MALE INSERT, STAINLESS STEEL SCREW,NO LOGO HDD-042公插,不锈钢螺丝,无LOGO	TYPE-2 类 型-2
T2030422101-000	HDD-042-M	HDD-042 MALE INSERT HDD-042公插	TYPE-1 类 型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI	18MAR2015	 TE Connectivity			
		CHK CHRIS WANG	18MAR2015				
DIMENSIONS: mm		APVD XU XIANG	18MAR2015	NAME HDD-042-M			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		0 PLC ±-		108-137043			
		1 PLC ±-		APPLICATION SPEC			
		2 PLC ±-		114-137043			
		3 PLC ±-		SIZE			
		4 PLC ±-		CAGE CODE			
		ANGLES ±-		DRAWING NO			
MATERIAL		FINISH		RESTRICTED TO			
-		-		A3			
-		-		-			
		WEIGHT		C-T2030422101000			
		-		-			
CUSTOMER DRAWING				SCALE		SHEET	
				1:1		2 OF 2	
				REV		B1	