


FEATURES

- 1.8-V, 2.7-V, and 5-V Specifications
- Rail-to-Rail Output Swing
 - 600-Ω Load . . . 80 mV From Rail
 - 2-kΩ Load . . . 30 mV From Rail
- V_{ICR} . . . 200 mV Beyond Rails
- Gain Bandwidth . . . 1.4 MHz
- Supply Current . . . 100 μ A/Amplifier
- Max V_{IO} . . . 4 mV
- Space-Saving Packages
 - LMV931: SOT-23 and SC-70
 - LMV932: MSOP and SOIC
 - LMV934: SOIC and TSSOP


APPLICATIONS

- Industrial (Utility/Energy Metering)
- Automotive
- Communications (Optical Telecom, Data/Voice Cable Modems)
- Consumer Electronics (PDAs, PCs, CDR/W, Portable Audio)
- Supply-Current Monitoring
- Battery Monitoring


LMV931 . . . DBV (SOT-23-5) OR DCK (SC-70) PACKAGE
(TOP VIEW)



LMV932 . . . D (SOIC) OR
DGK (VSSOP/MSOP) PACKAGE
(TOP VIEW)



LMV934 . . . D (SOIC) OR PW (TSSOP) PACKAGE
(TOP VIEW)



DESCRIPTION/ORDERING INFORMATION

ORDERING INFORMATION

| T_A | PACKAGE ⁽¹⁾ | | | ORDERABLE PART NUMBER | TOP-SIDE MARKING ⁽²⁾ |
|----------------|------------------------|------------------|--------------|-----------------------|---------------------------------|
| –40°C to 125°C | Single | SOT-23 – DBV | Reel of 3000 | LMV931IDBVR | RBB_ |
| | | | Reel of 250 | LMV931IDBVT | PREVIEW |
| | | SC-70 – DCK | Reel of 3000 | LMV931IDCKR | RB_ |
| | | | Reel of 250 | LMV931IDCKT | PREVIEW |
| | Dual | MSOP/VSSOP – DGK | Reel of 2500 | LMV932IDGKR | RD_ |
| | | | Reel of 250 | LMV932IDGKT | PREVIEW |
| | | SOIC – D | Tube of 75 | LMV932ID | MV932I |
| | | | Reel of 2500 | LMV932IDR | |
| | Quad | SOIC – D | Tube of 50 | LMV934ID | LMV934I |
| | | | Reel of 2500 | LMV934IDR | |
| | | TSSOP – PW | Tube of 90 | LMV934IPW | MV934I |
| | | | Reel of 2000 | LMV934IPWR | |

(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

(2) DBV/DCK/DGK: The actual top-side marking has one additional character that designates the assembly/test site.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

LMV931 SINGLE, LMV932 DUAL, LMV934 QUAD 1.8-V OPERATIONAL AMPLIFIERS WITH RAIL-TO-RAIL INPUT AND OUTPUT

SLOS441G–AUGUST 2004–REVISED FEBRUARY 2006

DESCRIPTION/ORDERING INFORMATION (CONTINUED)


The LMV93x devices are low-voltage low-power operational amplifiers that are well suited for today's low-voltage and/or portable applications. Specified for operation of 1.8 V to 5 V, they can be used in portable applications that are powered from a single-cell Li-ion or two-cell batteries. They have rail-to-rail input and output capability for maximum signal swings in low-voltage applications. The LMV93x input common-mode voltage extends 200 mV beyond the rails for increased flexibility. The output can swing rail-to-rail unloaded and typically can reach 80 mV from the rails, while driving a 600- Ω load (at 1.8-V operation).

During 1.8-V operation, the devices typically consume a quiescent current of 103 μ A per channel, and yet they are able to achieve excellent electrical specifications, such as 101-dB open-loop DC gain and 1.4-MHz gain bandwidth. Furthermore, the amplifiers offer good output drive characteristics, with the ability to drive a 600- Ω load and 1000-pF capacitance with minimal ringing.

The LMV93x devices are offered in the latest packaging technology to meet the most demanding space-constraint applications. The LMV931 is offered in standard SOT-23 and SC-70 packages. The LMV932 is available in the traditional MSOP and SOIC packages. The LMV934 is available in the traditional SOIC and TSSOP packages.

The LMV93x devices are characterized for operation from -40°C to 125°C , making the part universally suited for commercial, industrial, and automotive applications.

SIMPLIFIED SCHEMATIC



Absolute Maximum Ratings⁽¹⁾

over free-air temperature range (unless otherwise noted)

| | | MIN | MAX | UNIT |
|---|---|--------------------|-----------------|------|
| $V_{CC+} - V_{CC-}$ | Supply voltage ⁽²⁾ | | 5.5 | V |
| V_{ID} | Differential input voltage ⁽³⁾ | Supply voltage | | |
| V_I | Input voltage range, either input | $V_{CC-} - 0.2$ | $V_{CC+} + 0.2$ | V |
| Duration of output short circuit (one amplifier) to $V_{CC\pm}$ ⁽⁴⁾⁽⁵⁾ | | Unlimited | | |
| θ_{JA} | Package thermal impedance ⁽⁵⁾⁽⁶⁾ | D package (8 pin) | | 97 |
| | | D package (14 pin) | | 86 |
| | | DBV package | | 206 |
| | | DCK package | | 252 |
| | | DGK package | | 172 |
| | | PW package | | 113 |
| T_J | Operating virtual junction temperature | | 150 | °C |
| T_{stg} | Storage temperature range | –65 | 150 | °C |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values (except differential voltages and V_{CC} specified for the measurement of I_{OS}) are with respect to the network GND.
- (3) Differential voltages are at $IN+$ with respect to $IN-$.
- (4) Applies to both single-supply and split-supply operation. Continuous short-circuit operation at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Output currents in excess of 45 mA over long term may adversely affect reliability.
- (5) Maximum power dissipation is a function of $T_J(\text{max})$, θ_{JA} , and T_A . The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_J(\text{max}) - T_A)/\theta_{JA}$. Operating at the absolute maximum T_J of 150°C can affect reliability.
- (6) The package thermal impedance is calculated in accordance with JESD 51-7.

Recommended Operating Conditions

| | | MIN | MAX | UNIT |
|----------|--|-----|-----|------|
| V_{CC} | Supply voltage ($V_{CC+} - V_{CC-}$) | 1.8 | 5 | V |
| T_A | Operating free-air temperature | –40 | 125 | °C |

ESD Protection

| | TYP | UNIT |
|------------------|------|------|
| Human-Body Model | 2000 | V |
| Machine Model | 200 | V |

LMV931 SINGLE, LMV932 DUAL, LMV934 QUAD 1.8-V OPERATIONAL AMPLIFIERS WITH RAIL-TO-RAIL INPUT AND OUTPUT

SLOS441G–AUGUST 2004–REVISED FEBRUARY 2006

Electrical Characteristics

$V_{CC+} = 1.8\text{ V}$, $V_{CC-} = 0\text{ V}$, $V_{IC} = V_{CC+}/2$, $V_O = V_{CC+}/2$, and $R_L > 1\text{ M}\Omega$ (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | | T _A | MIN | TYP | MAX | UNIT | |
|-----------------------------|---|--|--|---------------------------------|------------------------|------------------------|------------------------|-------|------------------------|
| V _{IO} | Input offset voltage | LMV931 (single) | | 25°C | | 1 | 4 | mV | |
| | | | | Full range | | | 6 | | |
| | | LMV932 (dual), LMV934 (quad) | | 25°C | | 1 | 5.5 | | |
| | | | | Full range | | | 7.5 | | |
| α _{V_{IO}} | Average temperature coefficient of input offset voltage | | | 25°C | | 5.5 | | μV/°C | |
| I _{IB} | Input bias current | V _{IC} = V _{CC+} – 0.8 V | | 25°C | | 15 | 35 | nA | |
| | | | | 25°C | | | 65 | | |
| | | | | Full range | | | 75 | | |
| I _{IO} | Input offset current | | | 25°C | | 13 | 25 | nA | |
| | | | | Full range | | | 40 | | |
| I _{CC} | Supply current (per channel) | | | 25°C | | 103 | 185 | μA | |
| | | | | Full range | | | 205 | | |
| CMRR | Common-mode rejection ratio | 0 ≤ V _{IC} ≤ 0.6 V, 1.4 V ≤ V _{IC} ≤ 1.8 V | | 25°C | 60 | 78 | | dB | |
| | | | | –40°C to 85°C | | 55 | | | |
| | | 0.2 ≤ V _{IC} ≤ 0.6 V, 1.4 V ≤ V _{IC} ≤ 1.6 V | | –40°C to 125°C | | 55 | | | |
| | | | | 25°C | | 50 | 72 | | |
| k _{SVR} | Supply-voltage rejection ratio | 1.8 V ≤ V _{CC+} ≤ 5 V, V _{IC} = 0.5 V | | 25°C | 75 | 100 | | dB | |
| | | | | Full range | | 70 | | | |
| V _{ICR} | Common-mode input voltage range | CMRR ≥ 50 dB | | 25°C | V _{CC–} – 0.2 | –0.2 to 2.1 | V _{CC+} + 0.2 | V | |
| | | | | –40°C to 85°C | | V _{CC–} | | | V _{CC+} |
| | | | | –40°C to 125°C | | V _{CC–} + 0.2 | | | V _{CC+} – 0.2 |
| A _V | Large-signal voltage gain | LMV931 | V _O = 0.2 V to 1.6 V, V _{IC} = 0.5 V | R _L = 600 Ω to 0.9 V | 25°C | 77 | 101 | dB | |
| | | | | Full range | | 73 | | | |
| | | | | R _L = 2 kΩ to 0.9 V | 25°C | 80 | 105 | | |
| | | | | | Full range | | 75 | | |
| | | LMV932, LMV934 | | R _L = 600 Ω to 0.9 V | 25°C | 75 | 90 | | |
| | | | | | Full range | | 72 | | |
| | | | | R _L = 2 kΩ to 0.9 V | 25°C | 78 | 100 | | |
| | | | | | Full range | | 75 | | |
| V _O | Output swing | R _L = 600 Ω to 0.9 V, V _{ID} = ±100 mV | High level | 25°C | 1.65 | 1.72 | | V | |
| | | | | Full range | | 1.63 | | | |
| | | | Low level | 25°C | | 0.077 | 0.105 | | |
| | | | | Full range | | | 0.120 | | |
| | | R _L = 2 kΩ to 0.9 V, V _{ID} = ±100 mV | High level | 25°C | 1.75 | 1.77 | | | |
| | | | | Full range | | 1.74 | | | |
| | | | Low level | 25°C | | 0.024 | 0.035 | | |
| | | | | Full range | | | 0.040 | | |
| I _{OS} | Output short-circuit current | V _O = 0 V, V _{ID} = 100 mV | Sourcing | 25°C | 4 | 8 | mA | | |
| | | | | Full range | | 3.3 | | | |
| | | V _O = 1.8 V, V _{ID} = –100 mV | Sinking | 25°C | 7 | 9 | | | |
| | | | | Full range | | 5 | | | |

Electrical Characteristics (continued)

$V_{CC+} = 1.8\text{ V}$, $V_{CC-} = 0\text{ V}$, $V_{IC} = V_{CC+}/2$, $V_O = V_{CC+}/2$, and $R_L > 1\text{ M}\Omega$ (unless otherwise noted)

| | PARAMETER | TEST CONDITIONS | T_A | MIN | TYP | MAX | UNIT |
|----------|---|--|-------|-----|-------|-----|------------------------|
| GBW | Gain bandwidth product | | 25°C | | 1.4 | | MHz |
| SR | Slew rate ⁽¹⁾ | | 25°C | | 0.35 | | V/ μ S |
| Φ_m | Phase margin | | 25°C | | 67 | | ° |
| | Gain margin | | 25°C | | 7 | | dB |
| V_n | Equivalent input noise voltage | $f = 1\text{ kHz}$, $V_{IC} = 0.5\text{ V}$ | 25°C | | 60 | | nV/ $\sqrt{\text{Hz}}$ |
| I_n | Equivalent input noise current | $f = 1\text{ kHz}$ | 25°C | | 0.06 | | pA/ $\sqrt{\text{Hz}}$ |
| THD | Total harmonic distortion | $f = 1\text{ kHz}$, $A_V = 1$, $R_L = 600\ \Omega$, $V_{ID} = 1\text{ V}_{p-p}$ | 25°C | | 0.023 | | % |
| | Amplifier-to-amplifier isolation ⁽²⁾ | | 25°C | | 123 | | dB |

(1) Number specified is the slower of the positive and negative slew rates.

(2) Input referred, $V_{CC+} = 5\text{ V}$ and $R_L = 100\text{ k}\Omega$ connected to 2.5 V. Each amplifier is excited, in turn, with a 1-kHz signal to produce $V_O = 3\text{ V}_{p-p}$.

LMV931 SINGLE, LMV932 DUAL, LMV934 QUAD 1.8-V OPERATIONAL AMPLIFIERS WITH RAIL-TO-RAIL INPUT AND OUTPUT

SLOS441G–AUGUST 2004–REVISED FEBRUARY 2006

Electrical Characteristics

$V_{CC+} = 2.7\text{ V}$, $V_{CC-} = 0\text{ V}$, $V_{IC} = V_{CC+}/2$, $V_O = V_{CC+}/2$, and $R_L > 1\text{ M}\Omega$ (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | | T _A | MIN | TYP | MAX | UNIT | |
|-----------------------------|---|--|---------------------------------|----------------------------------|----------------------------------|------------|------------------------|-------|-----|
| V _{IO} | Input offset voltage | LMV931 (single) | | 25°C | | 1 | 4 | mV | |
| | | | | Full range | | | 6 | | |
| | | LMV932 (dual), LMV934 (quad) | | 25°C | | 1 | 5.5 | | |
| | | | | Full range | | | 7.5 | | |
| α _{V_{IO}} | Average temperature coefficient of input offset voltage | | | 25°C | | 5.5 | | μV/°C | |
| I _{IB} | Input bias current | V _{IC} = V _{CC+} – 0.8 V | | 25°C | | 15 | 35 | nA | |
| | | | | 25°C | | | 65 | | |
| | | | | Full range | | | 75 | | |
| I _{IO} | Input offset current | | | 25°C | | 8 | 25 | nA | |
| | | | | Full range | | | 40 | | |
| I _{CC} | Supply current (per channel) | | | 25°C | | 105 | 190 | μA | |
| | | | | Full range | | | 210 | | |
| CMRR | Common-mode rejection ratio | 0 ≤ V _{IC} ≤ 1.5 V, 2.3 V ≤ V _{IC} ≤ 2.7 V | | 25°C | 60 | 81 | | dB | |
| | | | | –40°C to 85°C | 55 | | | | |
| | | 0.2 ≤ V _{IC} ≤ 1.5 V, 2.3 V ≤ V _{IC} ≤ 2.5 V | | –40°C to 125°C | 55 | | | | |
| | | –0.2 ≤ V _{IC} ≤ 0 V, 2.7 V ≤ V _{IC} ≤ 2.9 V | | 25°C | 50 | 74 | | | |
| k _{SVR} | Supply-voltage rejection ratio | 1.8 V ≤ V _{CC+} ≤ 5 V, V _{IC} = 0.5 V | | 25°C | 75 | 100 | | dB | |
| | | | | Full range | 70 | | | | |
| V _{ICR} | Common-mode input voltage range | CMRR ≥ 50 dB | | 25°C | V _{CC–} – 0.2 | –0.2 to 3 | V _{CC+} + 0.2 | V | |
| | | | | –40°C to 85°C | V _{CC–} | | V _{CC+} | | |
| | | | | –40°C to 125°C | V _{CC–} + 0.2 | | V _{CC+} – 0.2 | | |
| A _V | Large-signal voltage gain | LMV931 | V _O = 0.2 V to 2.5 V | R _L = 600 Ω to 1.35 V | 25°C | 87 | 104 | dB | |
| | | | | | Full range | 86 | | | |
| | | | | R _L = 2 kΩ to 1.35 V | 25°C | 92 | 110 | | |
| | | | | | Full range | 91 | | | |
| | | | | LMV932, LMV934 | R _L = 600 Ω to 1.35 V | 25°C | 78 | | 90 |
| | | | | | | Full range | 75 | | |
| | | | | | R _L = 2 kΩ to 1.35 V | 25°C | 81 | | 100 |
| | | | | | | Full range | 78 | | |
| V _O | Output swing | R _L = 600 Ω to 1.35 V, V _{ID} = ±100 mV | High level | 25°C | 2.55 | 2.62 | V | | |
| | | | | Full range | 2.53 | | | | |
| | | | Low level | 25°C | | 0.083 | | 0.11 | |
| | | | | Full range | | | | 0.13 | |
| | | R _L = 2 kΩ to 1.35 V, V _{ID} = ±100 mV | High level | 25°C | 2.65 | 2.675 | | | |
| | | | | Full range | 2.64 | | | | |
| | | | Low level | 25°C | | 0.025 | | 0.04 | |
| | | | | Full range | | | | 0.045 | |
| I _{OS} | Output short-circuit current | V _O = 0 V, V _{ID} = 100 mV | Sourcing | 25°C | 20 | 30 | mA | | |
| | | | | Full range | 15 | | | | |
| | | V _O = 2.7 V, V _{ID} = –100 mV | Sinking | 25°C | 18 | 25 | | | |
| | | | | Full range | 12 | | | | |
| GBW | Gain bandwidth product | | | 25°C | | 1.4 | | MHz | |

Electrical Characteristics (continued)

$V_{CC+} = 2.7\text{ V}$, $V_{CC-} = 0\text{ V}$, $V_{IC} = V_{CC+}/2$, $V_O = V_{CC+}/2$, and $R_L > 1\text{ M}\Omega$ (unless otherwise noted)

| | PARAMETER | TEST CONDITIONS | T_A | MIN | TYP | MAX | UNIT |
|----------|---|---|-------|-----|-------|-----|------------------------|
| SR | Slew rate ⁽¹⁾ | | 25°C | | 0.4 | | V/ μ S |
| Φ_m | Phase margin | | 25°C | | 70 | | ° |
| | Gain margin | | 25°C | | 7.5 | | dB |
| V_n | Equivalent input noise voltage | $f = 1\text{ kHz}$, $V_{IC} = 0.5\text{ V}$ | 25°C | | 57 | | nV/ $\sqrt{\text{Hz}}$ |
| I_n | Equivalent input noise current | $f = 1\text{ kHz}$ | 25°C | | 0.082 | | pA/ $\sqrt{\text{Hz}}$ |
| THD | Total harmonic distortion | $f = 1\text{ kHz}$, $A_V = 1$, $R_L = 600\text{ }\Omega$, $V_{ID} = 1\text{ V}_{p-p}$ | 25°C | | 0.022 | | % |
| | Amplifier-to-amplifier isolation ⁽²⁾ | | 25°C | | 123 | | dB |

(1) Number specified is the slower of the positive and negative slew rates.

(2) Input referred, $V_{CC+} = 5\text{ V}$ and $R_L = 100\text{ k}\Omega$ connected to 2.5 V. Each amplifier is excited, in turn, with a 1-kHz signal to produce $V_O = 3\text{ V}_{p-p}$.

LMV931 SINGLE, LMV932 DUAL, LMV934 QUAD 1.8-V OPERATIONAL AMPLIFIERS WITH RAIL-TO-RAIL INPUT AND OUTPUT

SLOS441G–AUGUST 2004–REVISED FEBRUARY 2006

Electrical Characteristics

$V_{CC+} = 5\text{ V}$, $V_{CC-} = 0\text{ V}$, $V_{IC} = V_{CC+}/2$, $V_O = V_{CC+}/2$, and $R_L > 1\text{ M}\Omega$ (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | | T _A | MIN | TYP | MAX | UNIT |
|-----------------------------|---|--|---------------------------------|---------------------------------|------------------------|-------------|------------------------|-------|
| V _{IO} | Input offset voltage | LMV931 (single) | | 25°C | | 1 | 4 | mV |
| | | | | Full range | | | 6 | |
| | | LMV932 (dual), LMV934 (quad) | | 25°C | | 1 | 5.5 | |
| | | | | Full range | | | 7.5 | |
| α _{V_{IO}} | Average temperature coefficient of input offset voltage | | | 25°C | | 5.5 | | μV/°C |
| I _{IB} | Input bias current | V _{IC} = V _{CC+} – 0.8 V | | 25°C | | 15 | 35 | nA |
| | | | | 25°C | | | 65 | |
| | | | | Full range | | | 75 | |
| I _{IO} | Input offset current | | | 25°C | | 9 | 25 | nA |
| | | | | Full range | | | 40 | |
| I _{CC} | Supply current (per channel) | | | 25°C | | 116 | 210 | μA |
| | | | | Full range | | | 230 | |
| CMRR | Common-mode rejection ratio | 0 ≤ V _{IC} ≤ 3.8 V, 4.6 V ≤ V _{IC} ≤ 5 V | | 25°C | 60 | 86 | | dB |
| | | | | –40°C to 85°C | 55 | | | |
| | | 0.3 ≤ V _{IC} ≤ 3.8 V, 4.6 V ≤ V _{IC} ≤ 4.7 V | | –40°C to 125°C | 55 | | | |
| | | –0.2 ≤ V _{IC} ≤ 0 V, 5 V ≤ V _{IC} ≤ 5.2 V | | 25°C | 50 | 78 | | |
| k _{SVR} | Supply-voltage rejection ratio | 1.8 V ≤ V _{CC+} ≤ 5 V, V _{IC} = 0.5 V | | 25°C | 75 | 100 | | dB |
| | | | | Full range | 70 | | | |
| V _{ICR} | Common-mode input voltage range | CMRR ≥ 50 dB | | 25°C | V _{CC–} – 0.2 | –0.2 to 5.3 | V _{CC+} + 0.2 | V |
| | | | | –40°C to 85°C | V _{CC–} | | V _{CC+} | |
| | | | | –40°C to 125°C | V _{CC–} + 0.3 | | V _{CC+} – 0.3 | |
| A _V | Large-signal voltage gain | LMV931 | V _O = 0.2 V to 4.8 V | R _L = 600 Ω to 2.5 V | 25°C | 88 | 102 | dB |
| | | | | | Full range | 87 | | |
| | | | | R _L = 2 kΩ to 2.5 V | 25°C | 94 | 113 | |
| | | | | | Full range | 93 | | |
| | | | | R _L = 600 Ω to 2.5 V | 25°C | 81 | 90 | |
| | | | | | Full range | 78 | | |
| | | | | R _L = 2 kΩ to 2.5 V | 25°C | 85 | 100 | |
| | | | | | Full range | 82 | | |
| V _O | Output swing | R _L = 600 Ω to 2.5 V, V _{ID} = ±100 mV | High level | 25°C | 4.855 | 4.89 | V | |
| | | | | Full range | 4.835 | | | |
| | | | Low level | 25°C | | 0.12 | | 0.16 |
| | | | | Full range | | | | 0.18 |
| | | R _L = 2 kΩ to 2.5 V, V _{ID} = ±100 mV | High level | 25°C | 4.945 | 4.967 | | |
| | | | | Full range | 4.935 | | | |
| | | | Low level | 25°C | | 0.037 | | 0.065 |
| | | | | Full range | | | | 0.075 |
| I _{OS} | Output short-circuit current | V _O = 0 V, V _{ID} = 100 mV | Sourcing | 25°C | 80 | 100 | mA | |
| | | | | Full range | 68 | | | |
| | | V _O = 5 V, V _{ID} = –100 mV | Sinking | 25°C | 58 | 65 | | |
| | | | | Full range | 45 | | | |

Electrical Characteristics (continued)

$V_{CC+} = 5\text{ V}$, $V_{CC-} = 0\text{ V}$, $V_{IC} = V_{CC+}/2$, $V_O = V_{CC+}/2$, and $R_L > 1\text{ M}\Omega$ (unless otherwise noted)

| | PARAMETER | TEST CONDITIONS | T_A | MIN | TYP | MAX | UNIT |
|----------|---|--|-------|-----|-------|-----|------------------------|
| GBW | Gain bandwidth product | | 25°C | | 1.5 | | MHz |
| SR | Slew rate ⁽¹⁾ | | 25°C | | 0.42 | | V/ μ S |
| Φ_m | Phase margin | | 25°C | | 71 | | ° |
| | Gain margin | | 25°C | | 8 | | dB |
| V_n | Equivalent input noise voltage | $f = 1\text{ kHz}$, $V_{IC} = 0.5\text{ V}$ | 25°C | | 50 | | nV/ $\sqrt{\text{Hz}}$ |
| I_n | Equivalent input noise current | $f = 1\text{ kHz}$ | 25°C | | 0.07 | | pA/ $\sqrt{\text{Hz}}$ |
| THD | Total harmonic distortion | $f = 1\text{ kHz}$, $A_V = 1$, $R_L = 600\text{ }\Omega$, $V_{ID} = 1\text{ V}_{p-p}$ | 25°C | | 0.022 | | % |
| | Amplifier-to-amplifier isolation ⁽²⁾ | | 25°C | | 123 | | dB |

(1) Number specified is the slower of the positive and negative slew rates.

(2) Input referred, $V_{CC+} = 5\text{ V}$ and $R_L = 100\text{ k}\Omega$ connected to 2.5 V. Each amplifier is excited, in turn, with a 1-kHz signal to produce $V_O = 3\text{ V}_{p-p}$.

LMV931 SINGLE, LMV932 DUAL, LMV934 QUAD 1.8-V OPERATIONAL AMPLIFIERS WITH RAIL-TO-RAIL INPUT AND OUTPUT

SLOS441G–AUGUST 2004–REVISED FEBRUARY 2006

TYPICAL CHARACTERISTICS

$V_{CC+} = 5\text{ V}$, Single Supply, $T_A = 25^\circ\text{C}$ (unless otherwise specified)




Figure 1.




Figure 2.




Figure 3.




Figure 4.

TYPICAL CHARACTERISTICS (continued)

$V_{CC+} = 5\text{ V}$, Single Supply, $T_A = 25^\circ\text{C}$ (unless otherwise specified)




Figure 5.




Figure 6.




Figure 7.




Figure 8.

LMV931 SINGLE, LMV932 DUAL, LMV934 QUAD 1.8-V OPERATIONAL AMPLIFIERS WITH RAIL-TO-RAIL INPUT AND OUTPUT

SLOS441G–AUGUST 2004–REVISED FEBRUARY 2006

TYPICAL CHARACTERISTICS (continued)

$V_{CC+} = 5\text{ V}$, Single Supply, $T_A = 25^\circ\text{C}$ (unless otherwise specified)




Figure 9.




Figure 10.

TYPICAL CHARACTERISTICS (continued)

$V_{CC+} = 5\text{ V}$, Single Supply, $T_A = 25^\circ\text{C}$ (unless otherwise specified)




Figure 11.




Figure 12.

LMV931 SINGLE, LMV932 DUAL, LMV934 QUAD 1.8-V OPERATIONAL AMPLIFIERS WITH RAIL-TO-RAIL INPUT AND OUTPUT

SLOS441G–AUGUST 2004–REVISED FEBRUARY 2006

TYPICAL CHARACTERISTICS (continued)

$V_{CC+} = 5\text{ V}$, Single Supply, $T_A = 25^\circ\text{C}$ (unless otherwise specified)




Figure 13.




Figure 14.




Figure 15.




Figure 16.

TYPICAL CHARACTERISTICS (continued)

$V_{CC+} = 5\text{ V}$, Single Supply, $T_A = 25^\circ\text{C}$ (unless otherwise specified)




Figure 17.




Figure 18.




Figure 19.




Figure 20.

LMV931 SINGLE, LMV932 DUAL, LMV934 QUAD 1.8-V OPERATIONAL AMPLIFIERS WITH RAIL-TO-RAIL INPUT AND OUTPUT

SLOS441G–AUGUST 2004–REVISED FEBRUARY 2006

TYPICAL CHARACTERISTICS (continued)

$V_{CC+} = 5\text{ V}$, Single Supply, $T_A = 25^\circ\text{C}$ (unless otherwise specified)




Figure 21.




Figure 22.




Figure 23.




Figure 24.

TYPICAL CHARACTERISTICS (continued)

$V_{CC+} = 5\text{ V}$, Single Supply, $T_A = 25^\circ\text{C}$ (unless otherwise specified)




Figure 25.

PACKAGING INFORMATION

| Orderable Device | Status ⁽¹⁾ | Package Type | Package Drawing | Pins | Package Qty | Eco Plan ⁽²⁾ | Lead/Ball Finish | MSL Peak Temp ⁽³⁾ |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| LMV931IDBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV931IDBVR E4 | ACTIVE | SOT-23 | DBV | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV931IDBVR G4 | ACTIVE | SOT-23 | DBV | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV931IDCKR | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV931IDCKR E4 | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV931IDCKR G4 | ACTIVE | SC70 | DCK | 5 | 3000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV932ID | ACTIVE | SOIC | D | 8 | 75 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV932ID E4 | ACTIVE | SOIC | D | 8 | 75 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV932ID G4 | ACTIVE | SOIC | D | 8 | 75 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV932IDGKR | ACTIVE | MSOP | DGK | 8 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV932IDGKR G4 | ACTIVE | MSOP | DGK | 8 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV932IDR | ACTIVE | SOIC | D | 8 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV932IDR E4 | ACTIVE | SOIC | D | 8 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV932IDR G4 | ACTIVE | SOIC | D | 8 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934ID | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934ID E4 | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934ID G4 | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934IDR | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934IDR E4 | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934IDR G4 | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934IPW | ACTIVE | TSSOP | PW | 14 | 90 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934IPW E4 | ACTIVE | TSSOP | PW | 14 | 90 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934IPW G4 | ACTIVE | TSSOP | PW | 14 | 90 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934IPWR | ACTIVE | TSSOP | PW | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| LMV934IPWR E4 | ACTIVE | TSSOP | PW | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |

| Orderable Device | Status ⁽¹⁾ | Package Type | Package Drawing | Pins | Package Qty | Eco Plan ⁽²⁾ | Lead/Ball Finish | MSL Peak Temp ⁽³⁾ |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| LMV934IPWRG4 | ACTIVE | TSSOP | PW | 14 | 2000 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSELETE: TI has discontinued the production of the device.

⁽²⁾ Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF LMV931 :

- Automotive: [LMV931-Q1](#)

NOTE: Qualified Version Definitions:


- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

TAPE AND REEL INFORMATION


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LMV931IDBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| LMV931IDBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 9.2 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| LMV931IDCKR | SC70 | DCK | 5 | 3000 | 180.0 | 9.2 | 2.24 | 2.34 | 1.22 | 4.0 | 8.0 | Q3 |
| LMV932IDGKR | MSOP | DGK | 8 | 2500 | 330.0 | 12.4 | 5.3 | 3.4 | 1.4 | 8.0 | 12.0 | Q1 |
| LMV932IDGKR | MSOP | DGK | 8 | 2500 | 330.0 | 12.4 | 5.3 | 3.3 | 1.3 | 8.0 | 12.0 | Q1 |
| LMV932IDR | SOIC | D | 8 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| LMV934IDR | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| LMV934IPWR | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 7.0 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |

TAPE AND REEL BOX DIMENSIONS




*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LMV931IDBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| LMV931IDBVR | SOT-23 | DBV | 5 | 3000 | 205.0 | 200.0 | 33.0 |
| LMV931IDCKR | SC70 | DCK | 5 | 3000 | 205.0 | 200.0 | 33.0 |
| LMV932IDGKR | MSOP | DGK | 8 | 2500 | 358.0 | 335.0 | 35.0 |
| LMV932IDGKR | MSOP | DGK | 8 | 2500 | 370.0 | 355.0 | 55.0 |
| LMV932IDR | SOIC | D | 8 | 2500 | 340.5 | 338.1 | 20.6 |
| LMV934IDR | SOIC | D | 14 | 2500 | 346.0 | 346.0 | 33.0 |
| LMV934IPWR | TSSOP | PW | 14 | 2000 | 346.0 | 346.0 | 29.0 |

DBV (R-PDSO-G5)

PLASTIC SMALL-OUTLINE PACKAGE




- NOTES:
- All linear dimensions are in millimeters.
 - This drawing is subject to change without notice.
 - Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.
 - Falls within JEDEC MO-178 Variation AA.

PW (R-PDSO-G**)

PLASTIC SMALL-OUTLINE PACKAGE


14 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.
 B. This drawing is subject to change without notice.
 C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.
 D. Falls within JEDEC MO-153

DCK (R-PDSO-G5)

PLASTIC SMALL-OUTLINE PACKAGE




4093553-3/G 01/2007

- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.15 per side.
 - D. Falls within JEDEC MO-203 variation AA.

D (R-PDSO-G14)


PLASTIC SMALL-OUTLINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 (0,15) per end.
 - D. Body width does not include interlead flash. Interlead flash shall not exceed .017 (0,43) per side.
 - E. Reference JEDEC MS-012 variation AB.

DGK (S-PDSO-G8)


PLASTIC SMALL-OUTLINE PACKAGE



- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 per end.
 - D. Body width does not include interlead flash. Interlead flash shall not exceed 0.50 per side.
 - E. Falls within JEDEC MO-187 variation AA, except interlead flash.

D (R-PDSO-G8)

PLASTIC SMALL-OUTLINE PACKAGE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 (0,15) per end.
 - D. Body width does not include interlead flash. Interlead flash shall not exceed .017 (0,43) per side.
 - E. Reference JEDEC MS-012 variation AA.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

| | |
|-----------------------------|--|
| Amplifiers | amplifier.ti.com |
| Data Converters | dataconverter.ti.com |
| DLP® Products | www.dlp.com |
| DSP | dsp.ti.com |
| Clocks and Timers | www.ti.com/clocks |
| Interface | interface.ti.com |
| Logic | logic.ti.com |
| Power Mgmt | power.ti.com |
| Microcontrollers | microcontroller.ti.com |
| RFID | www.ti-rfid.com |
| RF/IF and ZigBee® Solutions | www.ti.com/lprf |

Applications

| | |
|--------------------|--|
| Audio | www.ti.com/audio |
| Automotive | www.ti.com/automotive |
| Broadband | www.ti.com/broadband |
| Digital Control | www.ti.com/digitalcontrol |
| Medical | www.ti.com/medical |
| Military | www.ti.com/military |
| Optical Networking | www.ti.com/opticalnetwork |
| Security | www.ti.com/security |
| Telephony | www.ti.com/telephony |
| Video & Imaging | www.ti.com/video |
| Wireless | www.ti.com/wireless |

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2009, Texas Instruments Incorporated