

## OSS10-IDW



## OSS10-IDW

### Brand Features

OSS10 is perfect for use in hospitality and health care facilities with night light feature to guide to manual-ON. The adjustable time delay settings of 30 seconds to 30 minutes will automatically turn lights OFF.

### Item Description

Discontinued Product. Product Line: OSS10, Technology: Passive Infrared, Switch Type: Single-Pole, LED NightLight, Device Type: Occupancy Sensor, Coverage (Sq.Ft.): 1200 Sq. Ft., Voltage: 120/277 Volt AC 60Hz, Pattern: 180°, Color: White, Neutral Wire Connection: Required, Warranty: 5-Year Limited

### Technical Information

#### Product Features

**Power Pack:** External Power Pack Not Required

**Relative Humidity:** 20% to 90% non-condensing

**Size:** 4.06" H x 1.75" W x 1.85" D (103.2mm x 44.4mm x 47.2mm)

**Coverage (Sq.Ft.):** 1200 Sq. Ft.

**Technology:** Passive Infrared

**Voltage:** 120/277 Volt AC 60Hz

**Storage Temperature Range:** -10°C to 85°C

**Time Delay:** 30s-30m

**Photocell:** Internal

**Code Compliance:** California Title 24

**HVAC Relay:** N/A

**Pattern:** 180°

**Operating Temperature:** 0°C to 40°C

**Warranty:** 5-Year Limited

**Adjustment:** Manual

**Motor:** 1/8 HP @ 120V

**Color:** White

**LED Color:** Red

**Switch Type:** Single-Pole, LED NightLight

**Device Type:** Occupancy Sensor

**Grade:** Commercial

**Mounting Height (Ft.):** 4 Ft.

**Neutral Wire Connection:** Required

**Mounting:** Wall Switch

**Wallplate:** Order Separately


**Load Rating:** 800W@120V INC 1200VA@120V 2700VA@277V FL

**Consumption (mA):** N/A

**Standards and Certifications:** UL/cUL

**Product Line:** OSS10

Color:



White

## Features and Benefits

- Manual On Only (30min max Time Delay).
- Exclusive dual PIR design provides unmatched range and small motion detection.
- Manual-ON/Auto-OFF operation
- Convenient push-button provides manual ON/OFF light switching at any time
- LED NightLight offers "Guide Light" functionality
- Adjustable NightLight illumination
- Setting for continuous or dimmed NightLight
- Proprietary segmented Fresnel lens provides optimum sensitivity and performance. Designed with an extensive "small motion" area where even the slight body movements will be detected
- Horizontal field-of-view may be adjusted between 180 and 32 32 degrees of arc by using internal blenders located on either side of the lens
- One unit can be used for either 120V or 277V lighting compatible with both electronic and magnetic ballasts
- Relay switches at the zero crossing point of the AC power curve to ensure maximum contact life and compatibility with electronic ballasts
- Fits in a standard wallbox and replaces single-pole wall switch; ground and neutral connection required. Gangable with other units
- CEC 24 Compliant Vacancy Sensor wall switch with NightLight

## SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/> <input type="text"/> <input type="text"/> <input type="text"/>		
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>

### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 · FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · [www.leviton.com.mx](http://www.leviton.com.mx)



### Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:  
[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)