




FEATURES


- Standard 2.5mm x 2.0mm Seam Weld Package
- Fundamental Crystal Design
- Frequency Range 12 – 60MHz
- Frequency Tolerance, $\pm 20\text{ppm}$ Standard
- Frequency Stability, $\pm 20\text{ppm}$ Standard
- Operating Temperature to -40°C to $+85^{\circ}\text{C}$
- Tape & Reel Packaging Standard, EIA-481
- RoHS/Green Compliant [6/6]



APPLICATIONS

Model 425 is a low cost quartz resonator used in a wide range of commercial applications including wearable and handheld electronics, notebooks, tablets, computer peripherals, Bluetooth, ZigBee and USB interfaces.

ORDERING INFORMATION




- 2] There are frequencies that have significant digits after the 'M' that exceed the 4 digits. The remaining digits will be truncated from the CTS part number, but the factory will calibrate to the full frequency desired. Ex. P.N Frequency = Actual Frequency
- | | | | |
|-------------------------|-------------------------|-------------------------|-------------------------|
| 13M5537 = 13.553750 MHz | 14M3381 = 14.318100 MHz | 16M6666 = 16.666670 MHz | 28M6363 = 28.636360 MHz |
|-------------------------|-------------------------|-------------------------|-------------------------|

Not all performance combinations and frequencies may be available.
Contact your local CTS Representative or CTS Customer Service for availability.

PACKAGING INFORMATION [Reference]

Device quantity is 3k pieces per 180mm reel.




ELECTRICAL CHARACTERISTICS

ELECTRICAL PARAMETERS	PARAMETER	VALUE
	Frequency Range	12MHz to 60MHz
	Operating Mode	Fundamental
	Crystal Cut	AT-Cut
	Frequency Tolerance @ +25°C	±20ppm, Standard
	Frequency Stability Tolerance [Operating Temperature Range, Referenced to +25°C Reading]	±20ppm, Standard
	Operating Temperature Ranges	-20°C to +70°C
		-30°C to +85°C -40°C to +85°C
	Equivalent Series Resistance [Maximum]	12MHz - <20MHz 120 Ohms
		20MHz - <30MHz 80 Ohms
		30MHz - <36MHz 60 Ohms
		36MHz - 60MHz 50 Ohms
	Load Capacitance	See Ordering Information
	Shunt Capacitance [C ₀]	3.0pF Typical, 5.0pF Maximum
	Drive Level	10µW Typ., 200µW Max.
	Aging @ +25°C	±3ppm/yr Typical
	Insulation Resistance	500M Ohms @ DC 100V
	Storage Temperature Range	-40°C to +90°C

MECHANICAL SPECIFICATIONS

PACKAGE DRAWING



MARKING INFORMATION

1. XX.XX – Frequency in MHz.
2. C – CTS and Pin 1 identifier.
3. ** – Manufacturing Site Code.
4. D – Date code. See Table I for codes.

NOTES

1. Complete CTS part number, frequency value, date code and manufacturing site code information must appear on reel and carton labels.
2. Terminations #2, #4 and the metal lid are connected internally. End user may connect these pins to circuit ground for EMI suppression.
3. Termination pads (e4); barrier plating is nickel [Ni] with gold [Au] flash plate.
4. Reflow conditions per JEDEC J-STD-020; +260°C maximum, 10 seconds.
5. MSL = 1.

SUGGESTED SOLDER PAD GEOMETRY




TABLE I – DATE CODE

YEAR \ MONTH					JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC
2001	2005	2009	2013	2017	A	B	C	D	E	F	G	H	J	K	L	M
2002	2006	2010	2014	2018	N	P	Q	R	S	T	U	V	W	X	Y	Z
2003	2007	2011	2015	2019	a	b	c	d	e	f	g	h	j	k	l	m
2004	2008	2012	2016	2020	n	p	q	r	s	t	u	v	w	x	y	z