

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0573113000

Status:

Active

Overview:

Application Tooling

Description:

Applicator for M211A Bench Press, 26-28 AWG Wire

- Documents:
- Tooling Manual (PDF)

Tooling Specification (PDF)

Tooling Specification (PDF)

Tooling Manual (PDF)

Tooling Parts List (PDF)

RoHS Certificate of Compliance (PDF)

Tooling Parts List (PDF)

General	
Product Family	Application Tooling
Series	57311
Function	Crimp
Geographic Area	Japan
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Applicator
UPC	800753480377
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

394_57311-3000, 477_57311-3000, 846_MCD, ATP-57311-3000E, ATP=57311-3000JE



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Not Reviewed

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

57311 Series

Use With

57275-4000 Molex M211A, most Industry Standard Presses, or Wire Process Machines.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION