

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

LOC	DIST	REVISIONS		
		P	LTR	DESCRIPTION
GP	00	A		RELEASE PER RTS 90046


04/DEC/07 ECC JO



1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF
TYCO ELECTRONICS STANDARD 230-702.

2. HIROSE COMPATIBLE, 2.5 mm MATING HEIGHT.
UMCC CONNECTOR, TYPE III

3. CABLE ASSEMBLY TO BE 100% ELECTRICALLY TESTED
FOR OPENS, SHORTS AND CONTINUITY.
HI-POT AT 150 VDC FOR 100mS
VSWR: 1.5:1 MAX.



2032442-1

TYCO ELECTRONICS P/N

A/R	MR	TUBING, HEAT SHRINK	3
1	PC	MCX, R/A, PLUG	2
1	PC	UMCC, PLUG [1.37mm CABLE]	1
-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28/NOV/07 E. C. CLAYBAUGH	Tyco Electronics Corporation		
DIMENSIONS:		CHK 04/DEC/07 J. ORNER	Harrisburg, PA 17105-3608		
mm [INCHES]		APVD 04/DEC/07 J. ORNER	NAME		
 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC —	CABLE ASSY, RF, UMCC PLUG TO MCX R/A PLUG [1.37mm CABLE]		
MATERIAL -		APPLICATION SPEC —	SIZE CAGE CODE DRAWING NO A3 00779 C-2032442		
FINISH -		WEIGHT —	RESTRICTED TO —		
CUSTOMER DRAWING		SCALE N.T.S.	SHEET 1 OF 1		REV A