







11. THE PARTS ARE RECOMMENDED FOR WAVE SOLDERING PROCESS,  
PEAK TEMPERATURE 260°C MAX, 10 SECONDS MAX.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG 16NOV2010 JAMISON CHEN/KC/10 CHK 16NOV2010 TONY YUAN APP'D KEITH ZHU 16NOV2010		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±		NAME 2X1 MAG45(TM),GIGABIT S8G56 CIRCUIT GROUND SHIELD, WITH LEADS	
		PRODUCT SPEC 108-104004 APPLICATION SPEC		SIZE CASE CODE DRAWING NO A1 00779 ©=1840855	
MATERIAL -		FINISH -		RESTRICTED TO -	
		WEIGHT -		SCALE 4 SHEET 1 OF 4 REV C	
CUSTOMER DRAWING					


LOC	DIST	REVISONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
-	-	SEE SHEET 1	-	-	-	




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JAMISON CHEN/0011 CHK: TONY YUAN APVD: KEITH ZHU	16NOV2010 16NOV2010 16NOV2010	NAME: 2X1 MAG45(TM), GIGABIT S8G56 CIRCUIT GROUND SHIELD, WITH LEDS	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH	± ± ±0.25 ± ± ± -	PRODUCT SPEC 108-104004 APPLICATION SPEC	SIZE: A1
MATERIAL				WEIGHT	SCALE: 4
					SHEET: 2
					OF: 4
					REV: C
					RESTRICTED TO: -
					CAGE CODE: 00779
					DRAWING NO: 1840855
					CUSTOMER DRAWING




Technical drawing of a mechanical part showing a cross-section. The drawing includes dimensions: 1.00 (height of the base), 3.58 (width of the base), and 18.59 (total width of the part). The part features a central slot and two circular features on the top surface. A vertical dashed line indicates a centerline. A note "IT IS RECOMMENDED" points to a specific feature.

RECOMMENDED PCB LAYOUT  
COMPONENT SIDE VIEW


SUGGESTED PANEL CUTOUT DIMENSIONS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16NOV2010 JAMISON CHEN/KO 1		 TE Connectivity	
DIMENSIONS:		CHE 16NOV2010 TONY ZHANG			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APRD		NAME	
mm	0 P L C ± 1 P L C ±0.25 2 P L C ± 3 P L C ± 4 P L C ± ANGLES ±	KEITH ZHANG PRODUCT SPEC 108-104004 APPLICATION SPEC - - -		2X1 MAG45(TM), GIGABIT S8G56 CIRCUIT GROUND SHIELD, WITH LEADS	
MATERIAL	FINISH	WEIGHT	SIZE CODE A1 00779		DRAWING NO C-1840855
CUSTOMER DRAWING			SCALE SHEET 3 OF 4 REV C		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00	-		SEE SHEET 1	-	-	-




LED HOLE DESIGNATIONS  
VIEWED FROM COMPONENT SIDE




PORT ASSIGNMENT  
COMPONENT SIDE VIEW


SINGLE COLOR LED



BI-COLOR LED



BI-COLOR LED



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JAMISON CHEN/KQ 11 CHK TONY YUAN 16NOV2010	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±	NAME APVD KEITH ZHU 16NOV2010	PRODUCT SPEC 108-104004 APPLICATION SPEC
MATERIAL -		FINISH -	WEIGHT -	SIZE A1
CUSTOMER DRAWING		SCALE 4	SHEET 4	OF 4
		REV C	RESTRICTED TO -	