





8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

#	DATE	DESCRIPTION	DATE	OWN	APPRO
—	—	SEE SHEET 1	—	—	—

1

HOUSING MATERIAL: THERMOPLASTIC, COLOR—NATURAL.

2

CONTACT MATERIAL: COPPER ALLOY.

3

FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108—9063; BASED ON TELCORDIA DR—1217—CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
SOLDER TAILS AREA: TIN—LEAD PLATED.

4

SOLDER TAILS MUST FIT HOLE PATTERN AS SHOWN ON THE RECOMMENDED P.C. BOARD LAYOUT.

5

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

HOUSINGS WITH CENTER MOUNTING IS RECOMMENDED FOR ASSEMBLIES HAVING 75 CONTACTS PER ROW OR MORE.

7

PART NUMBER IS OBSOLETE.

8

FINISH:
CONTACT FINISH: .00127—.00254 [.000050—.000100] NICKEL
UNDERPLATE ALL OVER; .000762 [.000030] GOLD PLATE IN CONTACT AREA, TIN—LEAD PLATED POSTS.

8	149.86 [5.900]	59	153.01 [6.024]	163.83 [6.450]	171.45 [6.750]	180	3—533268—9
8	124.46 [4.900]	49	127.61 [5.024]	138.43 [5.450]	146.05 [5.750]	150	3—533268—7
8	99.06 [3.900]	39	102.21 [4.024]	113.03 [4.450]	120.65 [4.750]	120	3—533268—5
7	22.86 [.900]	—9—	26.01 [1.024]	36.83 [1.450]	44.45 [1.750]	—30—	2—533268—0
	81.28 [3.200]	32	84.43 [3.324]	95.25 [3.750]	102.87 [4.050]	99	1—533268—9
7	144.78 [5.700]	—57—	147.93 [5.824]	158.75 [6.250]	166.37 [6.550]	—74—	1—533268—8
6 7	251.46 [9.900]	—99—	254.61 [10.024]	265.43 [10.450]	273.05 [10.750]	—300—	1—533268—7
6 7	238.76 [9.400]	—94—	241.91 [9.524]	252.73 [9.950]	260.35 [10.250]	—285—	1—533268—6
6	226.06 [8.900]	89	229.21 [9.024]	240.03 [9.450]	247.65 [9.750]	270	1—533268—5
6 7	213.36 [8.400]	—84—	216.51 [8.524]	227.33 [8.950]	234.95 [9.250]	—255—	1—533268—4
6	200.66 [7.900]	79	203.81 [8.024]	214.63 [8.450]	222.25 [8.750]	240	1—533268—3
	187.96 [7.400]	74	191.11 [7.524]	201.93 [7.950]	209.55 [8.250]	225	1—533268—2
7	175.26 [6.900]	—69—	178.41 [7.024]	189.23 [7.450]	196.85 [7.750]	—240—	1—533268—1
7	162.56 [6.400]	—64—	165.71 [6.524]	176.53 [6.950]	184.15 [7.250]	—495—	1—533268—0
	149.86 [5.900]	59	153.01 [6.024]	163.83 [6.450]	171.45 [6.750]	180	533268—9
	137.16 [5.400]	54	140.31 [5.524]	151.13 [5.950]	158.75 [6.250]	165	533268—8
	124.46 [4.900]	49	127.61 [5.024]	138.43 [5.450]	146.05 [5.750]	150	533268—7
	111.76 [4.400]	44	114.91 [4.524]	125.73 [4.950]	133.35 [5.250]	135	533268—6
	99.06 [3.900]	39	102.21 [4.024]	113.03 [4.450]	120.65 [4.750]	120	533268—5
	86.36 [3.400]	34	89.51 [3.524]	100.33 [3.950]	107.95 [4.250]	105	533268—4
	78.74 [3.100]	31	81.89 [3.224]	92.71 [3.650]	100.33 [3.950]	96	533268—3
7	73.66 [2.900]	—29—	76.81 [3.024]	87.63 [3.450]	95.25 [3.750]	—90—	533268—2
8	60.96 [2.400]	24	64.11 [2.524]	74.93 [2.950]	82.55 [3.250]	75	533268—1
	E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± 0.13 [.005]

4 PLC ± —

ANGLES ± —

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± 0.13 [.005]

4 PLC ± —

ANGLES ± —

MATERIAL

1

2

FINISH

3

8

WEIGHT

0

CUSTOMER DRAWING

OWN
R.K. SEIFRIED
CHK
G. SKIPPER
APPRO
G. SKIPPER

06/18/90
10/6/92
10/6/92

TE Connectivity

NAME
HDI, 3 ROW, RECEPTACLE ASSEMBLY,
3.05 [.120] LONG SOLDER TAILS
—

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=533268

RESTRICTED TO
—

SCALE
4:1

SHEET
2

OF
2

REV
P

4805 (1/15)