

**Mallory Sonalert Products, Inc.**




Part #:

MSR516XR**Sales Outline Drawing**

Revision:

C**Specifications: OBSOLETE- SEE MSE14LSN2**

Sound Level Category	LOU
Mode of Operation	Siren Tone (2-4 Hz Sweep)
Voltage Rating	5 to 16 VDC
Frequency	3400 ± 400 Hz
Loudness @ 1 FT	82 to 91 dB(A) Typ.
Current Draw	3-12 mA
Housing Material	Valox (UL94V-0), Color Blue
Storage Temperature	-30° to +80° C
Operating Temperature	-20° to +65° C
Weight (Typical)	3.5g
Options	Please contact factory.

Dimensions: Inches (mm)**ROHS Compliant**EMISSION HOLE
Ø .120±.005 [3.0±0.1]

NOTE A:
TERMINALS - .031" DIA. NICKEL/TIN COATED BRASS.

NOTE B:
MOUNTING- INSERT INTO PRINTED CIRCUIT BOARD AND HAND OR MACHINE SOLDER.
UNITS ARE SUITABLE FOR WAVE SOLDERING. RECOMMENDED MAXIMUM TEMPERATURE
AND TIME DURATION FOR WAVE SOLDERING IS +270°C AND 3 SECONDS RESPECTIVELY.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[MSR516XR](#)