




(2.00 mm) .0787"

TSH, TMMS SERIES

SHROUDED HEADERS

Mates with:

CLT, SQT, SQW, ESQT,
TLE, SMM, MMS, PTF

SPECIFICATIONS

For complete specifications and
recommended PCB layouts
see www.samtec.com?TSH**Insulator Material:**
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze

Plating:

Sn or Au over
50 μ " (1.27 μ m) Ni


Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold
RoHS Compliant: Yes

PROCESSING

Lead-Free Solderable: Yes
SMT Lead Coplanarity:(0.15 mm) .006" max*
*(.004" stencil solution
may be available; contact
IPG@samtec.com)

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality**Note:**
Some lengths, styles and options
are non-standard, non-returnable.

ALSO AVAILABLE (MOQ Required)

- Other sizes and platings

Mates with:

SQT, SQW, ESQT

SPECIFICATIONS

For complete specifications
see www.samtec.com?TMMS**Insulator Material:**
Black LCP**Terminal Material:**
Phosphor Bronze

Plating:

Sn or Au over
50 μ " (1.27 μ m) Ni


Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold
RoHS Compliant: Yes**Lead-Free Solderable:** Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality

Note:

Some lengths, styles and
options are non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.