


Registration Sensor -Slotted

E3XR-GM

Grooved Head Sensor Ideal
for Register Mark Detection
in Printing and Packaging Equipment

- Green or red light source according to color mark
- Fast response time, less than 1 ms
- Sensitivity adjuster and stability indicator allow fine tuning
- Switch selectable Light-ON/Dark-ON operation
- Pre-leaded with 2 m (6.6 ft) cable



Ordering Information

■ SENSORS

Light source color		Red LED	Green LED
Part number	NPN output	E3XR-GM5RE4	E3XR-GM5GE4
	PNP output	E3XR-GM5RB4	E3XR-GM5GB4

■ ACCESSORIES


Description		Part number
Mounting track	DIN rail, 50 cm (1.64 ft) length	PFP-50N
	DIN rail, 1 m (3.28 ft) length	PFP-100N
	End plate	PFP-M
	Spacer	PFP-S

■ REPLACEMENT PARTS

Description	Part number
Mounting bracket (supplied with each sensor)	E39-L48

■ TYPICAL APPLICATION

Detecting marks on transparent film




Specifications

Part number			E3XR-GM5R□4	E3XR-GM5G□4
Supply voltage			12 to 24 VDC ± 10% with 10% max. permissible ripple peak-to-peak	
Method of detection			Through beam type mounted in a grooved head	
Current consumption			40 mA max.	
Sensing distance			5 mm (0.197 in) groove width	
Light source			Red LED, pulse modulated	Green LED, pulse modulated
Detectable object type			Marks of 2 x 3 mm (0.079 x 0.118 in) min. on transparent film	
Operation mode			Light-ON/Dark-ON, switch selectable	
Sensitivity			Adjustable, four-turn potentiometer	
Mutual interference protection			Provided	
Control output	DC solid state	Type	NPN with current source (E3XR-GM5□E4) PNP (E3XR-GM5□B4)	
		Max. load	NPN: Load (sink) logic: 80 mA max. Voltage (source) logic: 1.5 to 4 mA max. PNP: Load (source) logic: 100 mA max.	
		Max. on-state voltage drop	1 VDC at 80 mA	
Response time		ON	0.5 ms max.	1 ms max.
		OFF	0.5 ms max.	1 ms max.
Circuit protection			Short-circuit and reverse polarity protection	
Indicators			Light Incident (red LED), Output Stability (green LED)	
Materials		Lens	Plastic	
		Case	Plastic	
		Cable sheath	Vinyl	
Mounting			Two 3.2 mm dia. side through holes, DIN rail track mount or E39-L48 mounting bracket included	
Connections		Prewired	3-conductor cable, 2 m (6.56 ft) length	
Weight			Approx. 80 g (3 oz.)	
Enclosure ratings		IEC 144	IP65	
Standards conformance			IEC 947-5-2	
Ambient temperature		Operating	-25° to 55° C (-13° to 131°F)	
		Storage	-25° to 70° C (-13° to 158°F)	

■ OUTPUT CIRCUIT DIAGRAMS

NPN output E3XR-GM5□E4



Note: IEC colors are shown in parentheses.

Red (Brown) +12 to 24 VDC

White (Black)

Black (Blue) 0 V

2.2 Ω

Z_p

$Z_p: V_z = 30 V$

Photo - electric switch circuit

Load (relay, source) logic

100 mA max.

LIGHT indicator

STABILITY indicator

Light	Incident	Interrupted
LIGHT indicator	ON	OFF
Output transistor	ON	OFF
Load (relay, source)	ON	OFF





OMRON ELECTRONICS LLC

One East Commerce Drive
Schaumburg, IL 60173

1-800-55-OMRON

OMRON ON-LINE

Global - <http://www.omron.com>
USA - <http://www.omron.com/oei>
Canada - <http://www.omron.com/oci>

OMRON CANADA, INC.

885 Milner Avenue
Scarborough, Ontario M1B 5V8

416-286-6465