


Coax Probes ATTACHED CABLE

100445 & 100746 SIGNAL PLUNGERS




A

B

ES

H


100445 & 100746 SHIELDING PLUNGERS



N

S


100999
PLUNGERS TIPS



B

U

100445/100746



PROBE SPECIFICATIONS

Minimum Centers: .200 (5.08)
Current Rating: 3 amps continuous
Spring Force: Signal Conductor:
 B Tip: 1.6 oz. @ .070 (1.78) travel
 A, ES, H Tips: 2.0 oz. @ .070 (1.78) travel
 Shielding Plunger: 4.3 oz. @ .070 (1.78) travel
Nominal Impedance: 50 Ω
Maximum Travel:
 .090 (2.29) for tip B
 .075 (1.91) for tips A, ES, H
Working Travel: .070 (1.78)

MATERIALS

Barrel: Brass, gold plated
Spring:
 Signal Conductor: Beryllium copper, gold plated
 Shielding Plunger: Stainless steel, gold plated
Shielding Plunger: Beryllium copper, gold plated
Dielectric Insulator: Teflon
Shielding Tube: Stainless steel, gold plated
Signal Conductor: Series S, Size 00 probe
Crimp Ferrule: Brass, gold plated
Coaxial Cable: 100445: RG 174U
 100746: RG 316

How to Order


100445	B	F	N	12	AM
BASE PART NUMBER	SIGNAL PROBE TIP	MOUNTING FLANGE	SHIELDING PLUNGER	CABLE LENGTH	TERMINATION
				N: WITHOUT FLANGE F: WITH FLANGE	
SHIELDING PLUNGER:	CABLE LENGTH:	AM: SMA MALE			
S: SERRATED	12 - 12 INCHES	AF: SMA FEMALE			
N: FLAT	36 - 36 INCHES	NC: NO CONNECTOR			

* WHEN ORDERING WITH A PREATTACHED CONNECTOR, PLEASE NOTE THAT THE CONNECTOR WILL NOT FIT THROUGH THE PROBE MOUNTING HOLE. THE PROBE MUST BE INSERTED FROM THE BOTTOM SIDE OF THE MOUNTING PLATE.

CONSULT IDI FOR MORE INFORMATION.

Specifications subject to change without notice. Dimensions in inches (millimeters)

100999



PROBE SPECIFICATIONS

Minimum Centers: .200 (5.08)
Current Rating: 3 amps continuous
Spring Force: Signal Conductor:
 B Tip: 1.6 oz. @ .070 (1.78) travel
 U Tip: 3.3 oz. @ .070 (1.78) travel
 Shielding Plunger: 4.5 oz. @ .070 (1.78) travel
Nominal Impedance: 50 Ω
Maximum Travel: .090 (2.29)
Working Travel: .070 (1.78)

MATERIALS

Barrel: Brass, gold plated

Spring:

- Signal Conductor: Beryllium copper, gold plated
- Shielding Plunger: Stainless steel, gold plated

Shielding Plunger: Beryllium copper, gold plated

Dielectric Insulator: Teflon

Shielding Tube: Brass, gold plated

Signal Conductor: Series S, Size 00 probe

Coaxial Cable: Semi-flex or flex cable

How to Order

100999	B	12	AM	F
BASE PART NUMBER	SIGNAL PROBE TIP	CABLE LENGTH	TERMINATION	CABLE TYPE

CABLE LENGTH:	AM: SMA MALE	F: FLEX
12 - 12 INCHES	AF: SMA FEMALE	S: SEMI-FLEX
36 - 36 INCHES	NC: NO CONNECTOR	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IDI:

[100445-H-N-N-12-AM](#) [100445-H-F-S-12-AM](#) [100445-H-F-N-12-AM](#) [100445-B-N-N-12-AM](#) [100445-H-N-N-12-AF](#)
[100445-H-N-N-12-NC](#) [100445-H-N-N-36-AM](#) [100445-H-F-N-12-AF](#) [100445-H-F-N-12-BF](#) [100445-H-F-N-12-NC](#)
[100445-H-F-N-36-AM](#) [100445-H-F-N-36-BF](#) [100445-H-F-N-36-NC](#) [100445-B-N-N-12-AF](#) [100445-B-N-N-12-NC](#)
[100445-B-F-N-12-AM](#) [100445-B-F-N-12-AF](#) [100445-B-F-N-12-NC](#) [100445-B-F-N-36-AM](#) [100445-J-N-N-12-AM](#)
[100445-J-N-N-12-AF](#) [100445-J-F-N-12-AM](#) [100445-J-F-N-12-AF](#) [100445-B-N-S-12-AM](#) [100445-B-N-S-12-AF](#)
[100445-B-N-S-12-NC](#) [100445-B-N-S-36-AM](#) [100445-B-N-S-36-NC](#) [100445-B-F-S-12-AM](#) [100445-B-F-S-12-AF](#)
[100445-B-F-S-12-NC](#) [100445-B-F-S-36-AM](#) [100445-U-N-N-12-AM](#) [100445-U-N-N-12-NC](#) [100445-U-N-N-36-AM](#)
[100445-U-F-N-12-AM](#) [100445-U-F-N-12-AF](#) [100445-U-F-N-36-NC](#) [100445-H-N-S-12-AM](#) [100445-H-N-S-12-AF](#)
[100445-H-N-S-12-BM](#) [100445-H-N-S-12-NC](#) [100445-H-N-S-36-NC](#) [100445-H-F-S-12-AF](#) [100445-H-F-S-12-NC](#)
[100445-H-F-S-36-AM](#) [100445-H-F-S-36-BM](#) [100445-H-F-S-36-NC](#) [100445-J-F-S-12-AM](#) [100445-ES-N-S-12-AM](#)
[100445-ES-N-S-12-NC](#) [100445-ES-N-S-36-AM](#) [100445-ES-N-S-36-NC](#) [100445-ES-F-S-12-AM](#) [100445-ES-F-S-12-AF](#)
[100445-ES-F-S-12-NC](#) [100445-ES-F-S-36-AM](#) [100445-ES-F-S-36-NC](#) [100445-A-N-N-12-AM](#) [100445-A-F-N-12-AM](#)
[100445-A-F-N-36-AM](#) [100445-A-N-S-12-AM](#) [100445-A-N-S-12-AF](#) [100445-A-N-S-12-NC](#) [100445-A-F-S-12-AM](#)
[100445-A-F-S-12-AF](#) [100445-A-F-S-12-NC](#) [100445-ES-N-N-12-AM](#) [100445-ES-N-N-12-AF](#) [100445-ES-N-N-12-BF](#)
[100445-ES-N-N-12-BM](#) [100445-ES-F-N-12-AM](#) [100445-ES-F-N-12-AF](#) [100445-ES-F-N-12-NC](#) [100445-ES-F-N-36-AM](#)
[100445-ES-F-N-36-NC](#) [100445-U-N-S-12-AM](#) [100445-U-N-S-12-AF](#) [100445-U-N-S-12-NC](#) [100445-U-F-S-12-AM](#)
[100445-U-F-S-12-AF](#) [100445-U-F-S-36-AM](#) [100445-U-F-S-36-AF](#) [100445-U-F-S-36-NC](#) [100746-H-N-N-12-NC](#)
[100746-H-F-N-12-AM](#) [100746-H-F-N-12-NC](#) [100746-H-F-N-36-NC](#) [100746-B-N-N-36-NC](#) [100746-B-F-N-12-AF](#)
[100746-B-F-N-36-AF](#) [100746-J-N-N-36-NC](#) [100746-B-N-S-12-NC](#) [100746-B-F-S-12-AM](#) [100746-B-F-S-12-NC](#)
[100746-B-F-S-36-AM](#) [100746-H-N-S-12-NC](#) [100746-H-F-S-12-AM](#) [100746-H-F-S-12-AF](#) [100746-H-F-S-36-NC](#)