





used for:	D-SUB COMBINATION
-----------	-------------------



NOTES:

1. METALSHELLS: STEEL; min. 320μ" TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: 30μ" HARD GOLD OVER min. 50μ" NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 - A3
5. CONNECTOR IS PART MARKED: 3013W3PCM99A10X CONEC ABC
6. = CHECK DIMENSION

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL #	FREIGABE #	DEBLOCKAGE #	AUTORIZACION #	APPROVAL
CUSTOMER APPROVAL DATE:				
NAME:		TITLE:		
COMPANY NAME:				

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm	
				2005	date	name	
				drawn	28.11.	Lehmenkühler	
				appd.	28.11.	Mickenbecker	
				norm			
				d-old			
							
rev.	description	date	name				

tolerance



scale:	2:1 (5:1)
--------	-----------

material:	SEE NOTES
-----------	-----------

title:	D-SUB COMBINATION MALE 13W3P SOLDER CUP
--------	--

dwg no:	AutoCAD 2004	DIN-A
---------	--------------	-------

13K3A1351

part no: 3013W3PCM99A10X

DIN-A
3
sh: 1/1