

Technical drawing of a shaft with dimensions A, B, C, D, E, and F. Dimension A is the total length, B is the diameter of the main shaft, C is the diameter of the flange, D is the thickness of the flange, and E is the height of the flange. The shaft has a threaded section at the right end.

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE ^{lbs.} (N)	CROSS SECTION	WEIGHT ^{lbs.} / 100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
BT2LH	.188 (4.8)	2.00 (51)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	8.7 (221)	120 (534)	LIGHT HEAVY	.59 (267)
BT3LH	.188 (4.8)	3.00 (76)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	11.8 (300)	120 (534)	LIGHT HEAVY	.79 (358)
BT4LH	.188 (4.8)	4.00 (102)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	14.9 (378)	120 (534)	LIGHT HEAVY	.99 (449)
BT5LH	.188 (4.8)	5.00 (127)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	18.1 (460)	120 (534)	LIGHT HEAVY	1.19 (540)
BT6LH	.188 (4.8)	6.00 (152)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	21.2 (538)	120 (534)	LIGHT HEAVY	1.39 (631)
BT7LH	.188 (4.8)	7.00 (178)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	24.4 (620)	120 (534)	LIGHT HEAVY	1.59 (722)
BT8LH	.188 (4.8)	8.00 (203)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	27.5 (699)	120 (534)	LIGHT HEAVY	1.79 (813)
BT9LH	.188 (4.8)	9.00 (229)	.065 (1.7)	.275 (7.0)	.325 (8.3)	.320 (8.1)	.520 (13.2)	30.7 (780)	120 (534)	LIGHT HEAVY	1.99 (904)

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty CABLE TIES
BT SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm .10$ (.5) (.XXX) $\pm .020$ (.5)
(.XX) $\pm .02$ (.5) ANGLES $\pm$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
PMH

MAT'L:

	SCALE
--	--------------

NONE

DATE	6-24-93
------	---------

NYLON 6.6

DRAWING NO.

BT - 0037

SHT. 3 OF 3

DWG
A
SIZE

6	5/2/06	JABC		REMOVED CURVED TIP REFERENCE & TIP STYLE COLUMN	BT-0037	6			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		