



Cylinder mountings

Type	Description	Cyl. bore Ø mm	Weight kg	Order code
Flange MF1/MF2 	Intended for fixed mounting of cylinder. Flange can be fitted to front- or rear end-plates of cylinder. Materials Flange: Surface-treated steel, black Mounting screws acc. to DIN 6912: Zinc-plated steel 8.8 Supplied complete with mounting screws for attachment to cylinder.	32	0,23	P1C-4KMB
		40	0,28	P1C-4LMB
		50	0,53	P1C-4MMB
		63	0,71	P1C-4NMB
		80	1,59	P1C-4PMB
		100	2,19	P1C-4QMB
		125	3,78	P1C-4RMB


According to ISO MF1/MF2, VDMA 24 562 T.2/2-, AFNOR

Cyl. bore mm	d1 H11 mm	FB H13 mm	TG1 mm	E mm	R JS14 mm	MF JS14 mm	TF JS14 mm	UF mm	l1 -0,5 mm	W mm	ZF mm	ZB mm
32	30	7	32,5	45	32	10	64	80	5	16	130	123,5
40	35	9	38	52	36	10	72	90	5	20	145	138,5
50	40	9	46,5	65	45	12	90	110	6,5	25	155	146,5
63	45	9	56,5	75	50	12	100	120	6,5	25	170	161,5
80	45	12	72	95	63	16	126	150	8	30	190	177,5
100	55	14	89	115	75	16	150	170	8	35	205	192,5
125	60	16	110	140	90	20	180	205	10,5	45	245	230,5

S = Stroke length



Foot bracket MS1



Intended for fixed mounting of cylinder. Foot bracket can be fitted to front- and rear end-covers of cylinder.

Materials
Foot bracket: Surface-treated steel, black
Mounting screws acc. to DIN 912: Zinc-plated steel 8.8

Supplied in pairs with mounting screws for attachment to cylinder.


32	0,06*	P1C-4KMF
40	0,08*	P1C-4LMF
50	0,16*	P1C-4MMF
63	0,25*	P1C-4NMF
80	0,50*	P1C-4PMF
100	0,85*	P1C-4QMF
125	1,48*	P1C-4RMF

* Weight per item


According to ISO MS1, VDMA 24 562 T.2/7-, AFNOR

Cyl. bore mm	AB H14 mm	TG1 mm	E mm	TR JS14 mm	AO mm	AU mm	AH JS15 mm	I7 mm	AT mm	I9 JS14 mm	SA mm
32	7	32,5	45	32	10	24	32	30	4,5	17	142
40	9	38	52	36	8	28	36	30	4,5	18,5	161
50	9	46,5	65	45	13	32	45	36	5,5	25	170
63	9	56,5	75	50	13	32	50	35	5,5	27,5	185
80	12	72	95	63	14	41	63	49	6,5	40,5	210
100	14	89	115	75	15	41	71	54	6,5	43,5	220
125	16	110	140	90	22	45	90	71	8	60	250

S = Stroke length



Pivot bracket with rigid bearing



Intended for flexible mounting of cylinder. The pivot bracket can be combined with clevis bracket MP2.

Materials
Pivot bracket: Surface-treated aluminium, black
Bearing: Sintered oil-bronze bushing

32	0,06	P1C-4KMD
40	0,08	P1C-4LMD
50	0,15	P1C-4MMD
63	0,20	P1C-4NMD
80	0,33	P1C-4PMD
100	0,49	P1C-4QMD
125	1,02	P1C-4RMD

According to CETOP RP 107 P, VDMA 24 562 T.2/5-, AFNOR

Cyl. bore mm	CK H9 mm	S5 H13 mm	K1 JS14 mm	K2 mm	G1 JS14 mm	G2 JS14 mm	EM mm	G3 mm	CA JS15 mm	H6 mm	R1 mm
32	10	6,6	38	51	21	18	25,5	31	32	8	10
40	12	6,6	41	54	24	22	27	35	36	10	11
50	12	9	50	65	33	30	31	45	45	12	13
63	16	9	52	67	37	35	39	50	50	12	15
80	16	11	66	86	47	40	49	60	63	14	15
100	20	11	76	96	55	50	59	70	71	15	19
125	25	14	94	124	70	60	69	90	90	20	22,5

