






LOC	DIST	REVISIONS					
AD	OO	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECO-14-000254	15APR2014	NK	MM



RECOMMENDED HOLE LAYOUT

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 4 HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
CONTACT: COPPER ALLOY
- 5 FINISH: 0.00254-0.00508 [0.000100-0.000200] MATTE TIN-LEAD
OVER 0.00127 [0.000050] NICKEL ENTIRE POST.
- 6 FINISH: 0.00254-0.00508 [0.000100-0.000200] MATTE TIN
OVER 0.00127 [0.000050] NICKEL ENTIRE POST.

	△5	101.19 [3.984]	99.06 [3.900]	39	80	4-146487-0
	△5	98.65 [3.884]	96.52 [3.800]	38	78	3-146487-9
	△5	96.11 [3.784]	93.98 [3.700]	37	76	3-146487-8
	△5	93.57 [3.684]	91.44 [3.600]	36	74	3-146487-7
	△5	91.03 [3.584]	88.90 [3.500]	35	72	3-146487-6
	△5	88.49 [3.484]	86.36 [3.400]	34	70	3-146487-5
OBSOLETE	△5	85.95 [3.384]	83.82 [3.300]	33	68	3-146487-4
	△5	83.41 [3.284]	81.28 [3.200]	32	66	3-146487-3
	△5	80.87 [3.184]	78.74 [3.100]	31	64	3-146487-2
	△5	78.33 [3.084]	76.20 [3.000]	30	62	3-146487-1
	△5	75.79 [2.984]	73.66 [2.900]	29	60	3-146487-0
	△5	73.25 [2.884]	71.12 [2.800]	28	58	2-146487-9
	△5	70.71 [2.784]	68.58 [2.700]	27	56	2-146487-8
	△5	68.17 [2.684]	66.04 [2.600]	26	54	2-146487-7
	△5	65.63 [2.584]	63.50 [2.500]	25	52	2-146487-6
	△5	63.09 [2.484]	60.96 [2.400]	24	50	2-146487-5
	△5	60.55 [2.384]	58.42 [2.300]	23	48	2-146487-4
	△5	58.01 [2.284]	55.88 [2.200]	22	46	2-146487-3
	△5	55.47 [2.184]	53.34 [2.100]	21	44	2-146487-2
	△5	52.93 [2.084]	50.80 [2.000]	20	42	2-146487-1
	△5	50.39 [1.984]	48.26 [1.900]	19	40	2-146487-0
	△5	47.85 [1.884]	45.72 [1.800]	18	38	1-146487-9
	△5	45.31 [1.784]	43.18 [1.700]	17	36	1-146487-8
	△5	42.77 [1.684]	40.64 [1.600]	16	34	1-146487-7
	△5	40.23 [1.584]	38.10 [1.500]	15	32	1-146487-6
	△5	37.69 [1.484]	35.56 [1.400]	14	30	1-146487-5
	△5	35.15 [1.384]	33.02 [1.300]	13	28	1-146487-4
	△5	32.61 [1.284]	30.48 [1.200]	12	26	1-146487-3
	△5	30.07 [1.184]	27.94 [1.100]	11	24	1-146487-2
	△5	27.53 [1.084]	25.40 [1.000]	10	22	1-146487-1
	△5	24.99 [.984]	22.86 [.900]	9	20	1-146487-0
	△5	22.45 [.884]	20.32 [.800]	8	18	146487-9
	△5	19.91 [.784]	17.78 [.700]	7	16	146487-8
	△5	17.37 [.684]	15.24 [.600]	6	14	146487-7
	△5	14.83 [.584]	12.70 [.500]	5	12	146487-6
	△5	12.29 [.484]	10.16 [.400]	4	10	146487-5
	△5	9.75 [.384]	7.62 [.300]	3	8	146487-4
	△5	7.21 [.284]	5.08 [.200]	2	6	146487-3
	△5	4.67 [.184]	2.54 [.100]	1	4	146487-2
	△5	2.13 [.084]	- -	-	2	146487-1
	PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 050EC95 CHK: HOFFMAN G. DUBNICZKI 02JAN96 02JAN96		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES: UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.51[.02] 3 PLC ± 0.127[.005] 4 RLC ± 0.0127[.0005] 5 RLC ± — 6 ANGLES ± —		PRODUCT SPEC APPLICATION SPEC	
MATERIAL 		FINISH SEE TABLE		SIZE A1	
		WEIGHT —		CASE CODE —	
		CUSTOMER DRAWING		DRAWING NO C146487	
				RESTRICTED TO	
				SCALE 4:1	
				SHEET 1 of 2	
				REV B	

