









5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

PN 2-3



	DESCRIPTION
	HD.40.S1s.1.29.Z
	HD-K.40.S1s.1.29.Z
	HD.40.S1s-VS.1.29.Z
	HDK.40.S1s-VS.1.29.Z
	HD.40.S1s-GR.1.29.Z
	HD-K.40.S1s-GR.1.29.Z
	HD-Z.40.S1s-ZB.1.29.Z
	HD-K/Z.40.S1s-ZB.1.29.Z

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO THE TYCO ELECTRONICS POLICY ON CONTROLLED DOCUMENTS SHOULD BE CONTACTED FOR THE LATEST REVISION.		OWN 11.12.1997 Gräf CHK 02.06.98 Kramer		 Tyco Electronics Corporation D-53819, Neunkirchen, Germany	
DIMENSIONS : mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: mm ISO 2768-mS mm ISO 2768-1S		NAME	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD - PRODUCT SPEC - APPLICATION SPEC -	
MATERIAL		FINISH		SIZE CAGE CODE DRAWING NO A 00779 C=1102566	
		WEIGHT -		RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 1:1 SHEET 1 of 1 REV A6	