

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00						
			Y	REVISED PER ECO-12-011709	26JUN2012	RW	SY

D

C

B

A



- 1. .000050 MIN THK NICKEL UNDERPLATE OVER ENTIRE CONTACT.
- 2. .000150 MIN BRIGHT TIN/LEAD OVER ENTIRE CONTACT.
- 3. .000100 MIN THK BRIGHT TIN/LEAD IN ZONE 1.
- 4. GOLD FLASH IN LOCALIZED GOLD PLATE AREA.
- 5. .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 6. .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 7. TO BE APPLIED PER AMP APPLICATION SPEC 114-16015.
- 8. RECOMMENDED HOLE SIZE IS .031-.035 DIA.
- 9. FOR SOLDERABILITY SEE AMP PRODUCT SPEC 108-9024.
- 10. .000150 MIN TIN-LEAD IN ZONE 2.
- 11. AREA TO BE UNPLATED (-9 ONLY).
- 12. GOLD FLASH IN ZONE 1. .000150 MIN TIN IN ZONE 3.
- 13. GOLD FLASH IN ZONE 1.
- 14. GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL IN THIS AREA.

D

C

B

A

				1-88997-4		
				1-88997-3		
				1-88997-2		
					88997-9	
						88997-5
						88997-4
						88997-3
						88997-2
FINISH					PART NO	

SUPERSEDED BY 88997-5

SECTION D-D

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B. MCMASTER CHK S. BOLASH APVD M. WALMSLEY		10MAR04 10MAR04 10MAR04		 TE Connectivity						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		CONTACT, SOLDER TAB, FFC, .100 ϕ							
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-9024 APPLICATION SPEC 114-16015		SIZE A2		CAGE CODE 00779		DRAWING NO C-88997		RESTRICTED TO —	
MATERIAL PH. BRONZE .010 THK		FINISH SEE TABLE		WEIGHT —									
CUSTOMER DRAWING						SCALE 10:1		SHEET 1 of 1		REV Y			