

Single-Phase Hot-Swap PDU, 2.9kW 30A 120V, 2U Horizontal Rackmount, 6 NEMA 5-15/20R and 1 NEMA L5-30R outlets, 2 NEMA L5-30P inputs

MODEL NUMBER: **PDUB30**



Description

Tripp Lite's Hot-swap PDU systems enable live-replacement of standard UPS systems for maintenance with no interruption of connected server or networking loads. Dual input power cables support PDU connection to separate Utility and UPS power sources. Manual transfer switch with lighted status indicators controls the source of power to connected equipment between Utility and UPS. Set the switch to UPS during normal operation and connected equipment will receive full-time conditioned power from the UPS. Set the switch to Utility to momentarily power connected equipment from the Utility line cord and bypass the UPS while the UPS system is removed and replaced with a fresh one. Once the new UPS is up and running with all data and electrical connections restored, set the switch back to the UPS setting to once again provide fully-conditioned UPS power to connected equipment.

Features

- Tripp Lite Hot-swap PDU systems support live-replacement of standard UPS systems for maintenance with no interruption of connected server or networking loads
- PDUB30 is universally compatible with any Tripp Lite or other brand of 100-127V UPS rated up to 3000VA or 2880 watts with a NEMA L5-30P input cable
- 2U horizontal rackmount form factor compatible with 2 or 4 post racks
- Supports space saving rear-post mounting in the same rack space as many Tripp Lite Rackmount UPS systems (select installations, see manual)
- Pair of attached L5-30P PDU input cables connect to separate Utility and UPS power sources
- 6 5-15/20R and 1 L5-30R outlets support critical networking loads in both Utility and UPS operating modes
- One additional L5-30R pass-through outlet supports UPS input power cord
- Dual input power cables support PDU connection to separate Utility and UPS power sources
- Manual transfer switch with lighted status indicators controls the source of power to connected equipment between Utility and UPS
- Set the switch to UPS during normal operation and connected equipment will receive full-time conditioned power from the UPS
- Set the switch to Utility to bypass the UPS and provide connected equipment with unfiltered power directly from the Utility line cord while the UPS system is removed and replaced with a fresh one

Highlights

- Single phase 30A 120V Hot-swap PDU
- Enables live replacement of a standard UPS with zero downtime
- 2U horizontal rackmount installation
- Compatible with any UPS with a L5-30P input plug
- Manual transfer switch controls PDU input power source
- Pair of L5-30P input cables connect to separate Utility and UPS inputs
- 7 outlets (6 5-15/20 & 1 L5-30R)

Applications

Hot-swap PDUs are ideal to install along with standard UPS systems to ensure that connected networking equipment will see no power interruption as the UPS is serviced, replaced or upgraded

Package Includes

- Hot-swap PDU System
- 2U mounting brackets
- User manual with warranty information

- Once the new UPS is up and running with all connections restored, set the switch back to the UPS setting to once again provide fully-conditioned UPS power to connected equipment
- TAA Compliant Version Available - Order Tripp Lite PDUB30TAA

Specifications

General Info	
Product Group	PDUS
OVERVIEW	
PDU Type	Hot-Swap
OUTPUT	
Output Capacity Details	2.9kW (120V input), 3.0kW (127V input), 2.4kW (100V input); 30A maximum (agency de-rated to 24A continuous)
Output Watt Capacity (Watts)	2880
Frequency Compatibility	50 / 60 Hz
Output Nominal Voltage	100-127V nominal, single phase
Outlet Quantity / Type	6 NEMA 5-15/20R and 1 L5-30R outlets support critical connected loads; 1 designated pass-through L5-30R outlet supports UPS L5-30P input plug
Outlet Type	NEMA 5-15/20R, L5-30R
INPUT	
PDU Input Voltage	100; 120; 127
Maximum Input Amps	24
PDU Plug Type	NEMA L5-30P
Input Cord Length Details	Utility input cable (10 ft / 3m) / UPS input cable (6 ft / 1.8m)
Input Phase	Single-Phase
LEDs ALARMS & SWITCHES	
Switches	Manual 2 position transfer switch offers fast switching between UPS and Utility operating modes in less than 6 milliseconds
Front Panel LEDs	Lighted indicators confirm UPS and Utility switch position and operating mode
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.25 x 20.23 x 6.1
Shipping Dimensions (hwd / cm)	23.5 x 51.4 x 15.5
Shipping Weight (lbs.)	11
Shipping Weight (kg)	5

Unit Dimensions (hwd / in.)	3.42 x 17.32 x 3.03
Unit Dimensions (hwd / cm)	8.7 x 44 x 7.7
Unit Weight (lbs.)	7.7
Unit Weight (kg)	3.5
Material of Construction	Steel
Style	Rackmount
Form Factors Supported	2U rackmount in 2 or 4 post racks
PDU Form Factor	Horizontal (1U, 2U, etc)
ENVIRONMENTAL	
Relative Humidity	0-95% non condensing
CERTIFICATIONS	
TAA Compliant Option	TAA Compliant Version Available - Order Tripp Lite PDUB30TAA
Certifications	Tested to UL60950 (USA), CSA (Canada)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.