



| Ampère | Poles | 110 V 50 a. 60 Hz | 230 V 50 a. 60 Hz | 400 V 50 a. 60 Hz | 500 V 50 a. 60 Hz | > 50 - 500 V 100 - 300 Hz | > 50 - 500 V over 300 - 500 Hz |  |  |
|--------|-------|----------------------------|----------------------------|----------------------------|----------------------------|-------------------------------|-----------------------------------|---|---|
| | | 3pole 4h 4pole 4h 5pole 4h | 3pole 6h 4pole 9h 5pole 9h | 3pole 9h 4pole 6h 5pole 6h | 3pole 7h 4pole 7h 5pole 7h | 3pole 10h 4pole 10h 5pole 10h | 3pole 2h 4pole 2h 5pole 2h | | |

| Part numbers | | | | | | | | | | |
|--|----|---|------------|-------------------|-------------------|------------|------------|------------|-------|-----|
|  | 16 | 4 | 310 404 SL | 310 409 SL | 310 406 SL | 310 407 SL | 310 410 SL | 310 402 SL | 10/60 | 261 |
| | 16 | 5 | 310 504 SL | 310 509 SL | 310SL | | | | 10/60 | 304 |
| | 32 | 3 | 330 304 SL | 330 306 SL | 330 309 SL | | | | 10/60 | 323 |
| | 32 | 4 | 330 404 SL | 330 409 SL | 330 406 SL | 330 407 SL | 330 410 SL | 330 402 SL | 10/60 | 342 |
| | 32 | 5 | 330 504 SL | 330 509 SL | 330 SL | | | | 10/60 | 371 |
| Screwless couplers with insulation displacement technique, IP 44  , with cable gland | | | | | | | | | | |

| | | | | | | | | | | |
|--|----|---|------------|-------------------|--|--|--|--|----|-----|
|  | 16 | 3 | 310 304 CK | 310 306 CK | CK = plugs with crimp contacts, screwless, click-together assembly, nonrewireable, tamper proof, maintenance-free | | | | 10 | 155 |
| | 16 | 3 | 310 304 SK | 310 306 SK | SK = plugs with screw terminals, rewireable | | | | 10 | 160 |
| Couplers with crimp contacts, IP 44  | | | | | | | | | | |

| | | | | | | | | | | |
|---|----|---|---------|----------------|----------------|---------|---------|---------|-------|-----|
|  | 16 | 4 | 310 404 | 310 409 | 310 406 | 310 407 | 310 410 | 310 402 | 10 | 248 |
| | 16 | 5 | 310 504 | 310 509 | 310 | | | | 10/60 | 270 |
| | 32 | 3 | 330 304 | 330 306 | 330 309 | | | | 10 | 312 |
| | 32 | 4 | 330 404 | 330 409 | 330 406 | 330 407 | 330 410 | 330 402 | 10 | 328 |
| | 32 | 5 | 330 504 | 330 509 | 330 | | | | 10/60 | 363 |
| Couplers  IP 44, with screw terminals, with cable gland | | | | | | | | | | |

| | | | | | | | | | | |
|---|---|---|---------|----------------|---------|--|--|--|----|-----|
|  | 16 | 3 | 315 304 | 315 306 | 315 309 | | | | 10 | 140 |
| | Couplers IP 44  , with inverted cable entry | | | | | | | | | |

| | | | | | | | | | | | |
|--|----|---|---|----------------|----------------|---------|---------|---------|----|-----|-----|
|  | 16 | 3 | 311 304 | 311 306 | 311 309 | | | | 10 | 147 | |
| | 16 | 4 | 311 404 | 311 409 | 311 406 | 311 407 | 311 410 | 311 402 | 10 | 197 | |
| | 16 | 5 | 311 504 | 311 509 | 311 | | | | 10 | 214 | |
| | 16 | 5 | 311 NI (with nickel plated contacts + glass-fibre reinforced enclosure) | | | | | | | 10 | 214 |
| | 32 | 3 | 331 304 | 331 306 | 331 309 | | | | 10 | 265 | |
| | 32 | 4 | 331 404 | 331 409 | 331406 | 331 407 | 331 410 | 331 402 | 10 | 278 | |
| | 32 | 5 | 331 504 | 331 509 | 331 | | | | 10 | 300 | |
| | 32 | 5 | 331 NI (with nickel plated contacts + glass-fibre reinforced enclosure) | | | | | | | 10 | 300 |
| | 63 | 3 | 361 304 | 361 306 | 361 309 | | | | 5 | 656 | |
| | 63 | 4 | 361 404 | 361 409 | 361 406 | 361 407 | 361 410 | 361 402 | 5 | 771 | |
| | 63 | 5 | 361 504 | 361 509 | 361 | | | | 5 | 787 | |
| | 63 | 5 | 361 NI (with nickel plated contacts + glass-fibre reinforced enclosure) | | | | | | | 5 | 787 |
| Couplers IP 44  , with gland entry | | | | | | | | | | | |

| | | | | | | | | | | | |
|--|----|---------|---|----------------|----------------|---------|---------|-----------------------------------|-------|-----|-----|
|  | 16 | 3 | 310 304 | 310 306 | 310 309 | | | | 10/60 | 150 | |
| | 16 | 3 | 310 306 AS (lockable with padlock (padlock not included)) | | | | | | | 10 | |
| | 16 | 5 | | | | | 310 NI | (with nickel plated contacts and | | 10 | 228 |
| | 32 | 5 | | | | | 330 NI | glass-fibre reinforced enclosure) | | 10 | 317 |
| | 63 | 5 | | | | | 360 NI | | | 5 | 782 |
| | 63 | 3 | 360 304 | 360 306 | 360 309 | | | | 5 | 672 | |
| | 63 | 4 | 360 404 | 360 409 | 360 406 | 360 407 | 360 410 | 360 402 | 5 | 719 | |
| 63 | 5 | 360 504 | 360 509 | 360 | | | | 5 | 782 | | |
| Couplers  IP 44, with screw terminals, with flexible cable entry | | | | | | | | | | | |





| Ampère | Poles | 110 V 50 a. 60 Hz | 230 V 50 a. 60 Hz | 400 V 50 a. 60 Hz | 500 V 50 a. 60 Hz | > 50 - 500 V 100 - 300 Hz | > 50 - 500 V over 300 - 500 Hz | | |
|--------|-------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|-------------------------------------|-----------------------------------|--|--|
| | | 3pole 4h 4pole 4h 5pole 4h | 3pole 6h 4pole 9h 5pole 9h | 3pole 9h 4pole 6h 5pole 6h | 3pole 7h 4pole 7h 5pole 7h | 3pole 10h 4pole 10h 5pole 10h | 3pole 2h 4pole 2h 5pole 2h | | |

Part numbers

3



319306

| | | | | | | | | | |
|----|---|---------|----------------|---------|--|--|--|----|-----|
| 16 | 3 | 319 304 | 319 306 | 319 309 | | | | 10 | 172 |
|----|---|---------|----------------|---------|--|--|--|----|-----|

Couplers ☹ IP 67, with screw terminals and gland entry



339 cable gland

new design

| | | | | | | | | | |
|----|---|---------|----------------|----------------|---------|---------|---------|----|-----|
| 16 | 4 | 319 404 | 319 409 | 319 406 | 319 407 | 319 410 | 319 402 | 10 | 268 |
| 16 | 5 | 319 504 | 319 509 | 319 | | | | 10 | 298 |
| 32 | 3 | 339 304 | 339 306 | 339 309 | | | | 10 | 351 |
| 32 | 4 | 339 404 | 339 409 | 339 406 | 339 407 | 339 410 | 339 402 | 10 | 369 |
| 32 | 5 | 339 504 | 339 509 | 339 | | | | 10 | 415 |

The couplers come with new design and with cable gland. Additionally they are also available as **screwless version** with IDC insulation displacement connection. To order a coupler as screwless version, just add „SL“ to the part number, e.g. 319SL.

Couplers ☹ IP 67, with screw terminals or as screwless SL version with IDC technique and cable gland



suitable for devices with cable gland

A holding plate allows you to suspend a plug/coupler with cable gland from the ceiling.

for a **16 A** plug/coupler use holding plate no.: **314 500**
for a **32 A** plug/coupler use holding plate no.: **334 500**

314 500

Holding plates, useable for plugs and couplers with cable gland



339 NI

369

| | | | | | | | | | |
|-----|---|---------|----------------|----------------|---|---------|---------|----|------|
| 16 | 5 | | | 319 NI | | | | 10 | 255 |
| 32 | 5 | | | 339 NI | <i>with nickel plated contacts + glass-fibre reinforced enclosure</i> | | | 10 | 350 |
| 63 | 5 | | | 369 NI | | | | 5 | 849 |
| 63 | 3 | 369 304 | 369 306 | 369 309 | | | | 5 | 758 |
| 63 | 4 | 369 404 | 369 409 | 369 406 | 369 407 | 369 410 | 369 402 | 5 | 796 |
| 63 | 5 | 369 504 | 369 509 | 369 | | | | 5 | 844 |
| 125 | 3 | 379 304 | 379 306 | 379 309 | | | | 2 | 1362 |
| 125 | 4 | 379 404 | 379 409 | 379 406 | 379 407 | 379 410 | 379 402 | 2 | 1536 |
| 125 | 5 | 379 504 | 379 509 | 379 | | | | 2 | 1710 |

Couplers IP 67 ☹, with gland entry, with multi contact



316 306

| | | | | | | | | | |
|----|---|---------|----------------|---------|--|--|--|----|-----|
| 16 | 3 | 316 304 | 316 306 | 316 309 | | | | 10 | 138 |
|----|---|---------|----------------|---------|--|--|--|----|-----|

Angled couplers IP 44 ⚠



317 306

| | | | | | | | | | |
|----|---|--|----------------|--|--|--|--|----|-----|
| 16 | 3 | | 317 306 | | | | | 10 | 152 |
|----|---|--|----------------|--|--|--|--|----|-----|

Angled coupler IP 44 ⚠, with Schuko socket on reverse side