


# Double-Pole Rocker Switch

## YR Series



### Features

- High current rating to 20 amps
- Lighted and non-lighted
- Maintained action and momentary
- Mechanical life: min. 50,000 operations

| Electrical Ratings |                                                |                                                 |                                       |                                      |
|--------------------|------------------------------------------------|-------------------------------------------------|---------------------------------------|--------------------------------------|
| Switch Series      | EN61058 Rating                                 | UL1054 Rating                                   | Electrical Life at Rated Load         |                                      |
|                    |                                                |                                                 | According to VDE<br>(Min. Operations) | According to UL<br>(Min. Operations) |
| YRM                | 16(4)A 250V ~ T125/55<br>16(8)A 250V ~ T125/55 | 20A, 125VAC;<br>16A 125/250VAC; ¾ HP 125/250VAC | 10,000                                | 6,000                                |

| Electrical Specifications   |                                                                                                                | Material Specifications |                            |
|-----------------------------|----------------------------------------------------------------------------------------------------------------|-------------------------|----------------------------|
| Ratings:                    | 20A 125VAC;<br>16A 125/250VAC, ¾ HP 125/250VAC cULus<br>16(4)A 250V ~ T125/55 VDE<br>16(8)A 250V ~ T125/55 VDE | Actuator (non-lighted): | Nylon 66 94V-2             |
|                             |                                                                                                                | (lighted):              | Polycarbonate              |
| Dielectric Strength:        | 1000VAC for 1 minute                                                                                           | Base:                   | Nylon 66 94V-2             |
| Insulation Resistance:      | 10 <sup>8</sup> ohms min at 500VDC                                                                             | Spring:                 | Steel Wire                 |
| Initial Contact Resistance: | 0.020 ohms max                                                                                                 | Contacts:               | Silver Alloy               |
| Temperature Range:          | 0°C to + 105°C UL                                                                                              | Movable Arm:            | Silver-Plated Copper Alloy |
|                             |                                                                                                                | Terminals:              | Tin-Plated Copper Alloy    |

RoHS Compliant  
UL File No: E23301



Specifications subject to change without notice.



## Double-Pole Rocker Switch

# YR Series

**Dimensions** inches (mm)



Z = Panel Thickness

### Recommended Panel Cut-Out Dimensions

| Dim. Z                           | Dim. X           | Dim. Y          |
|----------------------------------|------------------|-----------------|
| 0.030 to 0.049<br>(0.75 to 1.25) | 1.181<br>(30.00) | 0.866<br>(22.0) |
| 0.049 to 0.079<br>(1.25 to 2.00) | 1.189<br>(30.2)  | 0.866<br>(22.0) |
| 0.079 to 0.118<br>(2.00 to 3.00) | 1.201<br>(30.5)  | 0.866<br>(22.0) |

## Ordering Information

| Series | Code | Circuitry   |
|--------|------|-------------|
| YR     | 2    | Single Pole |
| M      | 3    | Double Pole |

| Code | Contact Rating                                                                                     |
|------|----------------------------------------------------------------------------------------------------|
| M    | 16A 125/250VAC 3/4 HP 20A 125VAC cULus<br>16(4) A 250V ~ T125/65 VDE<br>16(8) A 250V ~ T125/65 VDE |

Note: 10(2)A 250V~ 50E3 T125 special order

| Code | Switch Function |
|------|-----------------|
| 2    | On - Off        |
| 3    | On - On         |
| 5    | (On) - Off      |
| 6    | (On) - On       |

| Code | Terminal type inches (mm) |
|------|---------------------------|
| A    | 0.189" (4.8) QC           |
| F    | 0.250" (6.3) QC           |

| Code | Actuator Type |
|------|---------------|
| 2    | Curve         |

| Code | Actuator Marking |
|------|------------------|
| B    | Blank            |
| C    | ⊖ ⊕              |
| D    | ⊖ ⊕              |
| E    | ⊖ ⊕              |
| F    | ⊖ ⊕              |

| Code | Housing Color |
|------|---------------|
| B    | Black         |
| W    | White         |
| Y    | Grey          |

| Code | Actuator Color |
|------|----------------|
| A    | Amber          |
| B    | Black          |
| G    | Green          |
| R    | Red            |
| U    | Blue           |
| W    | White          |
| Y    | Grey           |

| Code | Lighted                    |
|------|----------------------------|
| N    | Non-Lighted                |
| L    | Lighted (Bulb 125VAC)      |
| E    | Lighted (Bulb 250VAC)      |
| F    | Lighted 5VDC Incandescent  |
| G    | Lighted 6VDC Incandescent  |
| H    | Lighted 12VDC Incandescent |

| Code | Splashproof    |
|------|----------------|
| N    | No Rocker Boot |

Rocker boot sold separately: P/N 0015-0646

## Examples of Common Part Numbers and Descriptions inches (mm)

| Part Number  | Circuitry | Switch Function  | Terminal Type             | Actuator/Housing Color | Legend Marking |
|--------------|-----------|------------------|---------------------------|------------------------|----------------|
| YRM32F2FBBNN |           | On - Off         | 0.250 (6.3) Quick-Connect | Black/Black            |                |
| YRM33F2BBBNN |           | On - On          | 0.250 (6.3) Quick-Connect | Black/Black            |                |
| YRM32F2BBRLN |           | On - Off/Lighted | 0.250 (6.3) Quick-Connect | Red/Black              |                |

## Contact

Call, fax or visit our Website for more information.

**ZF Electronics Corporation**  
11200 88th Avenue  
Pleasant Prairie, WI 53158

Phone: 262.942.6500  
Web: [www.cherrycorp.com](http://www.cherrycorp.com)  
Email: [cep\\_sales@zf.com](mailto:cep_sales@zf.com)  
Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.

Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2007 ZF Electronics Corporation

Last Updated: 10/01/12

