

NOTES:


① MAT'L: PURE NICKEL

PLATING: NONE

STUD SIZES: (.005)

02 = .094 209 = .209
 04 = .119 413 = .413
 06 = .146
 08 = .173
 10 = .198
 14 = .265
 56 = .328
 38 = .390

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$



FILE NO.

C-CO-101-04

WIRE SIZE: 12-10 AWG
 40-6.0 MM²


PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES		
101	$\frac{.750}{19.05}$	$\frac{.611}{15.52}$	$\frac{1.280}{32.51}$	14, 56, 38, 76, 12		
C-U-128-	$\frac{.375}{9.53}$	$\frac{.303}{7.70}$	$\frac{.785}{19.94}$	04, 06, 08, 10, 209		
C-U-130-	$\frac{.530}{13.46}$	$\frac{.393}{9.98}$	$\frac{.952}{24.18}$	10, 14, 56, 38		
136	$\frac{.282}{7.16}$	$\frac{.306}{7.77}$	$\frac{.741}{18.82}$	04, 06, 08		
C-U-140-	$\frac{.592}{15.04}$	$\frac{.468}{11.89}$	$\frac{1.056}{26.82}$	10, 14, 56, 38, 209, 413		
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE: NTS	DATE	TITLE: TEMP-TERM (1200°)	
FRAC.	DEC.	ANG.			DRWN. BY: ELLIF	2-3-87
±	±	±			CHKD. BY:	
					APPRD. BY:	
					TERMINAL RING TONGUE	
					KRIIMPITE	
					100-SERIES	
					DWG. NO.	A
					CUSTOMER DWG.	



ETC
INCORPORATED
molex

ETC mox
 INCORPORATED

10	9	8	7	6	5	4	3	2	1
MATERIAL NO. LOOSE PIECE	ENG. NO.	MATERIAL NO. TAPE MOUNTED	ENG. NO.	STUD SIZE	"S" ±.005/0.13	STOCK THICKNESS	FINISH		
190690200	C-128-04	190690147	C-128-04T	4	.119/(3.02)	.040/(1.02)	SEE NOTE 2		
190690202	C-128-06	190690148	C-128-06T	6	.146/(3.71)				
190690205	C-128-08	190690208	C-128-08T	8	.173/(4.39)				
190690209	C-128-10	190690212	C-128-10T	10	.198/(5.03)				
190690215	C-128-209	---	---	209	.209/(5.18)				
192030159	C-U-128-06	192030111	C-U-128-06T	6	.146/(3.71)	.038/(0.97)			
192030160	C-U-128-08	192030112	C-U-128-08T	8	.173/(4.39)				
192030113	C-U-128-10	192030114	C-U-128-10T	10	.198/(5.03)				
190690682	C-128-10-AU	---	---	10	.198/(5.03)	.040/(1.02)	SEE NOTE 3		



NOTES:

1. MATERIAL: COPPER.
2. FINISH: TIN PLATING, 100(2.5)µin(µm) MIN
3. FINISH: GOLD, 50(1.25)µin(µm) MIN. OVER NICKEL, 50(1.25)µin(µm) MIN. PLATING.
4. WIRE SIZE: 12-10 AWG, 4.0-6.0 MM²
5. PARTS ARE ROHS COMPLIANT.

RELEASED

EC NO: IFC2015-0823

DRWNGR0JAS01 2014/10/30

CHKD: JMACNEIL 2014/10/30

APPR: JMACNEIL 2014/11/19

A

DESCRIPTION

REV

QUALITY SYMBOLS

▽=0

▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---
ANGULAR ±---°		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

IN/MM

DRAWN BY	DATE
BDEROSS	2000/6/13
CHECKED BY	DATE
JMACNEIL	2014/10/30
APPROVED BY	DATE
JMACNEIL	2014/11/19

MATERIAL NO.

SEE CHART

SIZE

B

SCALE

DESIGN UNITS

INCH

THIRD ANGLE PROJECTION

TITLE

RING TONGUE TERMINAL
KRIMPTITE, 128 SERIES
12-10 AWG

MOLEX INCORPORATED

DOCUMENT NO.

SD-19069-020

SHEET NO.

1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[19203-0113](#) [19203-0114](#)