

## G-type Twin Wheel Caster




### Characteristic

Small turning radius with its twin wheels.

### Application


Large size office automation appliances, etc.

#### G7N□S (with stopper)



Model No.	Material		Allowable Load (kg)	Net Weight (g)	Code No.
	Body	Wheel			
G7	ADC	PA	150	250	9924
G7S				264	9928
G7N3				178	9925
G7N3S				192	9929
G7N10				178	9926
G7N10S				192	9930
G7N12				188	9927
G7N12S				202	9931

#### G7S (with stopper)



### Size List

Model No.	A	B	C	D	E	G	d	H1	H2	J1	J2	K	L	W1	W2
G7	55	φ48	φ62	φ60	17	φ6.5	W3/8	79.5	70	t3.8	t6	17	19	44	18
G7S															
G7N3															
G7N3S															
G7N10	55	φ48	φ62	φ60	17	φ6.5	M10	79.5	70	t3.8	t6	17	19	44	18
G7N10S															
G7N12															
G7N12S	55	φ48	φ62	φ60	17	φ6.5	M12	79.5	70	t3.8	t6	17	22	44	18

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.