

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

2010

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.
Tous droits internationaux réservés.

LOC


DIST


00

REVISIONS


P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
-	-		-	-	-

SIGLE FOURNISSEUR
SUPPLIER LOGO







COUPE D-D
SECTION D-D




COUPE C-C
SECTION C-C



IDENTIFICATION DE LA GAMME
"B" = DE 5 A 6 MM2
WIRE RANGE IDENTIFICATION
"B" = FROM 5 TO 6 MM2



Y = IDENTIFICATION MATIERE
EN Cu MICRO ALLIE. VOIR TABLEAU
Y = MATERIAL IN Cu MICRO ALLOY
SEE DESCRIPTION IN TABLE



13±0.2 (35)

7.7±0.2 (34)

4.5 (33)

2x 3.8 (32)

2x 16.2±0.2 (37)

2x 3 (36)

(1.8)

(2.25)

(19.3)

(4.4)

PAS = 25 (40)


PITCH = 25

(30)

9.4±0.15

8 (31)

A



NOTA

NOTES

1	(X) = POUR INFORMATION	1	(X) = FOR INFORMATION
2	CONDITIONNEMENT : VOIR SPECIFICATION 107-15603	2	PACKAGING : SEE SPECIFICATION 107-15603
3	SPC = DIMENSION SUIVIE EN SPC	3	SPC = DIMENSION WITH MANUFACTURING CONTROL

REFERENCE / PN
TYCO Electronics

REFERENCE CLIENT
PN CUSTOMER

Y :
REPERE MATIERE
MATERIAL REPERE

MATIERE
MATERIAL

TRAITEMENT DE SURFACE
HEAT TREATMENT

1544968-1		S	CuSnMg SELON SPECIFICATION: 100-421 H02 CuSnMg ACCORDING TO SPECIFICATION: 100-421 H02	PRE-ETAME SnAg DE 1 A 3µ SELON SPECIFICATION 112-73-2 PRE-TINNED SnAg FROM 1 TO 3µ ACCORDING SPECIFICATION 112-73-2
1544968-2		T		PRE-ARGENTE Ag DE 1 A 3µ SELON SPECIFICATIONS 212-7, 112-32 ET 118-91 PRE-SILVERED Ag FROM 1 TO 3µ ACCORDING SPECIFICATIONS 212-7, 112-32 AND 118-91

PRODUIT ASSOCIE / APPLIED PRODUCT


DESIGNATION DES JOINTS SEALS DESCRIPTION	REFERENCE / PN TYCO Electronics	REFERENCE / PN CUSTOMER	COULEUR COLOR
JOINT UNIFILAIRE NG9K 2.5 A 5 MM2 NG9K SINGLE WIRE SEAL 2.5 TO 5 MM2	1544970-1		MARRON / BROWN
JOINT UNIFILAIRE NG9K 6 A 7 MM2 NG9K SINGLE WIRE SEAL 6 TO 7 MM2	1544970-2		BLEU / BLUE

INTERFACE MONTABILITE / INTERFACE CAVITY

1801558

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.
CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR SON RÉDACTEUR.
A EST RESPONSABLE D'ÊTRE MIS AU JOUR EN FONCTION
DES REVISIONS D'UN DE FRANCE POUR OBTENIR LA DERNIÈRE REVISION.


DIMENSIONS:
mm



MATERIAL
MATIERE

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES
(SUIVIR DE DECIMALES)
1 P.L.C./DEC. ±
2 P.L.C./DEC. ±0.1
3 P.L.C./DEC. ±
4 P.L.C./DEC. ±
ANGLES
FINISH
FINITION



SEE TABLE

DWN/DESSINE
P.FLORES
CHK/VERIFIE
L.CORONELLI
APVD/APPROVE
J.DAHER
PRODUCT SPEC
SPEC. PRODUIT
108-15382
APPLICATION SPEC
SPEC. APPLICATION
114-15109
WEIGHT
MASSE APPROX.
0.002kg

01FEB10
01FEB10
01FEB10

00779
C=1544968

CUSTOMER DRAWING /PLAN CLIENT

Tyco Electronics

Tyco Electronics France SAS
517, avenue de la Boisse, 73000 Chambéry

NAME
TITRE
LANGUETTE NG1+ - 5 A 6mm2
NG1+ TAB - WIRE RANGE 5 TO 6mm2

SIZE
FORMAT
A2

CAGE CODE
00779

DRAWING NO
No PLAN
C=1544968

RESTRICTED TO
RESERVE A
-

SHEET
FEUILLE
1

OF
DE
1

REV
A

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE
2:1

SHEET
FEUILLE
1

OF
DE
1

REV
A

1471-9 (2/09)