









P.C.B. HOLE LAYOUT

TOLERANCE $\pm .003$

1. INSULATOR MATERIAL - THERMOPLASTIC POLYESTER, PCT, BLACK, UL94 V-O
2. MACHINED CONTACT - BECU, PLATED WITH 80-200 μ ".
TIN (LEAD FREE) OVER 75-100 μ " COPPER.
3. SLEEVE - COPPER, PLATED WITH 180-340 μ "
THK TIN (LEAD FREE) OVER 75-125 MIN NICKEL.
4. MACHINED CONTACT - BECU, PLATED WITH 25 μ " MIN.
GOLD OVER 30-100 μ " NICKEL.
5. ELECTRICAL:
CONTACT RESISTANCE: 10 MILLIOHMS MAX
CONTACT RATING: 3 AMPS
CAPACITANCE: 1.0 pF PER MIL-STD-202, METHOD 305
INSULATION RESISTANCE: 5000 OHMS MIN @ 500 VDC PER
MIL-STD-1344, METHOD 3003.1
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS (RMS) PER
MIL-STD-1344, METHOD 3001.1
6. MECHANICAL:
INSERTION FORCE: 134 GRAMS AVG
WITHDRAWAL FORCE: 63 GRAMS AVG
"ACCEPTS IC PIN - .009"X.015" THROUGH .011"X.020", OR
.016" TO .021" DIAMETER, .150/.105 LONG"
7. ENVIRONMENTAL:
OPERATING TEMPERATURE: -55°C TO -105°C
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T.KRAYBILL	07NOV03	 TE Connectivity	
		CHK K.WRIGHT	-		
DIMENSIONS:		NAME		OPEN FRAME DIP, PREMIUM (MACHINE CONTACT), LEAD FREE (REF AUGAT 800 SERIES)	
INCHES		APVD K.WRIGHT			
		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		—			
		APPLICATION SPEC			
		—			
		ANGLES			
MATERIAL	FINISH	WEIGHT	—	A1 00779C-1571586	
		CUSTOMER DRAWING		SCALE	A1 00779C-1571586
				SHEET	1 OF 2
				REV	B

8		7		6		5		4		3		2		1	
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				-				-			
© COPYRIGHT - By -				ALL RIGHTS RESERVED.											